

PRC FT25-0-HSG - Device connector front mounting



1065795

<https://www.phoenixcontact.com/us/products/1065795>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Range of articles: PRC 35, color: black, rated voltage: 690 V AC, Connector housing without contact insert. Please order the appropriate contact inserts according to the accessories list

Your advantages

- Versatile interfaces with straight and angled connector housings
- Universal accommodation of existing connector heads with screw connection technology
- Modular system for optimized storage
- Locking mechanism can be unlocked manually or using a tool
- Ideal for indoor and outdoor use due to weatherproof materials

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1065795 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB03 |
| Product key | ABL CAD |
| GTIN | 4055626728384 |
| Weight per piece (including packing) | 30.2 g |
| Weight per piece (excluding packing) | 16.126 g |
| Customs tariff number | 85389099 |
| Country of origin | PL |

Technical data

Notes

| | |
|--------------------|--|
| Order information: | Connector housing without contact insert. Please order the appropriate contact inserts according to the accessories list |
|--------------------|--|

Safety note

| | |
|-------------|---|
| Safety note | <ul style="list-style-type: none"> • WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible. • WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product. WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property. • Assembled products may not be manipulated or improperly opened. • Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at phoenixcontact.com/products). • When using the product in direct connection with third-party manufacturers, the user is responsible. • For operating voltages > 50 V AC, conductive connector housings must be grounded • Ensure that the protective or functional ground has been properly connected. • VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector • Observe the corresponding technical data. You will find information: <ul style="list-style-type: none"> o On the product o On the packing label o In the supplied documentation o Online at phoenixcontact.com/products under the product • Only use tools recommended by Phoenix Contact • The installation notes/Design In documents online on the download page at phoenixcontact.com/products must be observed for this product. • Use a protective cap to protect connectors that are not in use. The suitable accessories are available online in the accessory section of the product at phoenixcontact.com/products • Operate the connector only when it is fully plugged in. • Operate the connector only when it is fully plugged in and interlocked. • Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the |
|-------------|---|

1065795

<https://www.phoenixcontact.com/us/products/1065795>

| | |
|--|--|
| | standards. |
| | <ul style="list-style-type: none"> • Observe the minimum bending radius of the cable. Lay the cable without twisting it. |
| | <ul style="list-style-type: none"> • The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting warnings (e.g. DIN EN ISO 13732-1:2008-12). |

Product properties

| | |
|----------------|--------------------|
| Product type | Panel feed-through |
| Product family | PRC 35 |

Insulation characteristics

| | |
|---------------------|----|
| Protection class | II |
| Degree of pollution | 2 |

Dimensions

| | |
|--------|---------|
| Width | 37.6 mm |
| Height | 37.6 mm |
| Length | 51.6 mm |

Electrical properties

| | |
|-----------------------------|--|
| Rated voltage (III/2) | 690 V |
| Rated voltage | 690 V AC (III/2.00) in accordance with IEC 61984 |
| | 600 V AC (III/2.00) In accordance with UL 2238 |
| | 500 V DC (III/2.00) in accordance with IEC 61535, when mounted |
| Rated surge voltage (III/3) | 6 kV |

Material specifications

| | |
|--|------------------|
| Color (Housing) | black (RAL 9005) |
| Color of the housing part | black |
| Material Housing | PPE |
| Material Screw connection | PPE |
| Material Seal | Silicon |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | I / CTI 6000 |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|---|
| Degree of protection | IP66 |
| | IP68 (2 m / 24 h) |
| | IP69 |
| | IP66/IP68 (2 m / 24 h) IP69K |
| Category of shock impact | IK08 (-25°C) |
| Ambient temperature (operation) | -40 °C ... 105 °C (dependent on the derating curve) |

PRC FT25-0-HSG - Device connector front mounting



1065795

<https://www.phoenixcontact.com/us/products/1065795>

| | |
|---|------------------|
| Ambient temperature (storage/transport) | -40 °C ... 70 °C |
| Ambient temperature (assembly) | -5 °C ... 85 °C |

1065795

<https://www.phoenixcontact.com/us/products/1065795>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1065795>



cUL Recognized

Approval ID: E468743-20200116



UL Recognized

Approval ID: E468743-20200116



VDE Zeichengenehmigung

Approval ID: 40054228



VDE Zeichengenehmigung

Approval ID: 40054231

1065795

<https://www.phoenixcontact.com/us/products/1065795>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440602 |
| ECLASS-15.0 | 27440602 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002566 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

1065795

<https://www.phoenixcontact.com/us/products/1065795>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Triphenyl phosphate(CAS: 115-86-6) |
| SCIP | c639faa1-34cc-4ee1-a0f6-9422b4ee3cf0 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.286 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com