

# UC-EM (20X9) SR - Snap-in markers



1057865

<https://www.phoenixcontact.com/us/products/1057865>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Snap-in markers, Sheet, unmarked, can be labeled with: BLUEMARK E.CARD, BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: latching, text field height: 9 mm, text field width: 20 mm



## Your advantages

- The markers, which are supplied in uniform sheets, can be labeled quickly and easily using the BLUEMARK LED
- The UC-EM ... UniCard labeling range includes markers for devices and switching devices from a wide range of manufacturers
- The format automatically ensures printing with a high degree of positioning accuracy
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts

## Commercial data

Item number	1057865
Packing unit	10 pc
Minimum order quantity	960 pc
Product key	BG2417
GTIN	4055626702315
Weight per piece (including packing)	22.22 g
Weight per piece (excluding packing)	22.22 g
Country of origin	PL

# UC-EM (20X9) SR - Snap-in markers



1057865

<https://www.phoenixcontact.com/us/products/1057865>

## Technical data

### Product properties

Product type	Device marker
--------------	---------------

### Marking

Identification technology	UV LED technology
---------------------------	-------------------

### Dimensions

Width	19.85 mm
Height	8.90 mm
Depth	3.20 mm
Length	9 mm

### Text field

Text field width	20 mm
Text field height	9 mm

### Material specifications

Color	silver
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

#### Wipe resistance of inscriptions

Specification	IEC 61010-1:2010-06
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

### Mounting

Mounting type	latching
---------------	----------

# UC-EM (20X9) SR - Snap-in markers



1057865

<https://www.phoenixcontact.com/us/products/1057865>

## Classifications

### ECLASS

ECLASS-13.0

27281103

### ETIM

ETIM 9.0

EC001288

### UNSPSC

UNSPSC 21.0

39131500

# UC-EM (20X9) SR - Snap-in markers



1057865

<https://www.phoenixcontact.com/us/products/1057865>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)