

AXL F PSAI8 I 1F - Safety module



1061424

<https://www.phoenixcontact.com/us/products/1061424>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline F, Analog input module, Functional safety, PROFIsafe, Only for connection to Phoenix Contact or Siemens controllers in PROFINET systems, Safe analog inputs: 8 (1-channel assignment), 4 (2-channel assignment), 4 mA ... 20 mA, connection technology: 2-conductor (shielded, twisted pair), degree of protection: IP20; Extended temperature range.

Your advantages

- Up to Cat. 4/PL e in accordance with EN ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Safe analog value acquisition 4 ... 20 mA
- 8 safe inputs for 1-channel assignment
- 4 safe inputs for 2-channel assignment

Commercial data

Item number	1061424
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN03
Product key	DNA522
GTIN	4055626715391
Weight per piece (including packing)	227 g
Weight per piece (excluding packing)	235 g
Customs tariff number	85389099
Country of origin	DE


AXL F PSAI8 I 1F - Safety module



1061424
<https://www.phoenixcontact.com/us/products/1061424>

Technical data

Dimensions

Dimensional drawing		
Width		53.6 mm
Height		126.1 mm
Depth		54 mm
Note on dimensions		Housing dimensions

Notes

Note on application	
Note on application	Only for industrial use

Mounting

Mounting type	DIN rail mounting
Mounting position	any

Material specifications

Color (Housing)	yellow (RAL 1018)
-----------------	-------------------

System properties

Programming data	
Input address area	22 Byte (PROFIsafe 2.6.1)
Output address area	5 Byte (PROFIsafe 2.6.1)
Fieldbus data telegram	
Required configuration data	31 Byte

Input data

Analog:	
Input name	Safe analog inputs
Number of inputs	8 (1-channel assignment)
	4 (2-channel assignment)
Connection method	Push-in connection
Connection technology	2-conductor (shielded, twisted pair)
Current input signal	4 mA ... 20 mA
Input resistance current input	typ. 104 Ω

AXL F PSAI8 I 1F - Safety module



1061424

<https://www.phoenixcontact.com/us/products/1061424>

A/D converter resolution	16 bit
Data formats	Standardized representation
Input filter	30 Hz
Filtering	RFI filtering / passive TP 1st order
Limit frequency (3 dB)	30 Hz
Measured value representation	16 bits
Protective circuit	Transient protection of inputs; Suppressor diode
	Overload protection; No; ± 5.2 V DC, maximum, $I_{\max} = 50$ mA

Product properties

Product type	I/O component
Product family	Axioline F
Application	Functional safety
	PROFIsafe
	Only for connection to Phoenix Contact or Siemens controllers in PROFINET systems
Type	modular
Mounting position	any
Operating mode	PROFIsafe 2.6.1
Special properties	Extended temperature range

Insulation characteristics

Overvoltage category	II (IEC 60664-1)
Pollution degree	2 (EN 60664-1)

Electrical properties

Maximum power dissipation for nominal condition	1.8 W
---	-------

Potentials: Axioline F local bus supply (U_{Bus})

Supply voltage	5 V DC (via bus base module)
Current draw	max. 110 mA (at U_{Bus} 5 V DC)
	typ. 105 mA (at U_{Bus} 5 V DC)

Potentials: I/O supply (U_A)

Supply voltage	24 V DC (Power connector)
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 31 mA
	typ. 25.5 mA (Power supply from U_A with 30 V DC)
Protective circuit	Surge protection; electronic (35 V, 0.5 s)
	Reverse polarity protection (parallel)
	Undervoltage detection; at 17 V
	Surge voltage detection; No
Protection	max. 8 A (slow-blow, required externally)

Connection data

Connection method	Push-in connection
-------------------	--------------------

AXL F PSAI8 I 1F - Safety module



1061424

<https://www.phoenixcontact.com/us/products/1061424>

Note on the connection method	Note the specification in the section Conductor cross-sections, and stripping and insertion lengths.
Conductor cross-section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross-section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross-section AWG	24 ... 16
Stripping length	8 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-35 °C ... 60 °C
Degree of protection	IP20
Degree of protection at installation location	min. IP54
Note	Recommendation Do not use the AXL F PSAI8 I 1F in an atmosphere that contains corrosive gas.
Air pressure (operation)	70 kPa ... 108 kPa
Air pressure (storage/transport)	66 kPa ... 108 kPa
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	5g
Shock in accordance with EN 60068-2-27/IEC 60068-2-27	30g
Continuous shock in accordance with EN 60068-2-27/IEC 60068-2-27	10g

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Air clearances and creepage distances

Air clearances and creepage distances	IEC 60664-1
---------------------------------------	-------------

Characteristics

Safety data: EN ISO 13849

Performance level (PL)	c (1-channel assignment)
	e (2-channel assignment)

AXL F PSAI8 I 1F - Safety module


1061424

<https://www.phoenixcontact.com/us/products/1061424>



Drawings

Dimensional drawing



Dimensions (in mm)

AXL F PSAI8 I 1F - Safety module



1061424

<https://www.phoenixcontact.com/us/products/1061424>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1061424>



DNV GL

Approval ID: TAA00000DF

PROFIsafe

Approval ID: Z20296

BSH

Approval ID: 840



cULus Listed

Approval ID: E238705



Functional Safety

Approval ID: 968/EZ 650.04/20

FS Thermoprocess

Approval ID: 968 INS 799.01 25

AXL F PSAI8 I 1F - Safety module



1061424

<https://www.phoenixcontact.com/us/products/1061424>

Classifications

ECLASS

ECLASS-13.0	27242601
ECLASS-15.0 ASSET	27250101
ECLASS-15.0	27242601

ETIM

ETIM 10.0	EC001596
-----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

AXL F PSAI8 I 1F - Safety module



1061424

<https://www.phoenixcontact.com/us/products/1061424>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I, 7(c)-II

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	45044652-4cb2-44f1-8b25-ffbde4a7f0ad

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com