# PTRV 8 /BK - Marshalling panel

1061722

https://www.phoenixcontact.com/us/products/1061722

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marshalling panel, nom. voltage: 250 V, nominal current: 8 A, connection method: Push-in connection, 1st, 2nd, 3rd, 4th, 5th, 6th, 7th and 8th level, Rated cross section: 1.5 $mm^2$, cross section: 0.14 $mm^2$ - 2.5 $mm^2$, mounting: NS 35/7,5, NS 35/15, color: gray, color of connection elements: black

## Commercial data

| | |
|---|---|
| Item number | 1061722 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Sales key | BE62 |
| Product key | BE6211 |
| GTIN | 4055626716824 |
| Weight per piece (including packing) | 36.88 g |
| Weight per piece (excluding packing) | 33.78 g |
| Customs tariff number | 85369010 |
| Country of origin | PL |

# Technical data

## Product properties

| | |
|---|---|
| Product type | Marshalling terminal |
| Number of positions | 2 |
| Number of connections | 32 |
| Number of rows | 8 |
| Potentials | 8 |

Insulation characteristics

| | |
|---|---|
| Overvoltage category | III |

## Electrical properties

| | |
|---|---|
| Rated surge voltage | 4 kV |
| Maximum power dissipation for nominal condition | 0.56 W |

## Connection data

| | |
|---|---|
| Number of connections per level | 4 |
| Nominal cross section | 1.5 mm² |

1st, 2nd, 3rd, 4th, 5th, 6th, 7th and 8th level

| | |
|---|---|
| Connection method | Push-in connection |
| Stripping length | 8 mm ... 10 mm |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 0.14 mm² ... 2.5 mm² |
| Cross section AWG | 26 ... 14 (converted acc. to IEC) |
| Conductor cross-section flexible | 0.14 mm² ... 1.5 mm² |
| Conductor cross-section, flexible [AWG] | 26 ... 16 (converted acc. to IEC) |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm² ... 1.5 mm² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 0.14 mm² ... 1.5 mm² |
| Nominal cross section | 1.5 mm² |
| Nominal current | 8 A |
| Maximum load current | 8 A (with 1.5 mm² conductor cross-section) |
| Nominal voltage | 250 V |

## Dimensions

| | |
|---|---|
| Width | 8.3 mm |
| Height | 100 mm |
| Depth on NS 35/7,5 | 87.5 mm |
| Depth on NS 35/15 | 95 mm |

## Material specifications

| | |
|---|---|
| Color | gray (RAL 7042) |
| Color of connection elements | black |
| Flammability rating according to UL 94 | V0 |

| | |
|---|---|
| Insulating material group | I |
| Insulating material | PA |

## Mechanical properties

Mechanical data

| | |
|---|---|
| Open side panel | Yes |

## Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -60 °C ... 105 °C (max. short-term operating temperature RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

## Standards and regulations


| | |
|---|---|
| Connection in acc. with standard | IEC 60947-7-1 |

## Mounting

| | |
|---|---|
| Mounting type | NS 35/7,5 |
| | NS 35/15 |

## Drawings

Circuit diagram



## Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1061722

**CSA**
Approval ID: 158887

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| B | | | | |
| | 300 V | 10 A | 26 - 14 | - |
| D | | | | |
| | 300 V | 10 A | 26 - 14 | - |

**IECEE CB Scheme**
Approval ID: NL-58817

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| | 250 V | 8 A | - | - |

**EAC**
Approval ID: RU C-DE.BL08.B.00682

**cULus Recognized**
Approval ID: E60425

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| D | | | | |
| | 300 V | 10 A | 26 - 14 | - |

**KEMA-KEUR**
Approval ID: 71-102890

| | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
|---|---|---|---|---|
| keine | | | | |
| Only flexible conductors | 250 V | 8 A | - | 0.14 - 1.5 |
| Only rigid conductors | 250 V | 8 A | - | 0.14 - 2.5 |

**DNV**
Approval ID: TAE000016Y

**EAC**
Approval ID: KZ7500651131219505

## Classifications

### ECLASS

| | |
|---|---|
| ECLASS-13.0 | 27250105 |
| ECLASS-15.0 | 27250105 |

### ETIM

| | |
|---|---|
| ETIM 10.0 | EC000897 |

### UNSPSC

| | |
|---|---|
| UNSPSC 21.0 | 39121400 |

## Environmental product compliance

EU RoHS

| | |
|---|---|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |

China RoHS

| | |
|---|---|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|---|---|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com