PRC FT25-45/90-HSG - Device connector front mounting

1065796

https://www.phoenixcontact.com/us/products/1065796

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector front mounting, Range of articles: PRC 35, color: black, rated voltage: 690 V AC, Connector housing without contact insert. Please order the appropriate contact inserts according to the accessories list

Your advantages

- Versatile interfaces with straight and angled connector housings
- Universal accommodation of existing connector heads with screw connection technology
- Modular system for optimized storage
- Locking mechanism can be unlocked manually or using a tool
- Ideal for indoor and outdoor use due to weatherproof materials

Commercial data

Item number	1065796
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB03
Product key	ABLCAD
GTIN	4055626730301
Weight per piece (including packing)	44.1 g
Weight per piece (excluding packing)	29.585 g
Customs tariff number	85389099
Country of origin	PL

Technical data

Notes

Order information:	Connector housing without contact insert. Please order the appropriate contact inserts according to the accessories list

Product properties

Product type	Panel feed-through
Product family	PRC 35

Insulation characteristics

Protection class	II
Degree of pollution	2

Dimensions

Width	60.9 mm
Height	37.6 mm
Length	74.8 mm

Electrical properties

Rated voltage (III/2)	690 V
Rated voltage	690 V AC (III/2) in accordance with IEC 61984
	600 V AC (III/2) In accordance with UL 2238
	500 V DC (III/2) in accordance with IEC 61535, when mounted
Rated surge voltage (III/3)	6 kV

Material specifications

Color (Housing)	black (RAL 9005)
Color of the housing part	black
Material Housing	PPE
Material Screw connection	PPE
Material Seal	Silicon
Flammability rating according to UL 94	V0
Insulating material group	I / CTI 600
O-ring material	EPDM

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66/IP68 (2 m / 24 h) IP69K
	IP66/IP68 (2 m / 24 h) IP69K
Ambient temperature (operation)	-40 °C ... 105 °C (dependent on the derating curve)
Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 85 °C

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1065796

cUL Recognized
Approval ID: E468743-20200116

UL Recognized
Approval ID: E468743-20200116

VDE Zeichengenehmigung
Approval ID: 40054228

VDE Zeichengenehmigung
Approval ID: 40054231

Classifications

ECLASS

ECLASS-13.0	27440602
ECLASS-15.0	27440602

ETIM

ETIM 10.0	EC002566

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	Triphenyl phosphate(CAS: 115-86-6)
SCIP	cdfe033c-1f41-4158-94e1-ce2229bcdc1e

EF3.1 Climate Change

CO2e kg	1.208 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com