

HC-COM-BAWS-EL-AL - Housing



1078593

<https://www.phoenixcontact.com/us/products/1078593>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Panel mounting base COM, with single locking latch, material: Die-cast aluminum, salt water resistant, height: 37.5 mm, cable gland: none, Standard

Your advantages

- Good shielding in the event of electromagnetic interference

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1078593 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF59 |
| Product key | AF7APP |
| GTIN | 4055626794112 |
| Weight per piece (including packing) | 89.5 g |
| Weight per piece (excluding packing) | 89 g |
| Customs tariff number | 85389099 |
| Country of origin | CN |

1078593


<https://www.phoenixcontact.com/us/products/1078593>

Technical data

Product properties

| | |
|---------------------|----------------------------|
| Product type | Housing with locking latch |
| Housing type | Panel mounting base |
| Product family | HC-COM |
| Application | Standard |
| Type | COM |
| Pg screw connection | none |

Dimensions

| | |
|---------------------|--|
| Dimensional drawing |  |
| Width | 49.5 mm |
| Height | 37.5 mm |
| Length | 63.5 mm |
| Hole diameter | 3.5 mm |

Installation dimensions

| | |
|-------------------------------|---------|
| Width of the assembly cutout | 24.5 mm |
| Length of the assembly cutout | 27 mm |

Material specifications

| | |
|--|---|
| Flammability rating according to UL 94 | V0 (Interlock) |
| Seal material Flat gasket | NBR, conductive |
| Housing material | Die-cast aluminum, salt water resistant |
| Locking latch material | PA |

Mechanical properties

Mechanical data

| | |
|--------------|-------|
| Locking type | Latch |
|--------------|-------|

Connection data

| | |
|-------------------|---|
| Tightening torque | 0.8 Nm ... 1.2 Nm (for M4 mounting screws on the surface-mount housing) |
|-------------------|---|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Degree of protection | IP66 |
| Impact strength | IK06 |
| Ambient temperature (operation) | -40 °C ... 125 °C |


HC-COM-BAWS-EL-AL - Housing

1078593


<https://www.phoenixcontact.com/us/products/1078593>

Drawings

Dimensional drawing



Dimensional drawing



Mounting cutout

HC-COM-BAWS-EL-AL - Housing



1078593

<https://www.phoenixcontact.com/us/products/1078593>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1078593>



cUL Recognized
Approval ID: E255026



UL Recognized
Approval ID: E255026

HC-COM-BAWS-EL-AL - Housing



1078593

<https://www.phoenixcontact.com/us/products/1078593>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000437 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

HC-COM-BAWS-EL-AL - Housing



1078593

<https://www.phoenixcontact.com/us/products/1078593>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com