


# PTV 2,5-QUATTRO-PE - Protective conductor terminal block



1079012

<https://www.phoenixcontact.com/us/products/1079012>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective conductor terminal block, number of connections: 4, connection method: Push-in connection, Rated cross section: 2.5 mm<sup>2</sup>, cross section: 0.14 mm<sup>2</sup> - 4 mm<sup>2</sup>, mounting type: NS 35/7,5, NS 35/15, color: green-yellow

## Your advantages

- Time-saving conductor connection thanks to tool-free direct-connection technology
- Vibration-resistant and maintenance-free conductor connection
- Full flexibility thanks to the standardized CLIPLINE complete bridging, marking, and testing accessories
- Meet the requirements of DIN EN 60947-7-2 or IEC 60947-7-2 for protective conductor connections
- High level of safety thanks to the low-resistance connection to the ground potential via the top-hat rail
- Direct contacting with the DIN rail enables fast, error-free grounding without additional wiring effort.

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1079012       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE23          |
| Product key                          | BE2323        |
| GTIN                                 | 4055626797519 |
| Weight per piece (including packing) | 12.484 g      |
| Weight per piece (excluding packing) | 11.063 g      |
| Customs tariff number                | 85369010      |
| Country of origin                    | CN            |

# PTV 2,5-QUATTRO-PE - Protective conductor terminal block



1079012

<https://www.phoenixcontact.com/us/products/1079012>

## Technical data

### Product properties

|                       |                       |
|-----------------------|-----------------------|
| Product type          | Ground terminal block |
| Product family        | PTV                   |
| Area of application   | Railway industry      |
|                       | Machine building      |
|                       | Plant engineering     |
|                       | Process industry      |
| Number of connections | 4                     |
| Number of rows        | 1                     |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Electrical properties

|   |        |
|---|--------|
| Rated surge voltage                             | 8 kV   |
| Maximum power dissipation for nominal condition | 0.77 W |

### Connection data

|   |  |
|---|--|
| Grounding foot  | Yes  |
| Number of connections per level                                   | 4  |
| Nominal cross section   | 2.5 mm <sup>2</sup>                          |
| Connection method   | Push-in connection                           |
| Stripping length  | 8 mm ... 10 mm                               |
| Internal cylindrical gage   | A3   |
| Connection in acc. with standard                                  | IEC 60947-7-2                                |
| Conductor cross-section rigid                                     | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Cross section AWG   | 26 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible                                  | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section, flexible [AWG]                           | 26 ... 12 (converted acc. to IEC)            |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Nominal cross section   | 2.5 mm <sup>2</sup>                          |

### Connection cross sections directly pluggable

|   |   |
|---|---|
| Conductor cross-section rigid                                     | 0.5 mm <sup>2</sup> ... 4 mm <sup>2</sup>   |
| Conductor cross-section, rigid [AWG]                              | 20 ... 12 (converted acc. to IEC)           |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 1.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Flexible conductor cross-section (ferrule with plastic sleeve)    | 1.5 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |

### Ex data

#### Rated data (ATEX/IECEx)

# PTV 2,5-QUATTRO-PE - Protective conductor terminal block



1079012

<https://www.phoenixcontact.com/us/products/1079012>

|                             |                             |
|-----------------------------|-----------------------------|
| Identification              | Ⓜ II 2 G Ex eb IIC Gb       |
| Operating temperature range | -60 °C ... 110 °C           |
| Ex-certified accessories    | 1088748 D-PTV 2,5/4-QUATTRO |
|                             | 1204517 SZF 1-0,6X3,5       |
|                             | 3022276 CLIPFIX 35-5        |
| output                      | (Permanent)                 |

## Ex connection data General

|                              |  |
|------------------------------|--|
| Nominal cross section        | 2.5 mm <sup>2</sup>                        |
| Rated cross section AWG      | 14   |
| Connection capacity rigid    | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
| Connection capacity AWG      | 26 ... 12                                  |
| Connection capacity flexible | 0.14 mm <sup>2</sup> ... 4 mm <sup>2</sup> |
| Connection capacity AWG      | 26 ... 12                                  |

## Dimensions

|                    |         |
|--------------------|---------|
| Width              | 5.2 mm  |
| End cover width    | 2.2 mm  |
| Height             | 69.2 mm |
| Depth              | 45.7 mm |
| Depth on NS 35/7,5 | 47.2 mm |
| Depth on NS 35/15  | 54.7 mm |

## Material specifications

|  |              |
|--|--------------|
| Color  | green-yellow |
| Flammability rating according to UL 94                           | V0           |
| Insulating material group  | I            |
| Insulating material  | PA           |
| Static insulating material application in cold                   | -60 °C       |
| Relative insulation material temperature index (Elec., UL 746 B) | 130 °C       |
| Fire protection for rail vehicles (DIN EN 45545-2) R22           | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R23           | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R24           | HL 1 - HL 3  |
| Fire protection for rail vehicles (DIN EN 45545-2) R26           | HL 1 - HL 3  |
| Surface flammability NFPA 130 (ASTM E 162)                       | passed       |
| Specific optical density of smoke NFPA 130 (ASTM E 662)          | passed       |
| Smoke gas toxicity NFPA 130 (SMP 800C)                           | passed       |

## Mechanical properties

### Mechanical data

|                 |     |
|-----------------|-----|
| Open side panel | Yes |
|-----------------|-----|

## Environmental and real-life conditions

### Oscillation/broadband noise

# PTV 2,5-QUATTRO-PE - Protective conductor terminal block



1079012

<https://www.phoenixcontact.com/us/products/1079012>

|                        |  |
|------------------------|--|
| Specification          | DIN EN 50155 (VDE 0115-200):2018-05            |
| Spectrum               | Long life test category 2, bogie-mounted       |
| Frequency              | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level              | $6.12 \text{ (m/s}^2\text{)}^2\text{/Hz}$      |
| Acceleration           | 3.12g  |
| Test duration per axis | 5 h  |
| Test directions        | X-, Y- and Z-axis                              |
| Result                 | Test passed                                    |

## Shocks

|                                |                                     |
|--------------------------------|-------------------------------------|
| Specification                  | DIN EN 50155 (VDE 0115-200):2018-05 |
| Pulse shape                    | Half-sine                           |
| Acceleration                   | 30g                                 |
| Shock duration                 | 18 ms                               |
| Number of shocks per direction | 3                                   |
| Test directions                | X-, Y- and Z-axis (pos. and neg.)   |
| Result                         | Test passed                         |

## Ambient conditions

|  |  |
|--|--|
| Ambient temperature (operation)          | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport)  | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)  |
| Ambient temperature (assembly)           | -5 °C ... 70 °C  |
| Ambient temperature (actuation)          | -5 °C ... 70 °C  |
| Permissible humidity (operation)         | 20 % ... 90 %  |
| Permissible humidity (storage/transport) | 30 % ... 70 %  |

## Standards and regulations

|                                  |               |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 60947-7-2 |
|----------------------------------|---------------|

## Mounting

|               |           |
|---------------|-----------|
| Mounting type | NS 35/7,5 |
|               | NS 35/15  |

# PTV 2,5-QUATTRO-PE - Protective conductor terminal block




1079012

<https://www.phoenixcontact.com/us/products/1079012>

## Drawings

Circuit diagram



# PTV 2,5-QUATTRO-PE - Protective conductor terminal block




1079012

<https://www.phoenixcontact.com/us/products/1079012>


## Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1079012>

|  <b>CSA</b><br>Approval ID: 158887 |                       |                       |                   |                      |
|---|-----------------------|-----------------------|-------------------|----------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| B   | -                     | -                     | 26 - 12           | -                    |
| C   | -                     | -                     | 26 - 12           | -                    |

|  <b>IECEE CB Scheme</b><br>Approval ID: DE1-67153 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  | -                     | -                     | -                 | 0.2 - 4              |

|  <b>EAC</b><br>Approval ID: RU C-DE.BL08.B.00644 |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

|  <b>cULus Recognized</b><br>Approval ID: E60425 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| B  | -                     | -                     | 26 - 12           | -                    |
| C  | -                     | -                     | 26 - 12           | -                    |
| F  | -                     | -                     | 26 - 12           | -                    |

|  <b>VDE Zeichengenehmigung</b><br>Approval ID: 40056332 |                       |                       |                   |                      |
|--|-----------------------|-----------------------|-------------------|----------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $mm^2$ |
| keine  | -                     | -                     | -                 | 0.2 - 4              |

|  <b>IECEx</b><br>Approval ID: IECExPTB20.0037U |  |  |  |  |
|---|--|--|--|--|
|---|--|--|--|--|

# PTV 2,5-QUATTRO-PE - Protective conductor terminal block



1079012

<https://www.phoenixcontact.com/us/products/1079012>



**IECEx**

Approval ID: IECExPTB20.0037U



**ATEX**

Approval ID: PTB20ATEX1016U



**CCC**

Approval ID: 2026322313007393



**UKCA-EX**

Approval ID: CSAE 22UKEX1099U



**EAC Ex**

Approval ID: KZ 7500525010101950

# PTV 2,5-QUATTRO-PE - Protective conductor terminal block



1079012

<https://www.phoenixcontact.com/us/products/1079012>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27250103 |
| ECLASS-15.0 | 27250103 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000901 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# PTV 2,5-QUATTRO-PE - Protective conductor terminal block



1079012

<https://www.phoenixcontact.com/us/products/1079012>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)