

# IOL MA8 PN DI8 - Communication module



1072838

<https://www.phoenixcontact.com/us/products/1072838>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Eight-channel IO-Link master provides convenient configuration of IO-Link devices using web-based management. Supports connectivity to PROFINET IO, MODBUS, and OPC UA. Features eight auxiliary digital inputs, redundant input power supply connections, plug-in push-in terminals.

## Product description

Provides connectivity to PROFINET, MODBUS TCP, and OPC UA networks. It enables the operation of up to eight IO-Link sensors/actuators and is also used to acquire digital signals. The device is designed for use in systems manufacturing.

## Your advantages

- Web-based management
- Eight-channel IO-Link master
- Diagnostic and status indicators
- Short-circuit and overload protection of the sensor supply
- Plug-in connection terminals, push-in connection technology
- Connections for up to 16 digital sensors

## Commercial data

Item number	1072838
Packing unit	250 pc
Minimum order quantity	1 pc
Sales key	DR04
Product key	DRI7PA
GTIN	4055626765778
Weight per piece (including packing)	372.5 g
Weight per piece (excluding packing)	226.8 g
Customs tariff number	85176200
Country of origin	US

1072838

<https://www.phoenixcontact.com/us/products/1072838>

## Technical data

### Dimensions

Width	45 mm
Height	114.5 mm
Depth	99 mm

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Material specifications

Color (Housing)	gray (RAL 7042)
Housing material	Polyamide

### Interfaces

#### PROFINET

No. of channels	2
Connection method	RJ45 jack
Transmission speed	10/100 Mbps (with auto negotiation)
Transmission physics	Ethernet in RJ45 twisted pair

#### PROFINET

Equipment type	PROFINET-Device
System-specific protocols	PROFINET protocols LLDP
	PROFINET protocols MRP client
	PROFINET protocols DCP
	DCE/RPC
Protocols supported	SNMP v1
	HTTP
	TFTP
	FTP
	BootP
	DHCP
	SSH

### Input data

#### Digital:

Input name	Digital inputs
------------	----------------

# IOL MA8 PN DI8 - Communication module



1072838

<https://www.phoenixcontact.com/us/products/1072838>

Description of the input	IEC 61131-2 type 1
Number of inputs	8
Connection method	Push-in / plug connection
Connection technology	3-conductor
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input voltage $U_{IN}$	24 V DC
Nominal input current at $U_{IN}$	typ. 3.5 mA
Input frequency	0.5 kHz
Protective circuit	Overload protection Short-circuit protection for the sensor supply

## Digital

Input name	Digital inputs
Description of the input	IO-Link ports in digital input (DI) mode
Number of inputs	max. 8 (EN 61131-2 types 1 and 3)
Connection method	Push-in / plug connection
Connection technology	3-conductor
Nominal input voltage $U_{IN}$	24 V DC
Input voltage range "0" signal	8 V DC ... 11.5 V DC (for C/Q pin)
Input voltage range "1" signal	10.5 V DC ... 13 V DC
Sensor current per channel	max. 200 mA (from L+/L-)
Total sensor current	max. 1.6 A (from L+/L-)
Protective circuit	Overload protection; yes Short-circuit protection for the sensor supply; electronic

## IO-Link

Description of the input	Digital inputs (DI)
Connection method	Push-in / plug connection
Nominal input voltage $U_{IN}$	24 V DC
Input voltage range "0" signal	5.2 V DC ... 6.4 V DC
Input voltage range "1" signal	6.8 V DC ... 8 V DC
Nominal input current	typ. 3.5 mA
Sensor current per channel	max. 200 mA (from L+/L-)
Total sensor current	max. 1.6 A (from L+/L-)
Protective circuit	Overload protection; yes Short-circuit protection for the sensor supply; yes

## IO-Link

Number of ports	8
Connection method	Push-in / plug connection
Connection technology	3-conductor
Cycle Time	min. 4 ms (IO-Link cycle time)

## Output data

# IOL MA8 PN DI8 - Communication module



1072838

<https://www.phoenixcontact.com/us/products/1072838>

## Digital:

Maximum output current per channel	200 mA
------------------------------------	--------

## Digital

Output description	IO-Link ports in digital output (DO) mode
Connection method	Push-in / plug connection
Connection technology	3-conductor
Number of outputs	max. 8
Nominal output voltage	24 V DC
Maximum output current per channel	200 mA
Maximum output current per module	1.6 A
Nominal load, ohmic	4.8 W (120 $\Omega$ , at nominal load)
Output voltage when switched off	max. 1 V
Output current when switched off	max. 400 $\mu$ A
Protective circuit	Overload protection Short-circuit protection; yes
Behavior with overload	Shutdown with automatic restart

## Product properties

Product type	I/O component
Product family	Stand-alone
Type	Stand-alone

## Electrical properties

Maximum power dissipation for nominal condition	4.4 W
---	-------

### Supply: IO-Link

Nominal voltage for I/O supply	24 V DC
Nominal current for every IO-Link port	max. 200 mA (at C/Q) max. 200 mA (at L+/L-)
Permissible cable length	< 20 m
Protective circuit	Overload protection; yes

### Potentials

Supply voltage	24 V DC
Supply voltage range	10.8 V DC ... 30 V DC
Current draw	155 mA

### Supply: Module electronics

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC
Current consumption	3.7 A

### Supply:

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 30 V DC

# IOL MA8 PN DI8 - Communication module



1072838

<https://www.phoenixcontact.com/us/products/1072838>

Current consumption	max. 3.7 A
Typical current consumption	155 mA (at 24 V DC)

## Electrical isolation/isolation of the voltage ranges

Test voltage: 24 V supply/Ethernet	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (US) / FE	500 V AC, 50 Hz, 1 min
Test voltage: Ethernet/FE	500 V AC, 50 Hz, 1 min
Test voltage: Ethernet/Ethernet	500 V AC, 50 Hz, 1 min

## Connection data

Connection method	Push-in connection
pluggable	yes
Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 14
Stripping length	10 mm

## Environmental and real-life conditions

### Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
Degree of protection	IP20
Ambient temperature (storage/transport)	-25 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 %
Permissible humidity (storage/transport)	10 % ... 95 %

### Mechanical test

Vibration resistance in accordance with EN 60068-2-6/IEC 60068-2-6	1g
--	----

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# IOL MA8 PN DI8 - Communication module



1072838

<https://www.phoenixcontact.com/us/products/1072838>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1072838>



**UL Listed**

Approval ID: E238705



**cUL Listed**

Approval ID: E238705

# IOL MA8 PN DI8 - Communication module



1072838

<https://www.phoenixcontact.com/us/products/1072838>

## Classifications

### ECLASS

ECLASS-13.0	27242608
ECLASS-15.0	27242608

### ETIM

ETIM 10.0	EC001604
-----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------

1072838

<https://www.phoenixcontact.com/us/products/1072838>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)