

DS-PTV 2,5/4-MT - Cover segment



1083620

<https://www.phoenixcontact.com/us/products/1083620>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover segment, depth: 33.1 mm, width: 0.8 mm, height: 22 mm, color: gray



Commercial data

Item number	1083620
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE2Z1X
GTIN	4055626818450
Weight per piece (including packing)	0.98 g
Weight per piece (excluding packing)	0.98 g
Country of origin	IN

DS-PTV 2,5/4-MT - Cover segment



1083620

<https://www.phoenixcontact.com/us/products/1083620>

Technical data

Product properties

Product type	End cover
--------------	-----------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

Dimensions

Width	0.8 mm
Height	22 mm
Depth	33.1 mm

DS-PTV 2,5/4-MT - Cover segment



1083620

<https://www.phoenixcontact.com/us/products/1083620>

Classifications

ECLASS

ECLASS-13.0	27250301
ECLASS-15.0	27250301

ETIM

ETIM 10.0	EC000886
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

DS-PTV 2,5/4-MT - Cover segment



1083620

<https://www.phoenixcontact.com/us/products/1083620>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com