

# SACC-M12MSL-4PL-CM SH - Power connector



1080239

<https://www.phoenixcontact.com/us/products/1080239>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Power connector, Power, 4-position, shielded, Plug straight M12, coding: L, Push-lock spring connection, knurl material: Brass, nickel-plated, external cable diameter 6 mm ... 11 mm

## Your advantages

- Time-saving Push-Lock connection: Tool-free connection and disconnection of conductors by opening the contact levers
- Intuitive connection: Easy assignment of individual litz wires with color-coded and numerical identification of the contact levers
- Integrated Push-in Technology: Wire rigid and pretreated conductors easily by means of simple, direct insertion
- Shock- and vibration-resistant connection: Proven spring-cage technology guarantees secure and reliable contacting
- Safely shielded: Reliable 360° shield connection even under extreme mechanical strain

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1080239       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF33          |
| Product key                          | AF2CFP        |
| GTIN                                 | 4055626803050 |
| Weight per piece (including packing) | 74.1 g        |
| Weight per piece (excluding packing) | 74.1 g        |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-M12MSL-4PL-CM SH - Power connector



1080239

<https://www.phoenixcontact.com/us/products/1080239>

## Technical data

### Notes

|               |   |
|---------------|---|
| Assembly note | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties. |
|---------------|---|

### Mounting

|               |  |
|---------------|--|
| Assembly note | The wires can be connected both with ferrules and without ferrules |
|---------------|--|


### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Application          | Energy supply                   |
| Sensor type          | Power                           |
| Number of positions  | 4                               |
| No. of cable outlets | 1                               |
| Shielded             | yes                             |
| Coding               | L                               |
| Cable outlet         | straight                        |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Dimensions

|                     |  |
|---------------------|--|
| Dimensional drawing |  |
| Length              | 70 mm  |

### External dimensions

|                  |                |
|------------------|----------------|
| Outside diameter | 6 mm ... 11 mm |
|------------------|----------------|

### Housing

|                  |       |
|------------------|-------|
| Diameter housing | 23 mm |
|------------------|-------|

### Material specifications

|  |                      |
|--|----------------------|
| Flammability rating according to UL 94 | V0                   |
| Material of grip body                  | Brass, nickel-plated |
| Contact surface material               | Au                   |
| Material for screw connection          | Brass, nickel-plated |

# SACC-M12MSL-4PL-CM SH - Power connector



1080239

<https://www.phoenixcontact.com/us/products/1080239>

## Connection data

### Conductor connection

|   |   |
|---|---|
| Connection method                       | Push-lock spring connection                                 |
| Connection cross section                | 2.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>                 |
|   | 0.75 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> (with ferrule) |
|   | 1.5 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> (solid)         |
| Connection cross section AWG            | 16 ... 14 (without ferrule)                                 |
|   | 18 ... 14 (with ferrule)                                    |
| Stripping length of the individual wire | 10 mm   |
| Tightening torque                       | 0.6 Nm (M12 knurl)  |
|   | 5 Nm (Pressure nut with connector housing)                  |

### Connection assignment

|   |        |
|---|--------|
| Contact   Color (signal designation)   Contact (optional) | 1 = BN |
|   | 2 = WH |
|   | 3 = BU |
|   | 4 = BK |

## Electrical properties

|                                |  |
|--------------------------------|--|
| Rated surge voltage            | 1.5 kV   |
| Nominal voltage U <sub>N</sub> | 63 V DC  |
| Nominal current I <sub>N</sub> | 16 A (when using 2.5 mm <sup>2</sup> conductors) |
|                                | 16 A (at 40 °C)                                  |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Plug     |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Coding            | L        |

## Cable/line

|   |       |
|---|-------|
| Signal type/category                    | Power |
| Stripping length of the individual wire | 10 mm |

## Environmental and real-life conditions

### Ambient conditions

|                      |      |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|

# SACC-M12MSL-4PL-CM SH - Power connector



1080239

<https://www.phoenixcontact.com/us/products/1080239>

|   |                                  |
|---|----------------------------------|
| Ambient temperature (operation) (male connector/female connector) | -40 °C ... 85 °C (Plug / socket) |
| Ambient temperature (assembly)                                    | -5 °C ... 50 °C (Plug / socket)  |

## Standards and regulations

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 connector                |
| Standards/specifications | according to IEC 61076-2-111 |


# SACC-M12MSL-4PL-CM SH - Power connector

1080239

<https://www.phoenixcontact.com/us/products/1080239>


## Drawings

Dimensional drawing



Plug, M12 x 1, straight, shielded

Functional drawing




# SACC-M12MSL-4PL-CM SH - Power connector

1080239

<https://www.phoenixcontact.com/us/products/1080239>



Schematic diagram



Pin assignment of M12 connector, 4-pos., L-coded, pin side view

# SACC-M12MSL-4PL-CM SH - Power connector



1080239

<https://www.phoenixcontact.com/us/products/1080239>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
| ECLASS-15.0 | 27440116 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002635 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-M12MSL-4PL-CM SH - Power connector



1080239

<https://www.phoenixcontact.com/us/products/1080239>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)