

# NBC-M12MSX/1,0-94F/M12MRX - Network cable



1080724

<https://www.phoenixcontact.com/us/products/1080724>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Network cable, Ethernet CAT6<sub>A</sub> (10 Gbps) CAT6<sub>A</sub> (10 Gbps), 8-position, PUR halogen-free, water blue RAL 5021, shielded (Advanced Shielding Technology), Plug straight M12, coding: X / IP67, on Plug angled M12, coding: X / IP67, cable length: 1 m

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1080724       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BF04          |
| Product key                          | AF1CMJ        |
| GTIN                                 | 4055626805696 |
| Weight per piece (including packing) | 93.1 g        |
| Weight per piece (excluding packing) | 91 g          |
| Customs tariff number                | 85444290      |
| Country of origin                    | PL            |

1080724

<https://www.phoenixcontact.com/us/products/1080724>

## Technical data

### Product properties

|                      |                         |
|----------------------|-------------------------|
| Product type         | Data cable preassembled |
| Application          | Standard                |
| Number of positions  | 8                       |
| No. of cable outlets | 1                       |
| Shielded             | yes                     |
| Coding               | X                       |

### Interfaces

|                      |                                      |
|----------------------|--------------------------------------|
| Bus system           | Ethernet                             |
| Signal type/category | Ethernet CAT6 <sub>A</sub> , 10 Gbps |

### Signaling


|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Electrical properties

|   |                   |
|---|-------------------|
| Nominal voltage $U_N$                   | 48 V AC           |
|   | 60 V DC           |
| Nominal current $I_N$                   | 0.5 A             |
| Transmission medium                     | Copper            |
| Transmission speed                      | 10 Gbps           |
| Transmission characteristics (category) | CAT6 <sub>A</sub> |

### Connector

#### Connection 1

|                             |  |
|-----------------------------|--|
| Dimensional drawing         |  <p>Pin assignment of M12 plug, 8-pos., X-coded, pin side view</p> |
| Type                        | M12 Plug, straight, 8-position, shielded (Advanced Shielding Technology), Keying: X  |
| Number of positions         | 8  |
| Shielded                    | yes  |
| Shielding                   | Advanced Shielding Technology  |
| Signal type/category        | Ethernet CAT6 <sub>A</sub> , 10 Gbps<br>CC-Link IE CAT6 <sub>A</sub> , 10 Gbps   |
| Insertion/withdrawal cycles | ≥ 100  |

# NBC-M12MSX/1,0-94F/M12MRX - Network cable




1080724

<https://www.phoenixcontact.com/us/products/1080724>

|  |   |
|--|---|
| Insulation resistance                  | ≥ 100 Ω                                     |
| Overvoltage category                   | II  |
| Degree of pollution                    | 3   |
| Tightening torque                      | 0.4 Nm (M12 connector)                      |
| Material Contact                       | CuZn  |
| Material Contact surface               | Ni/Au                                       |
| Material Contact carrier               | PA 6.6                                      |
| Material Screw connection              | Die-cast zinc, nickel-plated                |
| Material Grip body                     | TPU, hardly inflammable, self-extinguishing |
| Material Seal                          | FKM   |
| Flammability rating according to UL 94 | V0  |
| Degree of protection                   | IP65<br>IP67                                |
| Ambient temperature (operation)        | -25 °C ... 85 °C                            |
| Standard designation                   | M12 connector                               |
| Standards/regulations                  | IEC 61076-2-109                             |

## Connection 2

|  |  |
|--|--|
| Dimensional drawing                    |  <p>Pin assignment of M12 plug, 8-pos., X-coded, pin side view</p> |
| Type                                   | M12 Plug, angled, 8-position, shielded (Advanced Shielding Technology), Keying: X  |
| Number of positions                    | 8  |
| Shielded                               | yes  |
| Shielding                              | Advanced Shielding Technology  |
| Signal type/category                   | Ethernet CAT6 <sub>A</sub> , 10 Gbps<br>CC-Link IE CAT6 <sub>A</sub> , 10 Gbps   |
| Insertion/withdrawal cycles            | ≥ 100  |
| Insulation resistance                  | ≥ 100 Ω  |
| Overvoltage category                   | II   |
| Degree of pollution                    | 3  |
| Tightening torque                      | 0.4 Nm (M12 connector)   |
| Material Contact                       | CuZn   |
| Material Contact surface               | Ni/Au  |
| Material Contact carrier               | PA 6.6   |
| Material Screw connection              | Die-cast zinc, nickel-plated   |
| Material Grip body                     | TPU, hardly inflammable, self-extinguishing  |
| Material Seal                          | FKM  |
| Flammability rating according to UL 94 | V0   |
| Degree of protection                   | IP65   |

# NBC-M12MSX/1,0-94F/M12MRX - Network cable



1080724

<https://www.phoenixcontact.com/us/products/1080724>

|                                 |                  |
|---------------------------------|------------------|
|                                 | IP67             |
| Ambient temperature (operation) | -25 °C ... 85 °C |
| Standard designation            | M12 connector    |
| Standards/regulations           | IEC 61076-2-109  |

## Cable/line

|              |     |
|--------------|-----|
| Cable length | 1 m |
|--------------|-----|

### Ethernet 10 Gbit [94F]

|   |  |
|---|--|
| Dimensional drawing                           |  |
| UL AWM Style                                  | 21238 (80 °C / 600 V)  |
| Number of positions                           | 8  |
| Shielded                                      | yes  |
| Cable type                                    | Ethernet 10 Gbit [94F]   |
| Conductor structure                           | 4x2xAWG26/7; S/FTP   |
| AWG signal line                               | 26   |
| Conductor cross-section                       | 4x 2x 0.14 mm <sup>2</sup>   |
| Wire diameter incl. insulation                | 1 mm ±0.05 mm  |
| External cable diameter                       | 6.40 mm ±0.2 mm  |
| Outer sheath, material                        | PUR  |
| External sheath, color                        | water blue RAL 5021  |
| Conductor material                            | Bare Cu litz wires   |
| Material wire insulation                      | Foamed PE  |
| Single wire, color                            | white/blue-blue, white/orange-orange, white/green-green, white/brown-brown         |
| Twisted pairs                                 | 2 cores to the pair  |
| Overall twist                                 | 4 pairs for core   |
| Optical shield covering                       | 70 %   |
| Insulation resistance                         | ≥ 500 MΩ*km  |
| Loop resistance                               | ≤ 290.00 Ω/km  |
| Wave impedance                                | 100 Ω ±5 Ω (at 100 MHz)  |
| Nominal voltage, cable                        | ≤ 100 V  |
| Test voltage Core/Core                        | 2000 V (50 Hz, 1 min.)   |
| Test voltage Core/Shield                      | 2000.00 V (50 Hz, 1 min.)  |
| Minimum bending radius, fixed installation    | 4 x D  |
| Minimum bending radius, flexible installation | 8 x D  |
| Smallest bending radius, fixed installation   | 26 mm  |

# NBC-M12MSX/1,0-94F/M12MRX - Network cable



1080724

<https://www.phoenixcontact.com/us/products/1080724>

|   |   |
|---|---|
| Smallest bending radius, movable installation | 51 mm   |
| Halogen-free                                  | according to IEC 60754-1                        |
| Flame resistance                              | according to IEC 60332-1-2                      |
|   | in accordance with UN ECE-R 118.03              |
|   | according to CSA C 22.2 No. 210-FT1             |
| Resistance to oil                             | in accordance with DIN EN 60811-404             |
| Ambient temperature (operation)               | -40 °C ... 80 °C (cable, fixed installation)    |
|   | -20 °C ... 80 °C (Cable, flexible installation) |

## Environmental and real-life conditions

### Ambient conditions

|                      |           |
|----------------------|-----------|
| Degree of protection | IP65      |
|                      | IP67      |
|                      | IP65/IP67 |

## Standards and regulations

### M12

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M12 connector   |
| Standards/specifications | IEC 61076-2-109 |

# NBC-M12MSX/1,0-94F/M12MRX - Network cable





1080724

<https://www.phoenixcontact.com/us/products/1080724>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1080724>

|  <b>UL Listed</b><br>Approval ID: FILE E 335024 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 30 V                  | 0.5 A                 | -                 | -                           |

|  <b>cUL Listed</b><br>Approval ID: FILE E 335024 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 30 V                  | 0.5 A                 | -                 | -                           |

# NBC-M12MSX/1,0-94F/M12MRX - Network cable



1080724

<https://www.phoenixcontact.com/us/products/1080724>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

# NBC-M12MSX/1,0-94F/M12MRX - Network cable



1080724

<https://www.phoenixcontact.com/us/products/1080724>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 2.195 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)