

FOC-SB-FR19:1U-LCD24-OS2 BK - Splice box



1080812

<https://www.phoenixcontact.com/us/products/1080812>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Splice box, design: 1RU, degree of protection: IP20, material: Metal, connection method: Splicing, color: black, Ethernet



The figure shows the version in gray

Product description

19" FDX 20 series splice boxes, 1 RU, with removable drawer, for 24x LC duplex OS2, black, completely ready to splice (correctly pre-mounted: 24 couplings, 48 pigtails, 4 cassettes, 4 combs, 1 cassette cover).

Your advantages

- Intuitive front-panel operation and clear control cabinet layout thanks to uniform design
- For easy field connection
- Exceptional fiber quality for reliable data transmission
- Continuously reliable data connection, thanks to extensively tested components

Commercial data

Item number	1080812
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	ABNGBA
GTIN	4055626805566
Weight per piece (including packing)	2,873.9 g
Weight per piece (excluding packing)	2,873.9 g
Country of origin	DE

1080812

<https://www.phoenixcontact.com/us/products/1080812>

Technical data

Product properties

Product type	Network distributor box
Housing type	Component housing
Series	FDX 20 series
Type	19" rack patch module
Sensor type	Ethernet
Connection profile	LC-Duplex
No. of cable outlets	4
No. of conductors	48
Number of module slots	24
Number of slots	48
Protective cover	yes

Electrical properties

Attenuation	≤ 0.3 dB
Transmission medium	FO

Connection data

Connection technology	
Connection method	Splicing

Interfaces

Signal type/category	Ethernet
----------------------	----------

Dimensions

Width	483 mm
Height	44.45 mm
Depth	241.5 mm

Mechanical characteristics

Ferrule diameter	1.25 mm
------------------	---------

Material specifications

Color	black
Flammability rating according to UL 94	V0
Ferrule material	Zirconia ceramics
Housing material	Metal
Housing surface material	Powder-coated, black

Cable/line

Cable type	Fiberglass
Cable type	Loose Tube

FOC-SB-FR19:1U-LCD24-OS2 BK - Splice box



1080812

<https://www.phoenixcontact.com/us/products/1080812>

Cable structure	semi-loose compact wires (STB)
Signal type/category	Ethernet
External cable diameter	6 mm ... 12 mm
Individual wire diameter	900 µm (250/900 µm)
Single wire, color	color coded

FO cable

Number of fibers	48
Fiber	GOF
Fiber type	Single mode fiberglass, 9/125 µm
Attenuation	≤ 0.3 dB (at 1310 nm / 1550 nm)
Return Loss	≥ 50 dB (at 1310 nm / 1550 nm)
Transmission medium	FO

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	min. 1000
Smallest bending radius	30 mm

Characteristics

Attenuation	≤ 0.3 dB
-------------	----------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
----------------------	------

Mounting

Mounting type	19" rack mounting
---------------	-------------------

1080812

<https://www.phoenixcontact.com/us/products/1080812>

Classifications

ECLASS

ECLASS-13.0	19170113
ECLASS-15.0	19170113

ETIM

ETIM 10.0	EC002699
-----------	----------

UNSPSC

UNSPSC 21.0	43223300
-------------	----------

1080812

<https://www.phoenixcontact.com/us/products/1080812>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	28.208 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com