

FL SWITCH 1005N-2SFX - Industrial Ethernet Switch



1085176

<https://www.phoenixcontact.com/us/products/1085176>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Unmanaged Switch 1000 series, 5 RJ45 ports 10/100 Mbps, 2 SFP ports 100 Mbps, degree of protection: IP30, Ambient temperature (operation): -10 °C ... 60 °C, Supply voltage range: 9 V DC ... 32 V DC, PROFINET Conformance Class A

Your advantages

- RJ45 ports support a transmission speed of 10/100 Mbps
- QoS-prioritized (Quality of Service) messages
- Local diagnostic indicators with LEDs
- PROFINET PTCP filter for reliable communication on PROFINET networks
- Enhanced traffic prioritization for automation protocols
- Energy-efficient Ethernet in accord. with IEEE 802.3az
- PROFINET conformance Class A for real-time data exchange, alarms, and diagnostics
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1085176 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN20 |
| Product key | DNN116 |
| GTIN | 4055626834832 |
| Weight per piece (including packing) | 258.75 g |
| Weight per piece (excluding packing) | 173 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SWITCH 1005N-2SFX - Industrial Ethernet Switch



1085176

<https://www.phoenixcontact.com/us/products/1085176>

Technical data

Dimensions

| | |
|--------|----------|
| Width | 22.5 mm |
| Height | 140.4 mm |
| Depth | 92.4 mm |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Utilization restriction

| | |
|----------|---|
| EMC note | EMC: class A product, see manufacturer's declaration in the download area |
|----------|---|

Material specifications

| | |
|------------------|--------------------------------|
| Color (Housing) | gray (RAL 7042) |
| Color (Cover) | light gray (RAL 7035) |
| Housing material | Polycarbonate fiber reinforced |

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Interfaces

Ethernet (RJ45)

| | |
|-------------------------------|-----------------------------------|
| Number of interfaces | 5 |
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100 Mbps |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Data receive, link status |
| No. of channels | 5 (RJ45 ports) |
| Input buffer | 768 Kbits |
| Output buffer | 768 Kbits |

Ethernet (SFP)

| | |
|----------------------|--|
| Number of interfaces | 2 |
| Connection method | SFP |
| Transmission speed | 100 Mbps (full duplex) |
| Transmission physics | Depending on the SFP module |
| Transmission length | up to 40 km (Depending on the fiber/SFP module used) |
| Signal LEDs | Data receive, link status |
| No. of channels | 2 (SFP ports) |

FL SWITCH 1005N-2SFX - Industrial Ethernet Switch



1085176

<https://www.phoenixcontact.com/us/products/1085176>

Product properties

| | |
|----------------|---|
| Product type | Switch |
| Product family | Unmanaged Switch 1000 |
| MTTF | 107.9 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) |
| | 1346 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) |
| | 1294.8 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day)) |

Switch functions

| | |
|----------------------------------|---|
| Basic functions | Unmanaged switch |
| | Autonegotiation |
| | Store and Forward switching mode |
| PROFINET conformance class | Conformance Class A |
| MAC address table | 2k |
| Status and diagnostic indicators | LEDs: U _S , link and activity per port |
| Additional functions | 100 BASE-TX/100BASE-FX (IEEE 802.3u) |
| | Quality of Service (QoS) prioritization (IEEE 802.1p) |
| | Energy-efficient Ethernet (IEEE 802.3az) |
| | 10Base-T (IEEE 802.3) |

Security functions

| | |
|-----------------|----------------------------------|
| Basic functions | Unmanaged switch |
| | Autonegotiation |
| | Store and Forward switching mode |

Electrical properties

| | |
|---|---------------------|
| Maximum power dissipation for nominal condition | 2.79 W (at 24 V DC) |
| Transmission medium | Copper |

Supply

| | |
|-----------------------------|--|
| Supply voltage (DC) | 24 V DC |
| Supply voltage (AC) | 24 V AC (50/60 Hz) |
| Supply voltage range | 9 V DC ... 32 V DC |
| | 18 V AC ... 30 V AC (50/60 Hz) |
| Power supply connection | Via COMBICON, max. conductor cross-section 2.5 mm ² |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Max. current consumption | 310 mA (at 9 V DC) |
| Typical current consumption | 25 mA (at 24 V DC) |

Connection data

Power supply

| | |
|-------------------|---------------------------|
| Connection method | Push-in spring connection |
| pluggable | yes |

FL SWITCH 1005N-2SFX - Industrial Ethernet Switch



1085176

<https://www.phoenixcontact.com/us/products/1085176>

| | |
|---|--|
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| | 0.25 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| Stripping length | 10 mm |

Environmental and real-life conditions

Ambient conditions

| | |
|--|---|
| Degree of protection | IP30 |
| Ambient temperature (operation) | -10 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude | 2000 m (maximum) |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Shock (operation) | 30g (EN 60068-2-27) |
| Vibration (operation) | in acc. with IEC 60068-2-6: 5g, 150 Hz |
| Air pressure (operation) | 79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating) |
| Air pressure (storage/transport) | 79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating) |

Approvals

Conformity/Approvals

| | |
|------------------|--|
| UL, USA / Canada | UL 61010-1, UL 61010-2-201 Class I, Div. 2, Groups A, B, C, D, T4 Class I, Zone 2, Group IIC, T4 |
| FCC | Title 47 Part 15 Subpart B:2018 Class A |
| FCC certificate | T190905D11-C |

EMC data

| | |
|-----------------------|-------------------|
| Noise immunity | EN 61000-6-2:2019 |
| Noise emission | |
| Standards/regulations | EN_61000-6-4:2019 |

System properties

Functionality

| | |
|-----------------|----------------------------------|
| Basic functions | Unmanaged switch |
| | Autonegotiation |
| | Store and Forward switching mode |

Signaling

FL SWITCH 1005N-2SFX - Industrial Ethernet Switch



1085176

<https://www.phoenixcontact.com/us/products/1085176>

Status display

LEDs: U_S, link and activity per port

FL SWITCH 1005N-2SFX - Industrial Ethernet Switch





1085176


<https://www.phoenixcontact.com/us/products/1085176>

Approvals


To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1085176>

 **KC**
Approval ID: R-R-PCK-1085176

 **cULus Listed**
Approval ID: E238705

 **cULus Listed**
Approval ID: E140403

 **cUL Listed**
Approval ID: E196811

 **UL Listed**
Approval ID: E196811

FL SWITCH 1005N-2SFX - Industrial Ethernet Switch



1085176

<https://www.phoenixcontact.com/us/products/1085176>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170402 |
| ECLASS-15.0 | 19170402 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000734 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

1085176

<https://www.phoenixcontact.com/us/products/1085176>

Environmental product compliance

EU RoHS

| | |
|---|--------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | c8234ce2-80ae-4c90-865e-e9b8e551afaf |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 5.859 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
 586 Fulling Mill Road
 Middletown, PA 17057, United States
 (+717) 944-1300
info@phoenixcon.com