

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/us/products/1081252>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



M12 female contact carrier,
straight

Contact carrier, Ethernet, 8-position, Socket, straight, M12, X-coding, SMD reflow, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1081252 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | AB23 |
| Product key | ABQBGH |
| GTIN | 4055626808130 |
| Weight per piece (including packing) | 7.07 g |
| Weight per piece (excluding packing) | 4.011 g |
| Customs tariff number | 85366990 |
| Country of origin | DE |

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/us/products/1081252>

Technical data

Notes

| | |
|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Notes on operation | The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration. |
|--------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

Product properties

| | |
|---------------------|----------------|
| Product type | Contact insert |
| Application | Data |
| Sensor type | Ethernet |
| Number of positions | 8 |
| Seal present | no |
| Shielded | yes |
| Coding | X |
| Thread type | M12 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|-----------------------------------------|--------------------------|
| Rated surge voltage | 1.5 kV |
| Contact resistance | $\leq 3 \text{ m}\Omega$ |
| Insulation resistance | $> 100 \text{ M}\Omega$ |
| Nominal voltage U_N | 50 V AC |
| | 60 V DC |
| Nominal current I_N | 0.5 A (Data) |
| Transmission characteristics (category) | CAT6 _A |

Connection data

| | |
|-------------------|------------|
| Connection method | SMD reflow |
|-------------------|------------|

Interfaces

| | |
|----------------------|----------|
| Signal type/category | Ethernet |
|----------------------|----------|

Material specifications

| | |
|----------------------------------------|----------|
| Material Contact carrier | PA |
| Material Contact | CuZn |
| Material Contact surface | Au |
| Material Shield crossover | GD-Zn/Ni |
| Flammability rating according to UL 94 | V0 |

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/us/products/1081252>

Connector

Connection 1

| | |
|-------------------|----------|
| Head design | Socket |
| Head cable outlet | straight |
| Head thread type | M12 |
| Coding | X |

Cable/line

| | |
|----------------------|----------|
| Signal type/category | Ethernet |
|----------------------|----------|

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 100 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|-------------------------------------------------------------------|-----------------------------------------------------------------------|
| Degree of protection | IP67 (correctly plugged in and locked) |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 105 °C -55 °C ... 105 °C (without mechanical actuation) |
| UL Type Rating | Type 4 (indoor use only) |

Standards and regulations

| | |
|--------------------------|------------------------------|
| Standard designation | M12 circular connector |
| Standards/specifications | according to IEC 61076-2-109 |

Packaging specifications

| | |
|-------------------|-------------------|
| Type of packaging | Belt |
| Delivery state | with assembly pad |


SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier

1081252

<https://www.phoenixcontact.com/us/products/1081252>

Drawings

Schematic diagram



Pin assignment M12 connector, 8-pos., view socket side

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier




1081252

<https://www.phoenixcontact.com/us/products/1081252>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1081252>

|  cUL Recognized Approval ID: E335024-20120308 | | | | |
|------------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 60 V | 0.5 A | - | - |

|  UL Recognized Approval ID: E335024-20120308 | | | | |
|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 60 V | 0.5 A | - | - |

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/us/products/1081252>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440223 |
| ECLASS-15.0 | 27440223 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003557 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SACC-CI-M12FSX-8P SMD SH R32PD - Contact carrier



1081252

<https://www.phoenixcontact.com/us/products/1081252>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com