FL SWITCH 1004N-FX ST - Industrial Ethernet Switch

1085179

https://www.phoenixcontact.com/us/products/1085179

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRA-READY



Ethernet switch, four RJ45 ports, one ST fiber port

Your advantages

- RJ45 ports support a transmission speed of 10/100 Mbps
- QoS-prioritized (Quality of Service) messages
- PROFINET PTCP filter for reliable communication on PROFINET networks
- Enhanced traffic prioritization for automation protocols
- Energy-efficient Ethernet in accord. with IEEE 802.3az
- PROFINET conformance Class A for real-time data exchange, alarms, and diagnostics
- Auto negotiation and autocrossing detection simplifies installation and setup

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	1085179
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN20

Product key	DNN116
GTIN	4055626835105
Weight per piece (including packing)	216.96 g
Weight per piece (excluding packing)	134 g
Customs tariff number	85176200
Country of origin	TW

Technical data

Dimensions

Width	22.5 mm
Height	117 mm
Depth	84 mm

Notes

Note on application	Only for industrial use
Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area

Material specifications

Color (Housing)	gray (RAL 7042)
Color (Cover)	light gray (RAL 7035)
Housing material	Polycarbonate fiber reinforced

Mounting

Mounting type	DIN rail mounting

Interfaces

Ethernet (RJ45)

Number of interfaces	4
Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	4 (RJ45 ports)
Input buffer	768 Kbits
Output buffer	768 Kbits

Ethernet FO

Number of interfaces	1
Connection method	ST
Transmission speed	100 Mbps (full duplex)
Transmit capacity, minimum	-20 dBm
Transmit capacity, maximum	-14 dBm

Minimum receiver sensitivity	-32 dBm
Maximum receiver sensitivity	0 dBm
Transmission physics	multi-mode fiberglass
Transmission length	8 km (fiberglass with F-G 62.5/125 0.7 dB/km F1000)
	5.71 km (fiberglass with F-G 50/125 0.7 dB/km F1200)
Wavelength	1300 nm
No. of channels	1 (ST multi-mode)

Product properties

Product type	Switch
Product family	Unmanaged Switch 1000
MTTF	115.1 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%)
	427.5 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)
	279.5 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))
Special properties	The product is being prepared for compliance with the Cyber Resilience Act (CRA)

Switch functions

MAC address table	2k
PROFINET conformance class	Conformance Class A
Status and diagnostic indicators	LEDs: U_S, link and activity per port
Basic functions	Unmanaged switch
	Autonegotiation
	Store and Forward switching mode
Additional functions	100 BASE-TX/100BASE-FX (IEEE 802.3u)
	Quality of Service (QoS) prioritization (IEEE 802.1p)
	Energy-efficient Ethernet (IEEE 802.3az)
	10Base-T (IEEE 802.3)

Electrical properties

Maximum power dissipation for nominal condition	2.196 W (at 24 V DC)
Transmission medium	Copper
	FO

Supply

Supply voltage (DC)	24 V DC
Supply voltage (AC)	24 V AC (50/60 Hz)
Supply voltage range	9 V DC ... 32 V DC
	18 V AC ... 30 V AC (50/60 Hz)
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm²
Residual ripple	3.6 V_{PP} (within the permitted voltage range)
Max. current consumption	244 mA (at 9 V DC)
Typical current consumption	60 mA (at 24 V DC)

Ground connection	Via DIN rail

Connection data

Power supply

Connection method	Push-in spring connection
pluggable	yes
Conductor cross-section, rigid	0.2 mm² ... 2.5 mm²
Conductor cross-section, flexible	0.2 mm² ... 2.5 mm²
Conductor cross-section AWG	24 ... 12
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm² ... 2.5 mm²
Conductor cross-section, flexible, with ferrule, without plastic sleeve	0.25 mm² ... 2.5 mm²
	0.25 mm² ... 2.5 mm²
Conductor cross-section, flexible, with ferrule, with plastic sleeve	0.25 mm² ... 2.5 mm²
Stripping length	10 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP30
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	2000 m (maximum)
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock (operation)	30g (EN 60068-2-27)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)
Air pressure (storage/transport)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)

Approvals

Conformity/Approvals

UL, USA / Canada	UL 61010-1, UL 61010-2-201, UL 62368-1 Class I, Div. 2, Groups A, B, C, D, T4 Class I, Zone 2, Group IIC, T4
FCC	Title 47 Part 15 Subpart B:2018 Class A
FCC certificate	T190905D11-C

EMC data

Noise immunity	EN 61000-6-2:2019

Noise emission

Standards/regulations	EN_61000-6-4:2019

Signaling

Status display	LEDs: U_S, link and activity per port

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1085179

KC
Approval ID: R-R-PCK-1085179

cULus Listed
Approval ID: E238705

cULus Listed
Approval ID: E140403

cUL Listed
Approval ID: E196811

UL Listed
Approval ID: E196811

Classifications

ECLASS

ECLASS-13.0	19170402
ECLASS-15.0	19170402

ETIM

ETIM 10.0	EC000734

UNSPSC

UNSPSC 21.0	43222600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	baad7a33-4893-4c0f-8ccf-c9147dac659b

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com