

# HS EH-B 140,5 DCS - Holder



1082302

<https://www.phoenixcontact.com/us/products/1082302>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



140.5 mm housing attachment, for max. load 10 kg, with ball joint and fastening plate 60 mm, pivotable in 15° increments, for 30 mm wall/profile bracket, material: black glass-fiber reinforced polycarbonate PC, and black anodized aluminum, 342 g

## Your advantages

- Secure mounting of small and large monitors and operator interfaces, thanks to the high load-bearing capacity
- Can be swiveled and tilted in three axes for optimum alignment with the field of view
- VESA interface in standard VESA 75 and VESA 100 for easy wall or aluminum profile mounting
- Item belongs to the DCS product range

## Commercial data

Item number	1082302
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC02
Product key	ACFBAZ
GTIN	4055626812748
Weight per piece (including packing)	342.8 g
Weight per piece (excluding packing)	342 g
Customs tariff number	39269097
Country of origin	DE

# HS EH-B 140,5 DCS - Holder

1082302

<https://www.phoenixcontact.com/us/products/1082302>



## Technical data

### Product properties

Product type	Mounting material
Housing type	Housing bracket
Housing series	DCS
Product family	DCS

# HS EH-B 140,5 DCS - Holder



1082302

<https://www.phoenixcontact.com/us/products/1082302>

## Classifications

### ECLASS

ECLASS-13.0	27190605
ECLASS-15.0	27190605

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# HS EH-B 140,5 DCS - Holder



1082302

<https://www.phoenixcontact.com/us/products/1082302>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)