

HS EH-B 140,5 DCS - Holder

1082302

<https://www.phoenixcontact.com/us/products/1082302>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



140.5 mm housing attachment, for max. load 10 kg, with ball joint and fastening plate 60 mm, pivotable in 15° increments, for 30 mm wall/profile bracket, material: black glass-fiber reinforced polycarbonate PC, and black anodized aluminum, 342 g

Your advantages

- Secure mounting of small and large monitors and operator interfaces, thanks to the high load-bearing capacity
- Can be swiveled and tilted in three axes for optimum alignment with the field of view
- VESA interface in standard VESA 75 and VESA 100 for easy wall or aluminum profile mounting
- Item belongs to the DCS product range

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1082302 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AC02 |
| Product key | ACFBAZ |
| GTIN | 4055626812748 |
| Weight per piece (including packing) | 342.8 g |
| Weight per piece (excluding packing) | 342 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

HS EH-B 140,5 DCS - Holder

1082302

<https://www.phoenixcontact.com/us/products/1082302>



Technical data

Product properties

| | |
|----------------|-------------------|
| Product type | Mounting material |
| Housing type | Housing bracket |
| Housing series | DCS |
| Product family | DCS |

HS EH-B 140,5 DCS - Holder



1082302

<https://www.phoenixcontact.com/us/products/1082302>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27190605 |
| ECLASS-15.0 | 27190605 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

HS EH-B 140,5 DCS - Holder



1082302

<https://www.phoenixcontact.com/us/products/1082302>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com