

# THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The THERMOMARK ROLL 2.0 thermal transfer printer prints markers in roll and continuous format for applications in terminal marking, wire and cable marking, and equipment and plant marking. Create high-quality printed labels, insert labels, and shrink and marking sleeves in prepunched or continuous format.

## Product description

The THERMOMARK ROLL 2.0 prints markers in roll format for top quality terminal, wire, cable, equipment, and plant marking applications. You can easily create high-quality printed labels and markers.

## Your advantages

- The THERMOMARK ROLL 2.0 prints marking material in roll format. For applications in terminal, wire, cable, equipment, and plant marking
- Printing of punched and continuous adhesive labels, insert labels, and shrink sleeves
- Fast, high-quality, and durable printing
- Easy and intuitive operation via touch color display
- Maintenance-free operation with proven thermal transfer printer technology
- Easy to control with the PROJECT COMPLETE software
- USB and Ethernet connections

## Commercial data

Item number	1085260
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221
GTIN	4055626834764
Weight per piece (including packing)	6,370 g
Weight per piece (excluding packing)	6,289 g
Customs tariff number	84433210
Country of origin	DE

# THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

## Technical data

### Product properties

Product type	Marking system
Scope of supply	Thermal transfer printer for roll material, incl. European/US power cable and USB cable. Manual printed in German and English. One packing unit EML (20X8)R/TL each and one THERMOMARK RIBBON 110/50 ink ribbon

### Marking

Identification technology	Thermotransfer
---------------------------	----------------

### Device properties

Print width	105 mm
Print resolution	300 dpi
Operating system	Windows 10, Windows 11, Windows Server 2016, Windows Server 2019, Windows Server 2022

### Electrical properties

#### Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)
----------------------	---

### Dimensions

Width	240 mm
Height	189 mm
Depth	320 mm
Length	320 mm

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	10 °C ... 35 °C
---------------------------------	-----------------

# THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1085260>



**EAC**

Approval ID: KZ 27978



**KC**

Approval ID: R-R-YG3-TR20



**EAC-RoHS**

Approval ID: RU D-DE.HB49.B.00023

**UAE-RoHS**

Approval ID: 13537\_E22-04-033555



**cULus Listed**

Approval ID: E140403



**cULus Listed**

Approval ID: E140403

# THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

## Classifications

### ECLASS

ECLASS-13.0	19140104
ECLASS-15.0	19140104

### ETIM

ETIM 10.0	EC001684
-----------	----------

### UNSPSC

UNSPSC 21.0	43212100
-------------	----------

# THERMOMARK ROLL 2.0 - Thermal transfer printer



1085260

<https://www.phoenixcontact.com/us/products/1085260>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	56594a1c-6e7d-4686-b665-e4de105ce09d

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)