

UBAL 50 GN - High-current terminal block



1086468

<https://www.phoenixcontact.com/us/products/1086468>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



High-current terminal block, nom. voltage: 1000 V, nominal current: 145 A, number of connections: 2, number of positions: 1, connection method: Screw connection, Rated cross section: 50 mm², cross section: 6 mm² - 50 mm², Rated cross section: 50 mm², cross section: 4 mm² - 50 mm², mounting type: NS 35/15, NS 35/7,5, color: green

Your advantages

- Maintenance-free terminal points that are greased beforehand simplify the connection of aluminum conductors
- Tailor-made screw connection for multi-stranded aluminum conductors and copper wires
- Extremely robust housing made from fiberglass-reinforced polyamide with V0 approval
- The special design of the UBAL enables the simultaneous connection of aluminum and copper conductors in various connections

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1086468 |
| Packing unit | 20 pc |
| Minimum order quantity | 20 pc |
| Sales key | BE13 |
| Product key | BE1311 |
| GTIN | 4055626877952 |
| Weight per piece (including packing) | 48.862 g |
| Weight per piece (excluding packing) | 45.65 g |
| Customs tariff number | 85369010 |
| Country of origin | EE |

UBAL 50 GN - High-current terminal block



1086468

<https://www.phoenixcontact.com/us/products/1086468>

Technical data

Notes

General

| | |
|------|--|
| Note | We recommend using ferrules when using flexible conductor. |
|------|--|

Product properties

| | |
|-----------------------|-----------------------------|
| Product type | Feed-through terminal block |
| Product family | UBAL |
| Number of positions | 1 |
| Number of connections | 2 |
| Number of rows | 1 |
| Potentials | 1 |

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 3 |

Electrical properties

| | |
|---|--------|
| Rated surge voltage | 8 kV |
| Maximum power dissipation for nominal condition | 4.73 W |

Connection data

| | |
|-----------------------|--------------------|
| Nominal cross section | 50 mm ² |
|-----------------------|--------------------|

Aluminum conductor

| | |
|----------------------------------|---|
| Connection method | Screw connection |
| Screw thread | M10 |
| Note | Screws with hexagonal socket The following values apply to aluminum conductors The values for aluminum conductors relate to rigid and multi-stranded conductors in accordance with EN 60228. Application notes on connecting aluminum conductors can be found in the download area. |
| Tightening torque | 12 Nm |
| Stripping length | 23 mm |
| Connection in acc. with standard | IEC 61238-1 |
| Conductor cross-section rigid | 6 mm ² ... 50 mm ² |
| Cross section AWG | 6 ... 1/0 (converted acc. to IEC) |
| Nominal cross section | 50 mm ² |
| Nominal current | 145 A |
| Maximum load current | 145 A (with 50 mm ² conductor cross-section – test current in accordance with IEC 61238-1) |
| Nominal voltage | 1000 V |

Copper conductor

UBAL 50 GN - High-current terminal block



1086468

<https://www.phoenixcontact.com/us/products/1086468>

| | |
|---|--|
| Note | The following values apply to copper wires |
| | Flexible conductors, class 5, in accordance with EN 60228. |
| Tightening torque | 4 ... 12 Nm |
| Stripping length | 23 mm |
| Connection in acc. with standard | IEC 60947-7-1 |
| Conductor cross-section rigid | 4 mm ² ... 50 mm ² |
| Cross section AWG | 6 ... 1/0 (converted acc. to IEC) |
| Conductor cross-section flexible | 2.5 mm ² ... 35 mm ² |
| Conductor cross-section flexible (ferrule without plastic sleeve) | 2.5 mm ² ... 35 mm ² |
| Flexible conductor cross-section (ferrule with plastic sleeve) | 2.5 mm ² ... 35 mm ² |
| 2 conductors with same cross section, flexible | 2.5 mm ² ... 16 mm ² |
| Nominal cross section | 50 mm ² |
| Nominal current | 150 A |
| Maximum load current | 150 A (with 50 mm ² conductor cross-section) |
| Nominal voltage | 1000 V |

Dimensions

| | |
|--------------------|---------|
| Width | 19.2 mm |
| Height | 82.5 mm |
| Depth | 51 mm |
| Depth on NS 35/7,5 | 51 mm |
| Depth on NS 35/15 | 58.5 mm |
| Hole diameter | 2.75 mm |

Material specifications

| | |
|--|------------------|
| Color | green (RAL 6021) |
| Flammability rating according to UL 94 | V0 |
| Insulating material group | II |
| Insulating material | PA |
| Relative insulation material temperature index (Elec., UL 746 B) | 400 °C |

Electrical tests

Surge voltage test

| | |
|-----------------------|-------------|
| Test voltage setpoint | 8 kV |
| Result | Test passed |

Temperature-rise test

| | |
|---|--------------------------------|
| Requirement temperature-rise test | Increase in temperature ≤ 45 K |
| Result | Test passed |
| Short-time withstand current 50 mm ² | 6 kA |
| Result | Test passed |

Power-frequency withstand voltage

| | |
|-----------------------|-------------|
| Test voltage setpoint | 2.2 kV |
| Result | Test passed |

1086468

<https://www.phoenixcontact.com/us/products/1086468>

Mechanical properties

Mechanical data

| | |
|-----------------|----|
| Open side panel | No |
|-----------------|----|

Mechanical tests

Mechanical strength

| | |
|--------|-------------|
| Result | Test passed |
|--------|-------------|

Attachment on the carrier

| | |
|-------------------------|-------------|
| DIN rail/fixing support | NS 35 |
| Test force setpoint | 10 N |
| Result | Test passed |

Test for conductor damage and slackening

| | |
|--------------------------------|---|
| Rotation speed | 10 rpm |
| Revolutions | 135 |
| Conductor cross-section/weight | 2.5 mm ² / 0.7 kg 50 mm ² / 9.5 kg |
| Result | Test passed |

Environmental and real-life conditions

Needle-flame test

| | |
|------------------|-------------|
| Time of exposure | 10 s |
| Result | Test passed |

Oscillation/broadband noise

| | |
|------------------------|--|
| Specification | DIN EN 50155 (VDE 0115-200):2018-05 |
| Spectrum | Long life test category 2, bogie-mounted |
| Frequency | $f_1 = 5 \text{ Hz}$ to $f_2 = 250 \text{ Hz}$ |
| ASD level | 6.12 (m/s ²) ² /Hz |
| Acceleration | 3.12g |
| Test duration per axis | 5 h |
| Test directions | X-, Y- and Z-axis |
| Result | Test passed |

Shocks

| | |
|--------------------------------|-----------------------------------|
| Pulse shape | Half-sine |
| Acceleration | 30g |
| Shock duration | 18 ms |
| Number of shocks per direction | 3 |
| Test directions | X-, Y- and Z-axis (pos. and neg.) |
| Result | Test passed |

Ambient conditions

UBAL 50 GN - High-current terminal block



1086468

<https://www.phoenixcontact.com/us/products/1086468>

| | |
|--|--|
| Ambient temperature (operation) | -60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.) |
| Ambient temperature (storage/transport) | -25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C) |
| Ambient temperature (assembly) | -5 °C ... 70 °C |
| Ambient temperature (actuation) | -5 °C ... 70 °C |
| Permissible humidity (operation) | 20 % ... 90 % |
| Permissible humidity (storage/transport) | 30 % ... 70 % |

Standards and regulations

| | |
|----------------------------------|---------------|
| Connection in acc. with standard | IEC 61238-1 |
| | IEC 60947-7-1 |

Mounting

| | |
|---------------|-----------|
| Mounting type | NS 35/15 |
| | NS 35/7,5 |

UBAL 50 GN - High-current terminal block

1086468

<https://www.phoenixcontact.com/us/products/1086468>



Drawings

Circuit diagram



UBAL 50 GN - High-current terminal block



1086468

<https://www.phoenixcontact.com/us/products/1086468>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1086468>



EAC

Approval ID: KZ7500651131219505



UL Recognized

Approval ID: FILE E 60425

| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
|---------------|-----------------------|-----------------------|-------------------|-----------------------------|
| E | | | | |
| | 1000 V | 150 A | 6 - 1/0 | - |
| Al conductors | 1000 V | 120 A | 6 - 1/0 | - |

UBAL 50 GN - High-current terminal block



1086468

<https://www.phoenixcontact.com/us/products/1086468>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27250101 |
| ECLASS-15.0 | 27250101 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000897 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

UBAL 50 GN - High-current terminal block



1086468

<https://www.phoenixcontact.com/us/products/1086468>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.626 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com