
UBAL 95 GN - High-current terminal block

1086477

https://www.phoenixcontact.com/us/products/1086477

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.





High-current terminal block, nom. voltage: 1000 V, nominal current: 220 A, number of connections: 2, number of positions: 1, connection method: Screw connection, Rated cross section: 95 mm^2, cross section: 16 mm^2 - 95 mm^2, Rated cross section: 95 mm^2, cross section: 16 mm^2 - 95 mm^2, mounting type: NS 35/15, NS 35/7,5, color: green

Your advantages

- Maintenance-free terminal points that are greased beforehand simplify the connection of aluminum conductors
- Tailor-made screw connection for multi-stranded aluminum conductors and copper wires
- Extremely robust housing made from fiberglass-reinforced polyamide with V0 approval
- The special design of the UBAL enables the simultaneous connection of aluminum and copper conductors in various connections

Commercial data

Item number	1086477
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE13
Product key	BE1311
GTIN	4055626878287
Weight per piece (including packing)	97.14 g
Weight per piece (excluding packing)	97.07 g
Customs tariff number	85369010
Country of origin	EE

Technical data

Notes

General	Terminal block for aluminum and copper conductors (AL-CU)

General

Note	We recommend using ferrules when using flexible donductor.

Product properties

Product type	High current terminal block
Product family	UBAL
Number of positions	1
Number of connections	2
Number of rows	1
Potentials	1

Insulation characteristics

Overvoltage category	III
Degree of pollution	3

Electrical properties

Rated surge voltage	8 kV
Maximum power dissipation for nominal condition	7.54 W

Connection data

Nominal cross section	95 mm²

Aluminum conductor

Connection method	Screw connection
Screw thread	M14
Note	Screws with hexagonal socket
	The following values apply to aluminum conductors
	The values for aluminum conductors relate to rigid and multi-stranded conductors in accordance with EN 60228. Application notes on connecting aluminum conductors can be found in the download area.
Tightening torque	20 Nm
Stripping length	27 mm
Connection in acc. with standard	IEC 61238-1
Conductor cross-section rigid	16 mm² ... 95 mm²
Cross section AWG	4 ... 4/0 (converted acc. to IEC)
Nominal cross section	95 mm²
Nominal current	220 A
Maximum load current	220 A (with 95 mm² conductor cross-section – test current in accordance with IEC 61238-1)
Nominal voltage	1000 V

Copper conductor

Note	The following values apply to copper wires
	Flexible conductors, class 5, in accordance with EN 60228.
Tightening torque	20 Nm
Stripping length	27 mm
Connection in acc. with standard	IEC 60947-7-1
Conductor cross-section rigid	16 mm² ... 95 mm²
Cross section AWG	4 ... 4/0 (converted acc. to IEC)
Conductor cross-section flexible	50 mm² ... 70 mm²
Conductor cross-section flexible (ferrule without plastic sleeve)	16 mm² ... 70 mm²
Flexible conductor cross-section (ferrule with plastic sleeve)	16 mm² ... 70 mm²
2 conductors with same cross section, flexible	16 mm² ... 35 mm²
Nominal cross section	95 mm²
Nominal current	232 A
Maximum load current	232 A (with 95 mm² conductor cross-section)
Nominal voltage	1000 V

Dimensions

Width	25.1 mm
Height	93.6 mm
Depth	58 mm
Depth on NS 35/7,5	58 mm
Depth on NS 35/15	65.5 mm
Hole diameter	2.75 mm

Material specifications

Color	green (RAL 6021)
Flammability rating according to UL 94	V0
Insulating material group	II
Insulating material	PA
Relative insulation material temperature index (Elec., UL 746 B)	400 °C

Electrical tests

Surge voltage test

Test voltage setpoint	8 kV
Result	Test passed

Temperature-rise test

Requirement temperature-rise test	Increase in temperature ≤ 45 K
Result	Test passed
Short-time withstand current 95 mm²	11.4 kA
Result	Test passed

Power-frequency withstand voltage

Test voltage setpoint	2.2 kV
Result	Test passed

Mechanical properties

Mechanical data

Open side panel	No

Mechanical tests

Mechanical strength

Result	Test passed

Attachment on the carrier

DIN rail/fixing support	NS 35
Test force setpoint	15 N
Result	Test passed

Test for conductor damage and slackening

Rotation speed	10 rpm
Revolutions	135
Conductor cross-section/weight	16 mm² / 2.9 kg
	95 mm²/14 kg
Result	Test passed

Environmental and real-life conditions

Needle-flame test

Time of exposure	10 s
Result	Test passed

Oscillation/broadband noise

Specification	DIN EN 50155 (VDE 0115-200):2018-05
Spectrum	Long life test category 2, bogie-mounted
Frequency	f_1 = 5 Hz to f_2 = 250 Hz
ASD level	6.12 $(m/s^2)^2/Hz$
Acceleration	3.12g
Test duration per axis	5 h
Test directions	X-, Y- and Z-axis
Result	Test passed

Shocks

Pulse shape	Half-sine
Acceleration	30g
Shock duration	18 ms
Number of shocks per direction	3
Test directions	X-, Y- and Z-axis (pos. and neg.)

Ambient conditions

Ambient temperature (operation)	-60 °C ... 110 °C (Operating temperature range incl. self-heating; for max. short-term operating temperature, see RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (operation)	20 % ... 90 %
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Connection in acc. with standard	IEC 61238-1
	IEC 60947-7-1

Mounting

Mounting type	NS 35/15
	NS 35/7,5

Drawings

Circuit diagram



Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1086477

EAC
Approval ID: KZ7500651131219505

UL Recognized
Approval ID: FILE E 60425

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
E				
	1000 V	230 A	4 - 4/0	-
Al conductors	1000 V	180 A	4 - 4/0	-

Classifications

ECLASS

ECLASS-13.0	27250101
ECLASS-15.0	27250101

ETIM

ETIM 10.0	EC000897

UNSPSC

UNSPSC 21.0	39121400

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	1.044 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com