

FL SWITCH 1108N - Industrial Ethernet Switch



1085243

<https://www.phoenixcontact.com/us/products/1085243>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Narrow Ethernet switch, eight RJ45 ports with 10/100/1000 Mbps on all ports, automatic data transmission speed detection, autocrossing function, and QoS

Your advantages

- QoS-prioritized (Quality of Service) messages
- RJ45 ports support a transmission speed of 10/100/1000 Mbps
- Jumbo frame support (frame size up to 9216 bytes/frame)
- Local diagnostic indicators with LEDs
- Enhanced traffic prioritization for automation protocols
- PROFINET PTCP filter for reliable communication on PROFINET networks
- Energy-efficient Ethernet in accord. with IEEE 802.3az
- PROFINET Conformance Class A for real-time data exchange
- Auto negotiation and autocrossing detection simplifies installation and setup

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1085243 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | DN20 |
| Product key | DNN116 |
| GTIN | 4055626835013 |
| Weight per piece (including packing) | 259 g |
| Weight per piece (excluding packing) | 179 g |
| Customs tariff number | 85176200 |
| Country of origin | TW |

FL SWITCH 1108N - Industrial Ethernet Switch



1085243

<https://www.phoenixcontact.com/us/products/1085243>

Technical data

Dimensions

| | |
|--------|----------|
| Width | 22.5 mm |
| Height | 140.4 mm |
| Depth | 92.4 mm |

Notes

Note on application

| | |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

Material specifications

| | |
|------------------|--------------------------------|
| Housing material | Polycarbonate fiber reinforced |
|------------------|--------------------------------|

Mounting

| | |
|---------------|-------------------|
| Mounting type | DIN rail mounting |
|---------------|-------------------|

Interfaces

Ethernet (RJ45)

| | |
|-------------------------------|-----------------------------------|
| Number of interfaces | 8 |
| Connection method | RJ45 |
| Note on the connection method | Auto negotiation and autocrossing |
| Transmission speed | 10/100/1000 Mbps |
| Transmission physics | Ethernet in RJ45 twisted pair |
| Transmission length | 100 m (per segment) |
| Signal LEDs | Data receive, link status |
| No. of channels | 8 (RJ45 ports) |
| Input buffer | 1.5 Mbits |
| Output buffer | 1.5 Mbits |

Product properties

| | |
|----------------|--|
| Product type | Switch |
| Product family | Unmanaged Switch 1000 |
| MTTF | 66.1 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) |
| | 786 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) |
| | 709 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day)) |

Switch functions

| | |
|-----------------|----------------------------------|
| Basic functions | Unmanaged switch |
| | Autonegotiation |
| | Store and Forward switching mode |

FL SWITCH 1108N - Industrial Ethernet Switch



1085243

<https://www.phoenixcontact.com/us/products/1085243>

| | |
|----------------------------------|---|
| PROFINET conformance class | Conformance Class A |
| MAC address table | 4k |
| Status and diagnostic indicators | LEDs: U _S , link and activity per port |
| Additional functions | 100 BASE-TX/100BASE-FX (IEEE 802.3u) |
| | Jumbo frames (Max. 9,216 bytes) |
| | Quality of Service (QoS) prioritization (IEEE 802.1p) |
| | Energy-efficient Ethernet (IEEE 802.3az) |
| | Gigabit Ethernet 1000BASE-T (IEEE 802.3ab) |
| | 10Base-T (IEEE 802.3) |

Security functions

| | |
|-----------------|----------------------------------|
| Basic functions | Unmanaged switch |
| | Autonegotiation |
| | Store and Forward switching mode |

Electrical properties

| | |
|---|----------------------|
| Maximum power dissipation for nominal condition | 4.068 W (at 24 V DC) |
| Transmission medium | Copper |

Supply

| | |
|-----------------------------|--|
| Supply voltage (DC) | 24 V |
| Supply voltage (AC) | 24 V AC (50/60 Hz) |
| Supply voltage range | 9 V DC ... 32 V DC |
| | 18 V AC ... 30 V AC (50/60 Hz) |
| Power supply connection | Via COMBICON, max. conductor cross-section 2.5 mm ² |
| Residual ripple | 3.6 V _{PP} (within the permitted voltage range) |
| Max. current consumption | 452 mA (at 9 V DC) |
| Typical current consumption | 54 mA (at 24 V DC) |

Connection data

Power supply

| | |
|---|--|
| Connection method | Push-in spring connection |
| pluggable | yes |
| Conductor cross-section, rigid | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible | 0.2 mm ² ... 2.5 mm ² |
| Conductor cross-section AWG | 24 ... 12 |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, without plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| | 0.25 mm ² ... 2.5 mm ² |
| Conductor cross-section, flexible, with ferrule, with plastic sleeve | 0.25 mm ² ... 2.5 mm ² |
| Stripping length | 10 mm |

Environmental and real-life conditions

Ambient conditions

FL SWITCH 1108N - Industrial Ethernet Switch



1085243

<https://www.phoenixcontact.com/us/products/1085243>

| | |
|--|---|
| Degree of protection | IP30 |
| Ambient temperature (operation) | -10 °C ... 60 °C |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C |
| Altitude | 2000 m (maximum) |
| Permissible humidity (operation) | 5 % ... 95 % (non-condensing) |
| Permissible humidity (storage/transport) | 5 % ... 95 % (non-condensing) |
| Shock (operation) | 30g (EN 60068-2-27) |
| Vibration (operation) | in acc. with IEC 60068-2-6: 5g, 150 Hz |
| Air pressure (operation) | 79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating) |
| Air pressure (storage/transport) | 79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating) |

Approvals

Conformity/Approvals

| | |
|------------------|--|
| UL, USA / Canada | UL 61010-1, UL 61010-2-201, UL 62368-1 Class I, Div. 2, Groups A, B, C, D, T4 Class I, Zone 2, Group IIC, T4 |
| FCC | Title 47 Part 15 Subpart B:2018 Class A |
| FCC certificate | T190905D11-C |

EMC data

| | |
|---------------------------------|--|
| Electromagnetic compatibility | Conformance with EMC Directive 2014/30/EU |
| Conformance with EMC directives | EN 61000-6-2 EN 61000-4-2 (ESD) Criterion B |
| | EN 61000-6-2 EN 61000-4-3 (electromagnetic fields) Criterion A |
| | EN 61000-6-2 EN 61000-4-4 (EFT burst) Criterion A |
| | EN 61000-6-2 EN 61000-4-5 (surge) Criterion B |
| | EN 61000-6-2 EN 61000-4-6 (line noise immunity) Criterion A |
| | EN 61000-6-2 EN 61000-4-8 (electromagnetic fields) Criterion A |
| Noise immunity | EN 61000-6-2 EN 55032 Class A |

Noise emission

| | |
|-----------------------|-------------------|
| Standards/regulations | EN_61000-6-4:2019 |
|-----------------------|-------------------|

System properties

Functionality

| | |
|-----------------|----------------------------------|
| Basic functions | Unmanaged switch |
| | Autonegotiation |
| | Store and Forward switching mode |

Signaling

| | |
|----------------|---|
| Status display | LEDs: U _S , link and activity per port |
|----------------|---|

FL SWITCH 1108N - Industrial Ethernet Switch



1085243

<https://www.phoenixcontact.com/us/products/1085243>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1085243>



IECEE CB Scheme
Approval ID: DK-91138-UL



IECEE CB Scheme
Approval ID: DK-91246-UL



KC
Approval ID: R-R-PCK-1085243



CC-Link IE Field
Approval ID: Ref. No. 214



CC-Link IE Field
Approval ID: NRT-IT-00065



cULus Listed
Approval ID: E238705



cULus Listed
Approval ID: E140304



cUL Listed
Approval ID: E196811



UL Listed
Approval ID: E196811

FL SWITCH 1108N - Industrial Ethernet Switch



1085243

<https://www.phoenixcontact.com/us/products/1085243>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170402 |
| ECLASS-15.0 | 19170402 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000734 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43222600 |
|-------------|----------|

FL SWITCH 1108N - Industrial Ethernet Switch



1085243

<https://www.phoenixcontact.com/us/products/1085243>

Environmental product compliance

EU RoHS

| | |
|---|---------------------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 15(a), 7(a), 7(c)-I |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | 25042bec-731a-40cb-af18-614ae543d184 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 11.89 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com