

FOC-FR19:1U-217S24-LCD24-OM1 - Patch panel



1087112

<https://www.phoenixcontact.com/us/products/1087112>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Preassembled 19" fiber-optic distributor box (1 RU) , M17 MPO series, for connecting an M17 MPO plug assembly.



Your advantages

- Prefabricated FO connection assembly, no welding required on site, plug-and-play
- 1U standard enclosure, receptacle and adapter, enable high-density FO connection
- Other modular housings (1 RU) are available for flexible configuration

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1087112 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB15 |
| Product key | ABNHBC |
| GTIN | 4055626883113 |
| Weight per piece (including packing) | 1,881 g |
| Weight per piece (excluding packing) | 1,825.152 g |
| Customs tariff number | 85367000 |
| Country of origin | CN |

1087112

<https://www.phoenixcontact.com/us/products/1087112>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Network distributor box |
| Type | 19" rack patch module |
| Number of positions | 24 |
| Connection profile | M17/UPC |

Dimensions

| | |
|--------|----------|
| Width | 482.6 mm |
| Height | 44.45 mm |
| Depth | 25.5 mm |

Material specifications

| | |
|--|---------------------|
| Color | gray |
| Flammability rating according to UL 94 | V0 |
| Ferrule material | PPS |
| Housing material | Aluminum alloy |
| Housing surface material | Powder-coated, gray |
| Outer sheath, material | LSFH |

Cable/line

| | |
|------------------------|--------------------------|
| Cable type | Multimode fiberglass |
| Cable type | Fan out |
| Outer sheath, material | LSFH |
| Halogen-free | according to IEC 60754-1 |

FO cable

| | |
|---------------------|----------------------------------|
| Fiber | 62.5/125 µm OM1 |
| Fiber type | Multimode fiberglass 62.5/125 µm |
| Attenuation | < 1.5 dB (1300 nm) |
| Transmission medium | Multi-mode fiberglass |

Mechanical properties

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | > 500 |
|-----------------------------|-------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Degree of protection | IP20 |
| Ambient temperature (operation) | -20 °C ... 70 °C |

Mounting

FOC-FR19:1U-217S24-LCD24-OM1 - Patch panel



1087112

<https://www.phoenixcontact.com/us/products/1087112>

| Mounting type | Screw mounting |
|---------------|----------------|
|---------------|----------------|

1087112

<https://www.phoenixcontact.com/us/products/1087112>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 19170113 |
| ECLASS-15.0 | 19170113 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002699 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 43223300 |
|-------------|----------|

1087112

<https://www.phoenixcontact.com/us/products/1087112>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com