THERMOMARK CARD 2.0 - Thermal transfer printer

1085267

https://www.phoenixcontact.com/us/products/1085267

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CRA-READY



Thermal transfer printer, The THERMOMARK CARD 2.0 thermal transfer printer prints marking materials in sheet and card format quickly and with high quality. Create high-quality markers for applications in terminal, wire, cable, equipment, and plant marking., weight: 6 kg, length: 0.325 m, width: 254 mm, height: 194 mm, The product is being prepared for compliance with the Cyber Resilience Act (CRA)

Product description

THERMOMARK CARD 2.0 prints markers in card format for top quality terminal, wire, cable, equipment and plant marking applications. You can easily create high-quality printed labels and markers.

Your advantages

- Maintenance-free operation with proven thermal transfer printer technology
- Easy to control and manage with MARKING system software
- Automatic material detection prevents printing errors
- Fast, high-quality, and durable printing; printing time for one card is less than 8 seconds
- Easy and intuitive operation via touch color display
- For all UniCard (UCT) and UniSheet (US) materials
- USB and Ethernet connections

ELEKTROGERÄTE RÜCKNAHME

Commercial data

Item number	1085267
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG01
Product key	BG1221
GTIN	4055626834931
Weight per piece (including packing)	9,940 g
Weight per piece (excluding packing)	9,908 g
Customs tariff number	84433210
Country of origin	DE

Technical data

Notes

Note on application

Note on application	As things stand now, we are preparing the product so that, as of December 11, 2027, it will comply with the requirements of the EU Cyber Resilience Act (CRA) based on the information currently available regarding the CRA.

Product properties

Product type	Marking system
Scope of supply	Thermal transfer printer for card materials, including Euro/US power cable and USB cable. Manual printed in German and English. Magazine for UCT-TM... sheets and magazines for US-.. . cards. One packing unit each UCT-TM 6, US-EMLP (85,6x54), ink ribbon: 50 m
Special properties	The product is being prepared for compliance with the Cyber Resilience Act (CRA)

Marking

Identification technology	Thermotransfer

Device properties

Print width	104 mm
Print resolution	300 dpi
Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

System properties

Operating system	MS Windows Vista, MS Windows 7 (32/64-bit), MS Windows 8 (32/64-bit), MS Windows 8.1 (32/64-bit), MS Windows 10 (32/64-bit), Server 2008, Server 2008 R2, Server 2012, Server 2012 R2

Electrical properties

Supply

Supply voltage range	100 V AC ... 240 V AC (50 Hz ... 60 Hz)

Dimensions

Width	254 mm
Height	194 mm
Length	325 mm

Material specifications

Material Plastic signs	UCT
	US
	UM

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	5 °C ... 35 °C

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1085267

IECEE CB Scheme
Approval ID: DK-172084-UL

EAC
Approval ID: KZ 27978

IECEE CB Scheme
Approval ID: DK-81169-M1-UL

UL Listed
Approval ID: E140143

CCC
Approval ID: 2019010904255703

cUL Listed
Approval ID: E140403

KC
Approval ID: R-R-YG3-TC2_0

EAC-RoHS
Approval ID: RU D-DE.HB49.B.00023

UAE-RoHS
Approval ID: 182175_E26-02-190200

ECAS
Approval ID: E25-07-163913

Classifications

ECLASS

ECLASS-13.0	19140104
ECLASS-15.0	19140104

ETIM

ETIM 10.0	EC001684

UNSPSC

UNSPSC 21.0	43212100

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	b86b10c5-dcf8-45e8-8be8-2bc4cdefc9e4

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com