

CUC-F-D1ZNI-S/R4GCHP8 - RJ45 coupling



1086111

<https://www.phoenixcontact.com/us/products/1086111>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



RJ45 coupling, degree of protection: IP20, number of positions: 8, 10 Gbps, CAT6_A, material: Metal, connection method: Coupling, cable outlet: straight, Freenet design for use with IP67 panel mounting frame and terminal outlets, Ethernet

Your advantages

- Compact design
- Freenet adapter for integration into IP6X panel mounting frame
- Rugged design
- 10 Gbps
- Assembly without special tools
- CAT6A in accordance with ISO/IEC 11801
- 360° shielding

Commercial data

Item number	1086111
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB10
Product key	ABNACB
GTIN	4055626877129
Weight per piece (including packing)	15.2 g
Weight per piece (excluding packing)	15.2 g
Customs tariff number	85366930
Country of origin	PL

CUC-F-D1ZNI-S/R4GCHP8 - RJ45 coupling



1086111

<https://www.phoenixcontact.com/us/products/1086111>

Technical data

Product properties

Product type	Female insert
Type	RJ45
Sensor type	Ethernet
Number of positions	8
Connection profile	RJ45
Number of slots	2
Cable outlet	straight

Insulation characteristics

Overvoltage category	III
Degree of pollution	2

Electrical properties

Rated voltage (III/3)	72 V (DC)
Rated surge voltage	0.8 kV
Rated current	1 A (at 60 °C)
Max. operating voltage U_{max}	72 V DC
Frequency range	500 MHz
Insulation resistance	$\geq 500 \text{ M}\Omega$
Nominal current I_N	0.5 A
Contact resistance	200 m Ω (Trunk in to trunk out)
Transmission speed	10 Gbps
Transmission characteristics (category)	CAT6 _A

Connection data

Connection technology

Connection method	Coupling
-------------------	----------

Material specifications

Flammability rating according to UL 94	V0
Housing material	Metal
Housing surface material	metal-plated
Contact material	Spring steel
Contact surface material	Gold

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 750
-----------------------------	------------

Environmental and real-life conditions

CUC-F-D1ZNI-S/R4GCHP8 - RJ45 coupling



1086111

<https://www.phoenixcontact.com/us/products/1086111>

Ambient conditions

Degree of protection	IP20
	IP20
Ambient temperature (operation)	-10 °C ... 60 °C
Ambient temperature (storage/transport)	60 °C

Standards and regulations

Standards/specifications	IEC 60603-7
	DIN EN 50173-1
	ISO/IEC 11801-Am.1
	IEC 60068-2

Mounting

Mounting type	Snap in
---------------	---------

CUC-F-D1ZNI-S/R4GCHP8 - RJ45 coupling



1086111

<https://www.phoenixcontact.com/us/products/1086111>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1086111>



cUL Recognized

Approval ID: E335024-DUXR8



UL Recognized

Approval ID: E335024-DUXR2

CUC-F-D1ZNI-S/R4GCHP8 - RJ45 coupling



1086111

<https://www.phoenixcontact.com/us/products/1086111>

Classifications

ECLASS

ECLASS-13.0	27440390
ECLASS-15.0	27440325

UNSPSC

UNSPSC 21.0	43222600
-------------	----------

CUC-F-D1ZNI-S/R4GCHP8 - RJ45 coupling



1086111

<https://www.phoenixcontact.com/us/products/1086111>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.48 kg CO2e
---------	--------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com