

SAC-5P-M12MS/7,5-810/M12FS-3L - Sensor/actuator cable



1087190

<https://www.phoenixcontact.com/us/products/1087190>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 5-position, PUR halogen-free, welding sputter-resistant, orange RAL 2003, Plug straight M12, coding: A, with 3 LEDs, on Socket straight M12, coding: A, with 3 LEDs, cable length: 7.5 m, for robots and drag chains

Commercial data

Item number	1087190
Packing unit	1 pc
Minimum order quantity	25 pc
Note	Made to order (non-returnable)
Product key	AF1CDA
GTIN	4055626883700
Weight per piece (including packing)	436.75 g
Weight per piece (excluding packing)	436.75 g
Country of origin	PL

SAC-5P-M12MS/7,5-810/M12FS-3L - Sensor/actuator cable



1087190

<https://www.phoenixcontact.com/us/products/1087190>

Technical data

Product properties

Product type	Sensor/actuator cable
Number of positions	5

Signaling

Status display	3 LEDs
----------------	--------

Connector

Connection 1

Type	Plug straight M12
Number of positions	5
Coding type	A

Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A

Cable/line

Cable length	7.5 m
--------------	-------

PUR, halogen-free, highly flexible, welding-sputter resistant, orange [810]

Dimensional drawing



Note	Due to the extremely robust outer sheath, this cable should only be stripped in 5 cm increments.
UL AWM Style	20549 (80°C/300 V)
Number of positions	5
Shielded	no
Cable type	PUR, halogen-free, highly flexible, welding-sputter resistant, orange [810]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross-section	5x 0.34 mm ²
Wire diameter incl. insulation	1.55 mm ±0.05 mm (Signal line)
External cable diameter	6.90 mm ±0.1 mm

SAC-5P-M12MS/7,5-810/M12FS-3L - Sensor/actuator cable



1087190

<https://www.phoenixcontact.com/us/products/1087190>

Outer sheath, material	PUR
External sheath, color	orange RAL 2003
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, white, blue, black, green-yellow
Overall twist	5 wires around filler to the core
Max. conductor resistance	approx. 57 Ω /km
Insulation resistance	$\geq 20 \text{ M}\Omega \cdot \text{km}$
Nominal voltage, cable	300 V (Peak value, not for high-power applications)
Test voltage Core/Core	3000 V (Spark test)
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Smallest bending radius, fixed installation	35 mm
Smallest bending radius, movable installation	69 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000000, Bending radius: 10 x D, Traversing path: 10 m, Traversing rate: 3 m/s, Acceleration: 10 m/s ² , Ambient temperature: $\leq 60 \text{ }^{\circ}\text{C}$
Halogen-free	in accordance with DIN VDE 0472 part 815
Flame resistance	in acc. with UL FT-2
Other resistance	hydrolysis and microbe resistant
Special properties	Sheath resistant to welding beads, can be recycled, matt, without adhesion, wear-resistant, flame resistant and self-extinguishing
	Free from silicone and cadmium
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	-40 $^{\circ}\text{C}$... 80 $^{\circ}\text{C}$ (cable, fixed installation)
	-25 $^{\circ}\text{C}$... 80 $^{\circ}\text{C}$ (Cable, flexible installation)
	$\leq 60 \text{ }^{\circ}\text{C}$ (cable, drag chain applications)

SAC-5P-M12MS/7,5-810/M12FS-3L - Sensor/actuator cable



1087190

<https://www.phoenixcontact.com/us/products/1087190>

Classifications

ECLASS

ECLASS-13.0	27060311
ECLASS-15.0	27060311

ETIM

ETIM 9.0	EC001855
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-5P-M12MS/7,5-810/M12FS-3L - Sensor/actuator cable



1087190

<https://www.phoenixcontact.com/us/products/1087190>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com