

SAC-6P-DTMS-5P-M12FS P - Adapter



1088173

<https://www.phoenixcontact.com/us/products/1088173>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Adapter, 5-position, Plug straight DEUTSCH DT04-6P, on Socket straight M12, coding: A



Commercial data

Item number	1088173
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF13
Product key	AF1GGA
GTIN	4055626887739
Weight per piece (including packing)	14.15 g
Weight per piece (excluding packing)	14.15 g
Customs tariff number	85444290
Country of origin	US

SAC-6P-DTMS-5P-M12FS P - Adapter



1088173

<https://www.phoenixcontact.com/us/products/1088173>

Technical data

Notes

Note on application	Sufficient strain relief at the connection point can prevent premature stress and wear. Utilize tie down accessories to eliminate bending and dynamic loads on the connector.
---------------------	---

Product properties

Product type	M8/M12 adapters
Number of positions	5
Coding	A

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Nominal voltage U_N	48 V AC
	60 V DC
Nominal current I_N	4 A

Material specifications

Flammability rating according to UL 94	V0
Seal material	Viton
Material of grip body	GF nylon
Contact material	CuSn
Contact surface material	Ni/Au M12, Ni/Sn DT
Contact carrier material	GF nylon
Material for screw connection	Plastic
Standards/regulations	Chemical, fertilizer (UAN32), UV resistance

Connector

Connection 1

Type	Plug straight DEUTSCH DT04-6P
Number of positions	5

Connection 2

Type	Socket straight M12
Number of positions	5
Coding type	A

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 100
-----------------------------	------------

SAC-6P-DTMS-5P-M12FS P - Adapter



1088173

<https://www.phoenixcontact.com/us/products/1088173>

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP67
	IP69K
Ambient temperature (operation)	-40 °C ... 105 °C

Approvals

National Marine Electronics Association

Certificate	approved
-------------	----------

Standards and regulations

Standard designation	M12 connector
Standards/specifications	IEC 61076-2-101
Standards/specifications	SAE J2030


SAC-6P-DTMS-5P-M12FS P - Adapter

1088173

<https://www.phoenixcontact.com/us/products/1088173>


Drawings

Dimensional drawing



DT/M12 adapter

Schematic diagram



DEUTSCH DT04-5P pin assignment

SAC-6P-DTMS-5P-M12FS P - Adapter



1088173

<https://www.phoenixcontact.com/us/products/1088173>

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, view female side

Circuit diagram



Contact assignment

SAC-6P-DTMS-5P-M12FS P - Adapter



1088173

<https://www.phoenixcontact.com/us/products/1088173>

Classifications

ECLASS

ECLASS-13.0	27440106
ECLASS-15.0	27440106

ETIM

ETIM 10.0	EC002925
-----------	----------

UNSPSC

UNSPSC 21.0	31251500
-------------	----------

SAC-6P-DTMS-5P-M12FS P - Adapter



1088173

<https://www.phoenixcontact.com/us/products/1088173>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	0a7ca152-349d-4d47-a3cd-d3cbb6868578

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com