

CUC-IND-J1ST-A/R4LS - Modular RJ45 PCB connectors



1091946

<https://www.phoenixcontact.com/us/products/1091946>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 90 °, Tab up, Shielded, number of positions: 8, 10 Gbps, PoE++, THT, THD, Wave, IP20

Your advantages

- Ideal for demanding applications due to the high shock and vibration resistance as well as the extended temperature range
- 360° shielding ensures reliable transmission, even in industrial applications
- The extended temperature range from -40°C to +105°C enables use in demanding industrial applications

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1091946 |
| Packing unit | 84 pc |
| Minimum order quantity | 84 pc |
| Sales key | AB12 |
| Product key | ABNADA |
| GTIN | 4055626906355 |
| Weight per piece (including packing) | 5.575 g |
| Weight per piece (excluding packing) | 5.57 g |
| Customs tariff number | 85366930 |
| Country of origin | CN |

CUC-IND-J1ST-A/R4LS - Modular RJ45 PCB connectors



1091946

<https://www.phoenixcontact.com/us/products/1091946>

Technical data

Product properties

| | |
|---------------------|--|
| Slots | 1x1 single-port |
| Orientation to PCB | 90.00 ° |
| Type | THD |
| Number of positions | 8 (8P8C) |
| Type of locking | Snap-in locking, Tab up |
| Shielding | Shielded |
| Processing notes | Wave |
| Transmission speed | 10 Gbps |
| Power transmission | PoE++ (according to IEEE 802.3bt) |
| Power PSE | 90 W (Class 8 in accordance with IEEE 802.3bt) |
| Power PD | 71 W (Class 4 in accordance with IEEE 802.3bt) |

Electrical properties

| | |
|--------------------------------|-------------------------|
| Pollution degree | 2 (IEC 60664-1) |
| Overvoltage category | I (IEC 60664-1) |
| Rated voltage | 72 V DC |
| Rated surge voltage | 1.5 kV DC (IEC 60664-1) |
| Rated current | 1.5 A (IEC 60603-7) |
| Insulation resistance | > 500 MΩ (IEC 60603-7) |
| Test voltage (Contact/contact) | 1.5 kV DC (IEC 60603-7) |
| Test voltage (Contact/shield) | 1.5 kV DC (IEC 60603-7) |

Dimensions

| | |
|------------------|----------|
| Length | 17.1 mm |
| Width | 16.2 mm |
| Height | 16.5 mm |
| Installed height | 12.80 mm |
| Data pin length | 3.30 mm |

Material specifications

| | |
|---|--------------------|
| Material Contact carrier | PA |
| Flame resistance | UL 94 V0 |
| Halogen-free | yes |
| Material Housing | Copper alloy |
| Material Housing coating | Ni |
| Material Housing pin coating (top layer/selective) | Ni |
| Material Contact | Copper alloy |
| Material Solder contact coating (intermediate layer) | Ni |
| Material Solder contact coating (top layer/selective) | Au |
| Material Plug contact coating (top layer/selective) | Au (1.27 μm/50 μ") |

CUC-IND-J1ST-A/R4LS - Modular RJ45 PCB connectors



1091946

<https://www.phoenixcontact.com/us/products/1091946>

| | |
|--|----|
| Material Plug contact coating (intermediate layer) | Ni |
|--|----|

Mechanical properties

Mechanical data

| | |
|-----------------------------|----------------------|
| Insertion/withdrawal cycles | > 750 (IEC 60603-7) |
| Insertion force | < 20 N (IEC 60603-7) |
| Withdrawal force | < 20 N (IEC 60603-7) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--------------------|
| Ambient temperature (operation) | -40 °C ... 105 °C |
| Ambient temperature (storage/transport) | -40 °C ... 105 °C |
| Degree of protection (plugged in) | IP20 (IEC 60603-7) |
| Degree of protection (Not plugged in) | IP20 (IEC 60603-7) |

Test specification for vibration - sine (IEC 60068-2-6)

| | |
|--------------|-------------------------------|
| Acceleration | 200 m/s ² |
| Frequency | 20 - 2000 Hz |
| Amplitude | 1 mm |
| Cycles | 10 cycles per axis, 20 sweeps |
| Sweep speed | 1 octave/min |

Test specification Shock (IEC 60068-2-27)

| | |
|--------------|----------------------|
| Pulse shape | Half-sine |
| Acceleration | 500 m/s ² |

Mounting

Processing notes

| | |
|---------------|-----|
| Mounting type | THT |
|---------------|-----|

CUC-IND-J1ST-A/R4LS - Modular RJ45 PCB connectors

1091946

<https://www.phoenixcontact.com/us/products/1091946>

Drawings



Classification wave soldering profile

CUC-IND-J1ST-A/R4LS - Modular RJ45 PCB connectors



1091946

<https://www.phoenixcontact.com/us/products/1091946>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1091946>



cUL Recognized
Approval ID: FILE E 335024



UL Recognized
Approval ID: FILE E 335024

CUC-IND-J1ST-A/R4LS - Modular RJ45 PCB connectors



1091946

<https://www.phoenixcontact.com/us/products/1091946>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27460201 |
| ECLASS-15.0 | 27460201 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002637 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

CUC-IND-J1ST-A/R4LS - Modular RJ45 PCB connectors



1091946

<https://www.phoenixcontact.com/us/products/1091946>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com