

# MM-TML (EX3,8)R C1 WH/BK - Label



1092026

<https://www.phoenixcontact.com/us/products/1092026>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, unmarked, can be labeled with: THERMOFOX, THERMOMARK GO, THERMOMARK GO.K, mounting type: adhesive, Number of individual labels: 1, roll length: 8 m, text field height: 3.8 mm, text field width: 8000 mm

## Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The material is cUL certified
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application
- Zack marker strips and flat zack marker strips can be marked subsequently with the TML marking foil
- The self-adhesive material in continuous format is particularly suitable for marking terminals without a marker groove

## Commercial data

Item number	1092026
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG211E
GTIN	4055626906591
Weight per piece (including packing)	54 g
Weight per piece (excluding packing)	41 g
Customs tariff number	96121010
Country of origin	CN

## Technical data

### Product properties

Product type	Terminal marker
--------------	-----------------

### Marking

Number of individual labels	1
Number of individual labels per row	1
Slot type	flat
Identification technology	Thermal transfer

### Dimensions

Length of roll	8.00 m
Height	3.8 mm
Depth	0.07 mm

### Text field

Text field width	8000 mm
Text field height	3.8 mm

### Material specifications

Foil strength	50 µm
Adhesive	Acrylic
Color	white (RAL 9010)
Base element material	Polyester
Components	free from silicone, halogen, and cadmium

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended ambient temperature (storage/transport)	21 °C
Recommended humidity (storage/transport)	45 %

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

#### UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

#### Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
---------------	-------------------------------------

# MM-TML (EX3,8)R C1 WH/BK - Label



1092026

<https://www.phoenixcontact.com/us/products/1092026>

	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

## Mounting

Mounting type	adhesive
---------------	----------

# MM-TML (EX3,8)R C1 WH/BK - Label



1092026

<https://www.phoenixcontact.com/us/products/1092026>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1092026>



**cULus Recognized**  
Approval ID: MH48542

# MM-TML (EX3,8)R C1 WH/BK - Label



1092026

<https://www.phoenixcontact.com/us/products/1092026>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

1092026

<https://www.phoenixcontact.com/us/products/1092026>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	1.003 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)