

# SAC-4P-10,0-680/M8FR FDP - Sensor/actuator cable



1096060

<https://www.phoenixcontact.com/us/products/1096060>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sensor/actuator cable, 4-position, PVC, gray, shielded, free cable end, on Socket angled M8, coding: A, cable length: 10 m, Foil shielding plus drain wire

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1096060                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | BF13                           |
| Product key                          | AF1IEF                         |
| GTIN                                 | 4055626930114                  |
| Weight per piece (including packing) | 22.22 g                        |
| Weight per piece (excluding packing) | 22.22 g                        |
| Country of origin                    | US                             |

1096060

<https://www.phoenixcontact.com/us/products/1096060>

## Technical data

### Product properties

|                      |                       |
|----------------------|-----------------------|
| Product type         | Sensor/actuator cable |
| Application          | Standard, U.S. cables |
| Number of positions  | 4                     |
| No. of cable outlets | 1                     |
| Shielded             | yes                   |
| Coding               | A                     |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Material specifications

|  |   |
|--|---|
| Flammability rating according to UL 94 | HB  |
| Seal material                          | NBR   |
| Material of grip body                  | TPU, hardly inflammable, self-extinguishing |
| Contact material                       | CuSn  |
| Contact surface material               | Ni/Au                                       |
| Contact carrier material               | TPU GF                                      |
| Material for screw connection          | Zinc die-cast, nickel-plated                |

### Electrical properties

|                       |                            |
|-----------------------|----------------------------|
| Insulation resistance | $\geq 100 \text{ M}\Omega$ |
| Nominal voltage $U_N$ | 48 V AC                    |
|                       | 60 V DC                    |
| Nominal current $I_N$ | 4 A                        |

### Mechanical properties

#### Mechanical data

|                             |            |
|-----------------------------|------------|
| Insertion/withdrawal cycles | $\geq 100$ |
|-----------------------------|------------|

### Signaling

|                        |    |
|------------------------|----|
| Status display         | no |
| Status display present | no |

### Connection data

#### Conductor connection

|                   |                        |
|-------------------|------------------------|
| Tightening torque | 0.2 Nm (M8 connectors) |
|-------------------|------------------------|

### Connector

#### Connection 1

# SAC-4P-10,0-680/M8FR FDP - Sensor/actuator cable



1096060

<https://www.phoenixcontact.com/us/products/1096060>

|      |                |
|------|----------------|
| Type | free cable end |
|------|----------------|

## Connection 2

|                     |                  |
|---------------------|------------------|
| Type                | Socket angled M8 |
| Number of positions | 4                |
| Coding type         | A                |

## Cable/line

|   |  |
|---|--|
| Cable length                                  | 10 m   |
| Dimensional drawing                           |  |
| Cable weight                                  | 26.04 kg/km  |
| UL AWM Style                                  | 2517 (105 °C / 300 V)  |
| Number of positions                           | 3  |
| Shielded                                      | yes  |
| AWG signal line                               | 24   |
| Wire diameter incl. insulation                | 1.12 mm ±0.03 mm   |
| External cable diameter                       | 4.17 mm ±0.2 mm  |
| Outer sheath, material                        | PVC  |
| External sheath, color                        | gray   |
| Conductor material                            | Tin-plated Cu litz wires   |
| Material wire insulation                      | PVC (Signal line)  |
| Single wire, color                            | brown, blue, black   |
| Type of pair shielding                        | Plastic-coated aluminum foil, aluminum side inside                                 |
| Overall twist                                 | Conductors, fillers, and drain wire are twisted with left-hand lay                 |
| Max. conductor resistance                     | max. 80.2 Ω/km (20 °C)   |
| Insulation resistance                         | ≥ (550 M Ohms/m @ 500V)  |
| Nominal voltage, cable                        | 300 V  |
| Minimum bending radius, flexible installation | 8 x D  |
| Smallest bending radius, movable installation | 34 mm  |
| Flame resistance                              | FT4  |
| Other resistance                              | UV resistant   |
| Ambient temperature (operation)               | -30 °C ... 105 °C (cable, fixed installation)                                      |

## Environmental and real-life conditions

### Ambient conditions

|                      |      |
|----------------------|------|
| Degree of protection | IP65 |
|                      | IP67 |

# SAC-4P-10,0-680/M8FR FDP - Sensor/actuator cable



1096060

<https://www.phoenixcontact.com/us/products/1096060>

|   |  |
|---|--|
|   | IP68   |
| Ambient temperature (operation) (male connector/female connector) | -25 °C ... 90 °C (Plug / socket)               |
| Ambient temperature (operation) (Cable, flexible installation)    | -40 °C ... 80 °C (cable, fixed installation)   |
|   | -5 °C ... 80 °C (Cable, flexible installation) |

## Standards and regulations

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M8 connector    |
| Standards/specifications | IEC 61076-2-104 |

# SAC-4P-10,0-680/M8FR FDP - Sensor/actuator cable

1096060

<https://www.phoenixcontact.com/us/products/1096060>

## Drawings

Dimensional drawing



Socket M8 x 1, angled

Schematic diagram



Pin assignment M8 socket, 4-pos., view female side


# SAC-4P-10,0-680/M8FR FDP - Sensor/actuator cable



1096060

<https://www.phoenixcontact.com/us/products/1096060>

Circuit diagram



Contact assignment of M8 plugs/sockets

# SAC-4P-10,0-680/M8FR FDP - Sensor/actuator cable



1096060

<https://www.phoenixcontact.com/us/products/1096060>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060311 |
| ECLASS-15.0 | 27060311 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31251501 |
|-------------|----------|

# SAC-4P-10,0-680/M8FR FDP - Sensor/actuator cable



1096060

<https://www.phoenixcontact.com/us/products/1096060>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)