

CUC-IND-J1ST-S/R4LS-LED-PG - Modular RJ45 PCB connectors



1099282

<https://www.phoenixcontact.com/us/products/1099282>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Modular RJ45 PCB connectors, 1x1 single-port, connection direction of the connector to the PCB: 180 °, Shielded, shield springs, Bicolor LED (green-yellow, green-yellow), number of positions: 8, 10 Gbps, PoE++, THT, THD, Wave, IP20

Your advantages

- Ideal for demanding applications due to the high shock and vibration resistance as well as the extended temperature range
- 360° shielding ensures reliable transmission, even in industrial applications
- With integrated hybrid LEDs as optical status indicators of data transmission
- The extended temperature range from -40°C to +105°C enables use in demanding industrial applications

Commercial data

Item number	1099282
Packing unit	84 pc
Minimum order quantity	84 pc
Sales key	AB12
Product key	ABNADA
GTIN	4055626948102
Weight per piece (including packing)	5.3 g
Weight per piece (excluding packing)	5.1 g
Customs tariff number	85366930
Country of origin	CN

CUC-IND-J1ST-S/R4LS-LED-PG - Modular RJ45 PCB connectors



1099282

<https://www.phoenixcontact.com/us/products/1099282>

Technical data

Product properties

Slots	1x1 single-port
Orientation to PCB	180.00 °
Type	THD
Number of positions	8 (8P8C)
Type of locking	Snap-in locking
Shielding	Shielded, shield springs
Status display	Bicolor LED (green-yellow, green-yellow)
Processing notes	Wave
Transmission speed	10 Gbps
Power transmission	PoE++ (according to IEEE 802.3bt)
Power PSE	90 W (Class 8 in accordance with IEEE 802.3bt)
Power PD	71 W (Class 4 in accordance with IEEE 802.3bt)

Electrical properties

Pollution degree	2
Overvoltage category	I (IEC 60664-1)
Rated voltage	72 V DC
Rated surge voltage	1.5 kV DC (IEC 60664-1)
Rated current	1.5 A (IEC 60603-7)
Insulation resistance	> 500 MΩ (IEC 60603-7)
Test voltage (Contact/contact)	1.5 kV DC (IEC 60603-7)
Test voltage (Contact/shield)	1.5 kV DC (IEC 60603-7)

Dimensions

Length	16.8 mm
Width	18 mm
Height	17.9 mm
Installed height	14.30 mm
Data pin length	3.18 mm

Material specifications

Material Contact carrier	PA
Flame resistance	UL 94 V0
Halogen-free	yes
Material Housing	Copper alloy
Material Housing coating	Ni
Material Housing pin coating (top layer/selective)	Ni
Material Contact	Copper alloy
Material Solder contact coating (intermediate layer)	Ni

CUC-IND-J1ST-S/R4LS-LED-PG - Modular RJ45 PCB connectors



1099282

<https://www.phoenixcontact.com/us/products/1099282>

Material Solder contact coating (top layer/selective)	Au
Material Plug contact coating (top layer/selective)	Au (1.27 µm/50 µ")
Material Plug contact coating (intermediate layer)	Ni

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 750 (IEC 60603-7)
Insertion force	< 20 N (IEC 60603-7)
Withdrawal force	< 20 N (IEC 60603-7)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Ambient temperature (storage/transport)	-40 °C ... 105 °C
Degree of protection (plugged in)	IP20 (IEC 60603-7)
Degree of protection (Not plugged in)	IP20 (IEC 60603-7)

Test specification for vibration - sine (IEC 60068-2-6)

Acceleration	200 m/s ²
Frequency	20 - 2000 Hz
Amplitude	1 mm
Cycles	10 cycles per axis, 20 sweeps
Sweep speed	1 octave/min

Test specification Shock (IEC 60068-2-27)

Pulse shape	Half-sine
Acceleration	500 m/s ²

Mounting

Processing notes


Mounting type	THT
---------------	-----

1099282

<https://www.phoenixcontact.com/us/products/1099282>

Drawings

Diagram



Classification wave soldering profile

CUC-IND-J1ST-S/R4LS-LED-PG - Modular RJ45 PCB connectors



1099282

<https://www.phoenixcontact.com/us/products/1099282>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1099282>



cUL Recognized
Approval ID: FILE E 335024



UL Recognized
Approval ID: FILE E 335024

CUC-IND-J1ST-S/R4LS-LED-PG - Modular RJ45 PCB connectors



1099282

<https://www.phoenixcontact.com/us/products/1099282>

Classifications

ECLASS

ECLASS-13.0	27460201
ECLASS-15.0	27460201

ETIM

ETIM 10.0	EC002637
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

CUC-IND-J1ST-S/R4LS-LED-PG - Modular RJ45 PCB connectors



1099282

<https://www.phoenixcontact.com/us/products/1099282>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com