

SK (126X...)A4 SR/TRU - Marker sheet



1101073

<https://www.phoenixcontact.com/us/products/1101073>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker sheet, Din A4, unmarked, can be labeled with: Office printing systems, mounting type: adhesive, Number of individual labels: 1, text field height: 130 mm, text field width: 150 mm

Your advantages

- SK ... self-adhesive device markers for identification of equipment in controller, system, and control cabinet building
- These labels have been specially developed for laser printers
- Can be printed on all commercially available laser printers

Commercial data

Item number	1101073
Packing unit	10 pc
Minimum order quantity	500 pc
Sales key	NULL
Product key	BG2114
GTIN	4055626957326
Weight per piece (including packing)	15.8 g
Weight per piece (excluding packing)	15.8 g
Customs tariff number	39191080
Country of origin	DE

SK (126X...)A4 SR/TRU - Marker sheet



1101073

<https://www.phoenixcontact.com/us/products/1101073>

Technical data

Notes

General	Print image may vary depending on laser printer
---------	---

Product properties

Product type	Device marker
--------------	---------------

Marking

Number of individual labels	1
-----------------------------	---

Dimensions

Width	130 mm
Length	150 mm

Text field

Text field width	150 mm
Text field height	130 mm

Material specifications

Color	silver-colored
Material	Polyester
Base element material	Polyester

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 120 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed

SK (126X...)A4 SR/TRU - Marker sheet



1101073

<https://www.phoenixcontact.com/us/products/1101073>

n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

SK (126X...)A4 SR/TRU - Marker sheet



1101073

<https://www.phoenixcontact.com/us/products/1101073>

Classifications

ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

ETIM

ETIM 10.0	EC000761
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

SK (126X...)A4 SR/TRU - Marker sheet



1101073

<https://www.phoenixcontact.com/us/products/1101073>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com