

# ICS25-C100X12-1018 - Upper housing part



1099162

<https://www.phoenixcontact.com/us/products/1099162>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail housing, Upper part, closed, Housing cover, width: 25 mm, height: 100 mm, depth: 14.35 mm, color: yellow (similar RAL 1018)



## Your advantages

- Flexible use, thanks to the modular system and unique modularity in the connection technology
- Standardized connections such as RJ45, USB, D-SUB and antenna sockets as components that can be integrated
- Optimal space utilization, as well as adaptability of design, colors, and printing
- Eight-position DIN rail connectors with parallel and up to two serial contacts for easy module-to-module communication

## Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1099162                        |
| Packing unit                         | 10 pc                          |
| Minimum order quantity               | 10 pc                          |
| Note                                 | Made to order (non-returnable) |
| Sales key                            | AC02                           |
| Product key                          | ACHAED                         |
| GTIN                                 | 4055626944463                  |
| Weight per piece (including packing) | 9.566 g                        |
| Weight per piece (excluding packing) | 9.566 g                        |
| Customs tariff number                | 85472000                       |
| Country of origin                    | DE                             |

# ICS25-C100X12-1018 - Upper housing part

1099162

<https://www.phoenixcontact.com/us/products/1099162>

## Technical data


### Notes

|               |   |
|---------------|---|
| Assembly note | Please observe the application note in the download area. |
|---------------|---|

### Product properties

|                              |                    |
|------------------------------|--------------------|
| Product type                 | Upper housing part |
| Housing type                 | DIN rail housing   |
| Housing type                 | Modular housings   |
| Housing series               | ICS                |
| Product family               | ICS25-..100X..     |
| Ventilation openings present | no                 |

### Dimensions

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |  |
| Width                           | 25 mm  |
| Height                          | 100 mm   |
| Depth                           | 14.35 mm   |
| Depth from base support surface | 11.9 mm  |

### PCB design

|               |                   |
|---------------|-------------------|
| PCB thickness | 1.4 mm ... 1.8 mm |
|---------------|-------------------|

### Material specifications

|  |                   |
|--|-------------------|
| Color (Upper housing part)             | yellow (RAL 1018) |
| Material Upper housing part            | PA                |
| Flammability rating according to UL 94 | V0                |
| CTI according to IEC 60112             | 600               |

### Environmental and real-life conditions

#### Vibration test

|               |                             |
|---------------|-----------------------------|
| Specification | IEC 60068-2-6:2007-12       |
| Frequency     | 10 - 150 - 10 Hz            |
| Sweep speed   | 1 octave/min                |
| Amplitude     | 0.15 mm (10 Hz ... 58.1 Hz) |
| Acceleration  | 2g (58.1 Hz ... 150 Hz)     |

# ICS25-C100X12-1018 - Upper housing part



1099162

<https://www.phoenixcontact.com/us/products/1099162>

|                        |                   |
|------------------------|-------------------|
| Test duration per axis | 2.5 h             |
| Test directions        | X-, Y- and Z-axis |

## Glow-wire test

|                  |                        |
|------------------|------------------------|
| Specification    | IEC 60695-2-11:2014-02 |
| Temperature      | 850 °C                 |
| Time of exposure | 30 s                   |

## Thermal stability / ball thrust test

|               |                        |
|---------------|------------------------|
| Specification | IEC 60695-10-2:2014-02 |
| Temperature   | 125 °C                 |
| Test duration | 1 h                    |
| Force         | 20 N                   |

## Mechanical strength / tumbling barrel

|                |                        |
|----------------|------------------------|
| Specification  | IEC 60068-2-31:2008-05 |
| Height of fall | 50 cm                  |
| Frequency      | 50                     |

## Shocks

|                                |                                   |
|--------------------------------|-----------------------------------|
| Specification                  | IEC 60068-2-27:2008-02            |
| Pulse shape                    | Semi-sinusoidal                   |
| Acceleration                   | 15g                               |
| Shock duration                 | 11 ms                             |
| Number of shocks per direction | 3                                 |
| Test directions                | X-, Y- and Z-axis (pos. and neg.) |

## Test for substances that would hinder coating with paint or varnish

|               |                    |
|---------------|--------------------|
| Specification | VDMA 24364:2018-05 |
| Result        | Test passed        |

## Degree of protection (IP code)

|                                       |   |
|---------------------------------------|---|
| Specification                         | IEC 60529:1989-11 + AMD 1:1999-11 + AMD 2:2013-08 |
| Result, degree of protection, IP code | IP20  |

## Ambient conditions

|   |  |
|---|--|
| Max. IP code to attain                  | IP20   |
| Ambient temperature (operation)         | -40 °C ... 105 °C (depending on power dissipation) |
| Ambient temperature (storage/transport) | -40 °C ... 55 °C                                   |
| Ambient temperature (assembly)          | -5 °C ... 100 °C                                   |
| Relative humidity (storage/transport)   | 80 %   |

## PCB data

|                      |                   |
|----------------------|-------------------|
| Type of PCB mount    | Slot              |
| Thickness of the PCB | 1.4 mm ... 1.8 mm |

## Mounting

# ICS25-C100X12-1018 - Upper housing part



1099162

<https://www.phoenixcontact.com/us/products/1099162>

|               |         |
|---------------|---------|
| Mounting type | Snap in |
|---------------|---------|

## Packaging specifications

|                      |                     |
|----------------------|---------------------|
| Type of packaging    | packed in cardboard |
| Outer packaging type | Carton              |

1099162

<https://www.phoenixcontact.com/us/products/1099162>

## Drawings

Dimensional drawing



Schematic figure for illustrating the item dimensions. The figure is not of the desired product. For further details, refer to the product drawings in the "Downloads" tab.

# ICS25-C100X12-1018 - Upper housing part



1099162

<https://www.phoenixcontact.com/us/products/1099162>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1099162>



**UL Recognized**

Approval ID: E240868

# ICS25-C100X12-1018 - Upper housing part



1099162

<https://www.phoenixcontact.com/us/products/1099162>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27190603 |
| ECLASS-15.0 | 27190603 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002779 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

# ICS25-C100X12-1018 - Upper housing part



1099162

<https://www.phoenixcontact.com/us/products/1099162>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |               |
|---------|---------------|
| CO2e kg | 0.078 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)