

# PSR-M-EF6-SDOR4-PI - Extension module



1104983

<https://www.phoenixcontact.com/us/products/1104983>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safe extension module with 4 safe relay outputs, 4 reset inputs, TBUS interface, up to SIL 3, Cat. 4/PL e, pluggable Push-in terminal block, TBUS connector included

## Product description

The configurable and individually scalable PSRmodular safety system is a flexible safety solution for monitoring your machine or system. The safe extension module provides the system with additional safe relay outputs.

## Your advantages

- Cost-effective safety solution with a high level of adaptability to individual requirements
- Fast startup, thanks to easy hardware and software configuration
- Machine downtimes minimized with comprehensive, easy-to-understand diagnostics
- Tool-free and time-saving installation thanks to Push-in technology
- Low housing width of just 22.6 mm
- Up to Cat. 4/PL e in accordance with ISO 13849-1, SIL 3 in accordance with EN IEC 62061, SIL 3 in accordance with IEC 61508
- Suitable for elevator applications in accordance with EN 81-20



## Commercial data

|                        |               |
|------------------------|---------------|
| Item number            | 1104983       |
| Packing unit           | 1 pc          |
| Minimum order quantity | 1 pc          |
| Sales key              | DN02          |
| Product key            | DNA362        |
| GTIN                   | 4055626973425 |

# PSR-M-EF6-SDOR4-PI - Extension module



1104983

<https://www.phoenixcontact.com/us/products/1104983>

|                                      |          |
|--------------------------------------|----------|
| Weight per piece (including packing) | 226 g    |
| Weight per piece (excluding packing) | 192 g    |
| Customs tariff number                | 85371098 |
| Country of origin                    | IT       |

## Technical data

### Notes

#### Note on application

|                     |                         |
|---------------------|-------------------------|
| Note on application | Only for industrial use |
|---------------------|-------------------------|

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Safety device   |
| Application  | Safe shutdown   |
| Control      | 1 and 2 channel |

#### Insulation characteristics

|                  |     |
|------------------|-----|
| Protection class | III |
|------------------|-----|

#### Insulation characteristics

|                      |    |
|----------------------|----|
| Overtoltage category | II |
| Degree of pollution  | 2  |

#### Times

|               |                       |
|---------------|-----------------------|
| Response time | see user manual       |
| Restart time  | min. 5 s (Boot time)  |
|               | max. 10 s (Boot time) |

### Electrical properties

|   |   |
|---|---|
| Maximum power dissipation for nominal condition | 7.07 W  |
| Nominal operating mode                          | 100% operating factor   |
| Interfaces                                      | DIN rail TBUS for connection to the master module, supplied as standard |
| Rated surge voltage/insulation                  | Basic insulation 4 kV between all current paths and housing             |

#### Supply

|  |  |
|--|--|
| Designation                                | A1/A2  |
| Rated control circuit supply voltage $U_S$ | 19.2 V DC ... 28.8 V DC                                  |
| Rated control circuit supply voltage $U_S$ | 24 V DC -20 % / +20 % (external fuse, typically 4 A)     |
| Rated control supply current $I_S$         | typ. 120 mA  |
| Power consumption at $U_S$                 | typ. 2.88 W  |
| Inrush current                             | 2 A ( $\Delta t = 1$ ms at $U_S$ )                       |
| Filter time                                | typ. 5 ms (at A1 in the event of voltage dips at $U_S$ ) |
| Protective circuit                         | Serial protection against polarity reversal              |

### Input data

#### Digital: Reset inputs (FBK1, FBK2, FBK3, FBK4)

|                                |                    |
|--------------------------------|--------------------|
| Description of the input       | IEC 61131-2 Type 2 |
| Number of inputs               | 4                  |
| Input voltage range "0" signal | 0 V DC ... 5 V DC  |

# PSR-M-EF6-SDOR4-PI - Extension module



1104983

<https://www.phoenixcontact.com/us/products/1104983>

|   |   |
|---|---|
| Input voltage range "1" signal                | 11 V DC ... 28.8 V DC                               |
| Input current range "0" signal                | < 1 mA  |
| Filter time                                   | 250 ms ±2 ms (Test pulse rate > 500 ms)             |
| Cable length                                  | max. 100 m (per input)                              |
| Max. permissible overall conductor resistance | 1.2 kΩ (Input and reset circuit at U <sub>S</sub> ) |
| Current consumption                           | typ. 10 mA (typ. with U <sub>S</sub> )              |
|   | max. 13 mA (at a control voltage of 28.8 V DC)      |

## Output data

Relay: Enabling current paths (13\_NO1/14\_NO1, 23\_NO2/24\_NO2, 33\_NO3/34\_NO3, 43\_NO4/44\_NO4)

|                             |  |
|-----------------------------|--|
| Output description          | safety-related N/O contacts                              |
| Number of outputs           | 4 (1 NO per output)                                      |
| Contact switching type      | 4 safe outputs   |
| Switching voltage           | min. 10 V AC/DC  |
|                             | max. 250 V AC/DC (Observe the load curve)                |
| Switching power             | min. 200 mW  |
| Inrush current              | min. 20 mA   |
|                             | max. 6 A   |
| Switching capacity          | 3 A (250 V (AC15))                                       |
|                             | 2 A (24 V (DC13))  |
| Limiting continuous current | 4 A (observe derating)                                   |
| Sq. Total current           | 64 A <sup>2</sup> (with 4 x 1-channel, observe derating) |
|                             | 32 A <sup>2</sup> (for 2 x 2-channel, observe derating)  |
| Switching frequency         | 0.5 Hz   |
| Mechanical service life     | 40x 10 <sup>6</sup> switching cycles                     |
| Output fuse                 | 4 A gL/gG  |

## Connection data

Connection technology

|           |     |
|-----------|-----|
| pluggable | yes |
|-----------|-----|

Conductor connection

|                                  |   |
|----------------------------------|---|
| Connection method                | Push-in connection                          |
| Conductor cross-section rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross-section AWG      | 24 ... 14                                   |
| Stripping length                 | 10 mm                                       |

## Signaling

|                           |                                   |
|---------------------------|-----------------------------------|
| Status display            | 4 x LED (yellow)                  |
|                           | 4 x LED (green, red)              |
|                           | 1 x LED (green), 2 x LED (orange) |
| Operating voltage display | 1 x LED (green)                   |
| Error indication          | 2 x LED (red)                     |

1104983

<https://www.phoenixcontact.com/us/products/1104983>

## Dimensions

|        |           |
|--------|-----------|
| Width  | 22.61 mm  |
| Height | 107.74 mm |
| Depth  | 113.6 mm  |

## Material specifications

|                  |                             |
|------------------|-----------------------------|
| Color (Housing)  | yellow (RAL 1018)           |
| Housing material | Polyamide PA non-reinforced |

## Characteristics

### Safety data

|                            |   |
|----------------------------|---|
| Stop category (EN 60204-1) | 0 |
|----------------------------|---|

### Safety data: EN ISO 13849

|                        |                      |
|------------------------|----------------------|
| Performance level (PL) | e (2-channel wiring) |
|                        | c (1-channel wiring) |

### Safety data: IEC 61508 - High-demand for 2-channel wiring

|                              |   |
|------------------------------|---|
| Safety Integrity Level (SIL) | 3 |
|------------------------------|---|

### Safety data: IEC 61508 - High-demand for 1-channel wiring

|                              |   |
|------------------------------|---|
| Safety Integrity Level (SIL) | 1 |
|------------------------------|---|

### Safety data: EN IEC 62061

|                              |                      |
|------------------------------|----------------------|
| Safety Integrity Level (SIL) | 3 (2-channel wiring) |
|                              | 1 (1-channel wiring) |

## Environmental and real-life conditions

### Ambient conditions

|  |  |
|--|--|
| Degree of protection                           | IP20   |
| Min. degree of protection of inst. location    | IP54   |
| Ambient temperature (operation)                | -10 °C ... 55 °C (observe derating)  |
| Ambient temperature (storage/transport)        | -20 °C ... 85 °C   |
| Maximum altitude                               | ≤ 2000 m (Above sea level)   |
| Max. permissible humidity (storage/transport)  | 95 % (non-condensing)  |
| Max. permissible relative humidity (operation) | 95 % (non-condensing)  |
| Shock  | 10g for $\Delta t = 16$ ms (continuous shock, 1000 shocks in each space direction) |
| Vibration (operation)                          | 10 Hz ... 150 Hz, amplitude 0.15 mm, 2g  |

## Approvals

### CE

|                |              |
|----------------|--------------|
| Identification | CE-compliant |
|----------------|--------------|

# PSR-M-EF6-SDOR4-PI - Extension module



1104983

<https://www.phoenixcontact.com/us/products/1104983>

## Mounting

|                   |                        |
|-------------------|------------------------|
| Mounting type     | DIN rail mounting      |
| Assembly note     | Observe derating       |
| Mounting position | vertical or horizontal |

# PSR-M-EF6-SDOR4-PI - Extension module




1104983

<https://www.phoenixcontact.com/us/products/1104983>


## Drawings

Application drawing



## Example application

Block diagram



## Block diagram

# PSR-M-EF6-SDOR4-PI - Extension module



1104983

<https://www.phoenixcontact.com/us/products/1104983>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1104983>



### cULus Listed

Approval ID: E238705



### Functional Safety

Approval ID: Z10029429 0013Rev.02

# PSR-M-EF6-SDOR4-PI - Extension module



1104983

<https://www.phoenixcontact.com/us/products/1104983>

## Classifications

### ECLASS

|                   |          |
|-------------------|----------|
| ECLASS-13.0       | 27371819 |
| ECLASS-15.0       | 27371819 |
| ECLASS-15.0 ASSET | 27250101 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001449 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39122200 |
|-------------|----------|

1104983

<https://www.phoenixcontact.com/us/products/1104983>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |                |
|---------|----------------|
| CO2e kg | 34.654 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)