

# FL SWITCH 2708 - Industrial Ethernet Switch



1106615

<https://www.phoenixcontact.com/us/products/1106615>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Managed Switch 2000 series, 8 M12 ports 10/100/1000 Mbps, degree of protection: IP65/IP66/IP67, Ambient temperature (operation): -40 °C ... 70 °C, Supply voltage range: 9 V DC ... 57 V DC, PROFINET Conformance Class B, Extended temperature range, Development process certified in accordance with IEC 62443-4-1, Product certified in accordance with IEC 62443-4-2

## Your advantages

- Robust IP67 housing
- Easy panel mounting

## Commercial data

Item number	1106615
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN17
Product key	DNN126
GTIN	4063151001674
Weight per piece (including packing)	1,408 g
Weight per piece (excluding packing)	1,400 g
Customs tariff number	85176200
Country of origin	DE

# FL SWITCH 2708 - Industrial Ethernet Switch




1106615

<https://www.phoenixcontact.com/us/products/1106615>

## Technical data

### Dimensions

Dimensional drawing	
Width	60 mm
Height	226 mm
Depth	46 mm
Drill hole spacing	210 mm

### Notes

General	Support by phone or on-site (fee is charged)
Note on application	
Note on application	Only for industrial use

### Material specifications

Housing material	Die-cast zinc
------------------	---------------

### Mounting

Mounting type	Panel mounting
---------------	----------------

### Interfaces

#### Ethernet

Connection method	M12 connector, X-coded
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100/1000 Mbps
Transmission physics	Copper
Transmission length	100 m (per segment)
Signal LEDs	Data receive, link status
No. of channels	8 (M12 ports)

### Product properties

Product type	Switch
Product family	Managed Switch 2000
Type	Stand-alone
MTTF	461.15 Years (SN 29500 standard, temperature 25°C, operating cycle 21%)

# FL SWITCH 2708 - Industrial Ethernet Switch



1106615

<https://www.phoenixcontact.com/us/products/1106615>

	149.69 Years (SN 29500 standard, temperature 40°C, operating cycle 34.25%)
	19.78 Years (SN 29500 standard, temperature 70°C, operating cycle 100%)
Special properties	Extended temperature range
	Development process certified in accordance with IEC 62443-4-1
	Product certified in accordance with IEC 62443-4-2
Signal delay	≥ 1.9 μs (Store-and-Forward mode, 10/100/1000 Mbps, depending on the frame size)

## Insulation characteristics

Protection class	III (VDE 0106)
------------------	----------------

## Switch functions

Diagnostic functions	RMON History
	LLDP (Link Layer Discovery Protocol)
	SNMP-Traps
	N:1-Portmirroring
	ACD (Address Conflict Detection)
	SysLog
	CRC-Surveillance
Basic functions	Store-and-forward switch, complies with IEEE 802.3
PROFINET conformance class	Conformance Class B
PROFINET device function	PROFINET device
	Fast Startup
Filter functions	Quality of Service (8 priority classes)
	Class of Service
	DiffServ/DSCP
	Port-Priorisierung
	VLAN (up to 32 VLANs)
	IGMP Snooping/Querier (v1/v2)
	Auto-Query-Port
	Extended Multicast Filtering
IP parameterization	DHCP client
	DHCP Option 82 (Relay Agent)
	DHCP server (pool-based, port-based)
	BootP
	DCP (Discovery and Configuration Protocol)
MAC address table	8k
Management	Web-based management (HTTP/HTTPS)
	Role-based user management (LDAP, RADIUS)
	SNMPv1/v2/v3
	Command Line Interface (Telnet, SSH)
Redundancy	MRP (Media Redundancy Protocol)
	RSTP (Rapid Spanning Tree Protocol)
	FRD (Fast Ring Detection)

# FL SWITCH 2708 - Industrial Ethernet Switch



1106615

<https://www.phoenixcontact.com/us/products/1106615>

	Large Tree Support
	LACP (Link Aggregation Control Protocol)
	PROFINET S2 system redundancy
Status and diagnostic indicators	LEDs: US1, US2 (power supply), Fail, 2 LEDs per Ethernet port (Link/Activity and Speed)
Additional functions	Jumbo frames (max. 9,600 bytes)
	Transmission of MMS and GOOSE (IEC 61850-8-1)
	Transmission of Modbus/TCP
Time synchronization	SNTP (Simple Network Time Protocol)

## Security functions

Port security	MAC-based, RADIUS (IEEE 802.1X), MAC Authentication Bypass
Basic functions	Store-and-forward switch, complies with IEEE 802.3

## Electrical properties

Current consumption	260 mA
Local diagnostics	US1/2 Supply voltage US1, US2 Green LED
	FAIL Div. LED red
	LINK Link status Green LED
Maximum power dissipation for nominal condition	6.93 W ( $U_S = \min, T_{amb} = \max$ )
Test section	24 V supply / functional ground 500 V DC 1 min
	Ethernet interface/all other potentials 2.25 kV DC 1 min
Transmission medium	Copper

## Supply

Supply voltage (DC)	24 V DC (redundant)
Supply voltage range	9 V DC ... 57 V DC
Residual ripple	3.6 V <sub>PP</sub> (within the permitted voltage range)
Max. current consumption	0.77 A ( $U_S = \min, T_{amb} = \max$ )
Typical current consumption	260 mA (at $U_S = 24$ V DC and 25 °C ambient temperature)
Current consumption	260 mA

## Connection data

Connection method	M12 connector, A-coded
-------------------	------------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP65
	IP66
	IP67
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 %
Permissible humidity (storage/transport)	5 % ... 95 %

# FL SWITCH 2708 - Industrial Ethernet Switch



1106615

<https://www.phoenixcontact.com/us/products/1106615>

Shock (operation)	30g (EN 60068-2-27)
Vibration (operation)	in acc. with IEC 60068-2-6: 5g, 150 Hz
Air pressure (operation)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)
Air pressure (storage/transport)	79 kPa ... 108 kPa up to 2000 m above mean sea level (Without derating)

## Standards and regulations

Free from substances that could impair the application of coating	Yes
---	-----

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	EN 61000-6-2 EN 61000-4-2 (ESD) Criterion B
	EN 61000-6-2 EN 61000-4-3 (electromagnetic fields) Criterion A
	EN 61000-6-2 EN 61000-4-4 (EFT burst) Criterion A
	EN 61000-6-2 EN 61000-4-5 (surge) Criterion B
	EN 61000-6-2 EN 61000-4-6 (line noise immunity) Criterion A
	EN 61000-6-3 (conducted emissions) Class B
EN 61000-6-3 (conducted emissions) Class B	
Noise immunity	EN 61000-6-2

## Noise emission

Standards/regulations	EN 61000-6-3
-----------------------	--------------

## System properties

### Functionality

Basic functions	Store-and-forward switch, complies with IEEE 802.3
-----------------	--

## Signaling

Status display	LEDs: US1, US2 (power supply), Fail, 2 LEDs per Ethernet port (Link/Activity and Speed)
----------------	---



# FL SWITCH 2708 - Industrial Ethernet Switch

1106615

<https://www.phoenixcontact.com/us/products/1106615>

Schematic diagram



## Connection of the supply voltage

PIN 1 Us1

PIN 2 GND


Pin 3 GND

Pin 4 Us2

Pin 5 functional ground

1106615

<https://www.phoenixcontact.com/us/products/1106615>



#### Assignment of the LAN female connector

- Pin 1 DB+
- Pin 2 DB-
- Pin 3 DA+
- Pin 4 DA-
- Pin 5 DC+
- Pin 6 DC-
- Pin 7 DD-
- Pin 8 DD+

# FL SWITCH 2708 - Industrial Ethernet Switch



1106615

<https://www.phoenixcontact.com/us/products/1106615>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1106615>



**cULus Listed**

Approval ID: E238705

**CC-Link IE Field**

**CC-Link IE Field**

Approval ID: NRT-IF-00058

**CC-Link IE Field**

**CC-Link IE Field**

Approval ID: NRT-IT-00067

**Cybersecurity Certificate**

Approval ID: 968 CSP 1043.00 25

# FL SWITCH 2708 - Industrial Ethernet Switch



1106615

<https://www.phoenixcontact.com/us/products/1106615>

## Classifications

### ECLASS

ECLASS-13.0	19170401
ECLASS-15.0	19170401

### ETIM

ETIM 10.0	EC000734
-----------	----------

### UNSPSC

UNSPSC 21.0	43222600
-------------	----------

# FL SWITCH 2708 - Industrial Ethernet Switch



1106615

<https://www.phoenixcontact.com/us/products/1106615>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a196de77-583f-4e57-a180-3b63bb2f12ed

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)