

VIP-2/SC/D37SUB/M/ET200SP-HA - Termination board



1100967

<https://www.phoenixcontact.com/us/products/1100967>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module for the SIMATIC ET200SP HA with screw connections and male D-SUB connector, for mounting on NS 35 rails, 37-pos.

Your advantages

- These VARIOFACE modules are used in combination with the relevant front adapters

Commercial data

Item number	1100967
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	C423
Product key	DK211S
GTIN	4055626953298
Weight per piece (including packing)	203.2 g
Weight per piece (excluding packing)	203 g
Customs tariff number	85366990
Country of origin	US

VIP-2/SC/D37SUB/M/ET200SP-HA - Termination board



1100967

<https://www.phoenixcontact.com/us/products/1100967>

Technical data

Product properties

Product type	Interface module
Product family	VARIOFACE Professional
Number of positions	37
No. of channels	8
	16
	32

Electrical properties

Operating voltage (AC)	25 V AC
Operating voltage (DC)	60 V DC
Current (per branch)	≤ 2 A

Supported controller: SIEMENS ET 200SP HA

Suitable terminal block	6DL1193-6TP00-0BH1
	6DL1193-6TP00-0DH1
	6DL1193-6TP00-0BM1
	6DL1193-6TP00-0DM1
Suitable I/O module	6DL1131-6BH00-0PH1 (Terminal Block H1/M1)
	6DL1131-6BL00-0PH1 (Terminal Block H1/M1)
	6DL1131-6TH00-0PH1 (Terminal Block H1/M1)
	6DL1132-6BH00-0PH1 (Terminal Block H1/M1)
	6DL1132-6BL00-0PH1 (Terminal Block H1/M1)
	6DL1133-6EW00-0PH1 (Terminal Block H1/M1)
	6DL1134-6JH00-0PH1 (Terminal Block H1/M1)
	6DL1134-6TH00-0PH1 (Terminal Block H1/M1)
	6DL1135-6TF00-0PH1 (Terminal Block H1/M1)

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M 3
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	D-SUB pin strip
Number of connections	1
Number of positions	37

VIP-2/SC/D37SUB/M/ET200SP-HA - Termination board



1100967

<https://www.phoenixcontact.com/us/products/1100967>

Signaling

Status display	no
Status display present	no

Dimensions

Item dimensions

Width	101 mm
Height	65.5 mm
Depth	45.1 mm

Material specifications

Color	gray (RAL 7042)
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 70 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

Standards and regulations

Standards/regulations	DIN EN 50178
-----------------------	--------------

Mounting

Mounting type	DIN rail mounting
Mounting position	any

VIP-2/SC/D37SUB/M/ET200SP-HA - Termination board




1100967

<https://www.phoenixcontact.com/us/products/1100967>

Drawings

Circuit diagram



VIP-2/SC/D37SUB/M/ET200SP-HA - Termination board





1100967


<https://www.phoenixcontact.com/us/products/1100967>


Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1100967>

 CSA Approval ID: 2122203				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	105 V	2 A	28 - 14	-

 cUL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	2 A	30 - 12	-

 UL Recognized Approval ID: E238705				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	125 V	2 A	30 - 12	-

 CSAus Approval ID: 2122203				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
keine				
	105 V	2 A	28 - 14	-

VIP-2/SC/D37SUB/M/ET200SP-HA - Termination board



1100967

<https://www.phoenixcontact.com/us/products/1100967>

Classifications

ECLASS

ECLASS-13.0	27141152
ECLASS-15.0	27141152

ETIM

ETIM 10.0	EC002780
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

VIP-2/SC/D37SUB/M/ET200SP-HA - Termination board



1100967

<https://www.phoenixcontact.com/us/products/1100967>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	6b552c94-d278-45ec-a868-aac8d0f6751a

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com