


# PSR-M-CABLE50 - Cable

1104841

<https://www.phoenixcontact.com/us/products/1104841>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Connection cable for TBUS extension in connection with PSR-M-TBUS1 or PSR-M-TBUS2, 50 m



The figure shows a version of the article

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1104841       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | DN02          |
| Product key                          | DNA366        |
| GTIN                                 | 4055626971254 |
| Weight per piece (including packing) | 4,716 g       |
| Weight per piece (excluding packing) | 4,716 g       |
| Customs tariff number                | 85444995      |
| Country of origin                    | IT            |

# PSR-M-CABLE50 - Cable



1104841

<https://www.phoenixcontact.com/us/products/1104841>

## Technical data

### Notes

#### Note on application

Note on application

Only for industrial use

### Product properties

Product type

Adapter cable

### Electrical properties

Impedance

nom. 120  $\Omega$

### Dimensions

#### External dimensions

External diameter max.

9.00 mm

### Material specifications

Outer sheath, material

PVC

### Cable/line

Cable length

50 m

Cable structure

2 x 2 x 24 AWG

External cable diameter

8.70 mm

Outer sheath, material

PVC

External sheath, color

yellow

Shielding

Braided copper wires

Cable resistance

< 95 m $\Omega$ /m

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)

-30 °C ... 60 °C

# PSR-M-CABLE50 - Cable



1104841

<https://www.phoenixcontact.com/us/products/1104841>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27371392 |
| ECLASS-15.0 | 27371392 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002886 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121100 |
|-------------|----------|

# PSR-M-CABLE50 - Cable



1104841

<https://www.phoenixcontact.com/us/products/1104841>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |                |
|---------|----------------|
| CO2e kg | 15.202 kg CO2e |
|---------|----------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)