

PSR-M-CABLE50 - Cable




1104841

<https://www.phoenixcontact.com/us/products/1104841>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Connection cable for TBUS extension in connection with PSR-M-TBUS1 or PSR-M-TBUS2, 50 m



The figure shows a version of the article

Commercial data

Item number	1104841
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DN02
Product key	DNA366
GTIN	4055626971254
Weight per piece (including packing)	4,716 g
Weight per piece (excluding packing)	4,716 g
Customs tariff number	85444995
Country of origin	IT

PSR-M-CABLE50 - Cable



1104841

<https://www.phoenixcontact.com/us/products/1104841>

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Adapter cable
--------------	---------------

Electrical properties

Impedance	nom. 120 Ω
-----------	------------

Dimensions

External dimensions

External diameter max.	9.00 mm
------------------------	---------

Material specifications

Outer sheath, material	PVC
------------------------	-----

Cable/line

Cable length	50 m
Cable structure	2 x 2 x 24 AWG
External cable diameter	8.70 mm
Outer sheath, material	PVC
External sheath, color	yellow
Shielding	Braided copper wires
Cable resistance	< 95 mΩ/m

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-30 °C ... 60 °C
---------------------------------	------------------

PSR-M-CABLE50 - Cable



1104841

<https://www.phoenixcontact.com/us/products/1104841>

Classifications

ECLASS

ECLASS-13.0	27371392
ECLASS-15.0	27371392

ETIM

ETIM 10.0	EC002886
-----------	----------

UNSPSC

UNSPSC 21.0	39121100
-------------	----------

PSR-M-CABLE50 - Cable



1104841

<https://www.phoenixcontact.com/us/products/1104841>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	15.202 kg CO2e
---------	----------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com