CRIMPFOX VARIO 16S - Crimping pliers

1108767

https://www.phoenixcontact.com/us/products/1108767

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, min. cross section: 6 mm^2, max. cross section: 16 mm^2, compression: Square crimp, weight 582 g, black/green

Your advantages

- Lateral conductor entry
- Proven high-quality technology
- Unlockable pressure lock
- “The original”
- Suitable for TWIN sleeves

Commercial data

Item number	1108767
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3131
GTIN	4063151016449
Weight per piece (including packing)	698.6 g
Weight per piece (excluding packing)	582.25 g
Customs tariff number	82032000
Country of origin	SE

Technical data

Product properties

Product type	Crimping tool
Compression	Square crimp
Product property	Lateral conductor entry
	Unlockable pressure lock
	Suitable for TWIN ferrules

Crimping position 1

Max. cross section	6 mm²
AWG max	10

Crimping position 2

Max. cross section	10 mm²
AWG max	8

Crimping position 3

Max. cross section	16 mm²
AWG max	6

Electrical properties

Fuse	DIN 46228-1, DIN 46228-4

Connection data

Conductor connection

Cross section range, metric	6 mm² ... 16 mm²
Cross section range AWG	10 ... 6

Dimensions

Width	76 mm
Height	25 mm
Length	222 mm

Material specifications

Color	black/green

Approvals

To download certificates, visit the product detail page: https://www.phoenixcontact.com/us/products/1108767

EAC
Approval ID: RU x-DE.xx08.B.02974

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 10.0	EC000168

UNSPSC

UNSPSC 21.0	27111500

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com