

BL2 BPC 9100 - Box PC

1105778

<https://www.phoenixcontact.com/us/products/1105778>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

IP20-rated fanless industrial box PC (BPC) with a powerful Intel® Core™ i7-6600U processor with 16 GB of RAM and M.2 mass storage.



Commercial data

Item number	1105778
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DR20
Product key	DRBABA
Weight per piece (including packing)	9,999 g
Weight per piece (excluding packing)	9,999 g
Customs tariff number	84715000
Country of origin	TW

Technical data

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Product properties

Product type	Box PC
Computer data	
Processor	Intel® Core™ i7-6600U
Operating system	Windows® 10 IoT Enterprise LTSC 2019 (64-bit), Multi-language
RAM	16 GB DDR3 SODIMM
Data storage system	M.2 SSD
Cooling	passive

System properties

User software	without user software
	Visu+

Electrical properties

Service life of battery	5 years (typical)
Supply	
Power supply unit	24 V DC $\pm 20\%$
Real-time clock	
Realtime clock	Yes (battery-backed)

Interfaces

Interfaces	1x COM (RS-232/422/485)
	2x COM (RS-232)
	2x USB 2.0
	2x USB 3.0
Monitor output	2x DisplayPort
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

Dimensions

External dimensions	
Width / Height / Depth	247 mm / 145 mm / 54 mm
Installation dimensions	
Width / Height / Installation depth	247 mm / 94 mm /

Material specifications

Color (Housing)	white aluminium (RAL 9006)
-----------------	----------------------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 75 °C
Permissible humidity (operation)	10 % ... 90 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 90 % (non-condensing)
Shock	20g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	2g _{rms} at sine, 5~500 Hz, 1 h/axis (panel mounting; SSD operating) according to EN 60068-2-6 0.5g _{rms} at sine, 5~500 Hz, 1 h/axis (panel mounting; HDD operating) according to EN 60068-2-6

Mounting

Mounting type	Panel mounting
	DIN rail mounting

BL2 BPC 9100 - Box PC


1105778

<https://www.phoenixcontact.com/us/products/1105778>



Drawings

Dimensional drawing



BL2 BPC 9100 - Box PC



1105778

<https://www.phoenixcontact.com/us/products/1105778>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1105778>



IECEE CB Scheme
Approval ID: US-37343-M1-UL



UL Listed
Approval ID: E238705



cUL Listed
Approval ID: E238705



cULus Listed
Approval ID: E238705

BL2 BPC 9100 - Box PC

1105778

<https://www.phoenixcontact.com/us/products/1105778>



Classifications

ECLASS

ECLASS-13.0	19200102
ECLASS-15.0	19200102

ETIM

ETIM 10.0	EC001413
-----------	----------

UNSPSC

UNSPSC 21.0	43211500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(a), 6(a)-I, 7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	1-Methyl-2-pyrrolidone (NMP)(CAS: 872-50-4)
	Lead(CAS: 7439-92-1)
	2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one(CAS: 71868-10-5)