

NBC-R4ACS/0,3-93C/R4ACS - Patch cable



1112940

<https://www.phoenixcontact.com/us/products/1112940>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, RJ45/IP20 straight on RJ45/IP20 straight, cable length: 0.3 m, number of positions: 4, 100 Mbps, CAT5, PROFINET, 1x4xAWG22/7, SF/TQ, green RAL 6018

Your advantages

- Perfect for industrial applications
- PUR cable for moving applications (bend)
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- Resistant to shock and vibrations, thanks to robust molding
- High-speed data transmission with up to 100 Mbps (CAT5)



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1112940 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB11 |
| Product key | ABNABA |
| GTIN | 4063151034818 |
| Weight per piece (including packing) | 45.8 g |
| Weight per piece (excluding packing) | 33.962 g |
| Customs tariff number | 85444210 |

NBC-R4ACS/0,3-93C/R4ACS - Patch cable



1112940

<https://www.phoenixcontact.com/us/products/1112940>

| | |
|-------------------|----|
| Country of origin | PL |
|-------------------|----|

1112940

<https://www.phoenixcontact.com/us/products/1112940>

Technical data

Product properties

| | |
|---------------------|--------------------------|
| Product type | Data cable preassembled |
| Product family | RJ45 INDUSTRIAL PN4 CAT5 |
| Number of positions | 4 |
| Shielded | yes |

Interfaces

| | |
|----------------------|-------------------------------------|
| Signal type/category | PROFINET CAT5 (IEC 11801), 100 Mbps |
|----------------------|-------------------------------------|

Electrical properties

| | |
|---|----------|
| Rated voltage (III/2) | 72 V |
| Rated current | 1.75 A |
| Insulation resistance | > 1 TΩ |
| Contact resistance | < 20 mΩ |
| Transmission speed | 100 Mbps |
| Transmission characteristics (category) | CAT5 |
| Transmission speed | 100 Mbps |

Dimensions

| | |
|--------|---------|
| Width | 13.8 mm |
| Height | 14.8 mm |
| Length | 44.2 mm |

Connector

Connection 1

| | |
|--|--|
| Type | RJ45 Plug, straight, 4-position |
| Number of positions | 4 |
| Signal type/category | PROFINET CAT5 (IEC 11801), 100 Mbps EtherCAT®, 100 Mbps |
| Insertion/withdrawal cycles | ≥ 750 |
| Insertion force | 50 N (per signal contact) |
| Withdrawal force | 30 N (per signal contact) |
| Overvoltage category | I |
| Degree of pollution | 2 |
| Material Contact | CuSn6 |
| Material Contact surface | Ni/Au |
| Material Contact carrier | PC |
| Material Housing | PP |
| Color (Housing) | black |
| Flammability rating according to UL 94 | V2 |
| Degree of protection | IP20 |

NBC-R4ACS/0,3-93C/R4ACS - Patch cable



1112940


<https://www.phoenixcontact.com/us/products/1112940>

| | |
|--|--|
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Connection 2 | |
| Type | RJ45 Plug, straight, 4-position |
| Number of positions | 4 |
| Signal type/category | PROFINET CAT5 (IEC 11801), 100 Mbps EtherCAT®, 100 Mbps |
| Insertion/withdrawal cycles | ≥ 750 |
| Insertion force | 50 N (per signal contact) |
| Withdrawal force | 30 N (per signal contact) |
| Overvoltage category | I |
| Degree of pollution | 2 |
| Material Contact | CuSn6 |
| Material Contact surface | Ni/Au |
| Material Contact carrier | PC |
| Material Housing | PP |
| Color (Housing) | black |
| Flammability rating according to UL 94 | V2 |
| Degree of protection | IP20 |
| Ambient temperature (operation) | -40 °C ... 85 °C |

Cable/line

| | |
|--------------|--------|
| Cable length | 0.30 m |
|--------------|--------|

PROFINET drag chain CAT5 [93C]

| | |
|--------------------------------|--|
| Dimensional drawing |  |
| UL AWM Style | 20233 (80°C/300 V) |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | PROFINET drag chain CAT5 [93C] |
| Conductor structure | 1x4xAWG22/7, SF/TQ |
| AWG signal line | 22 |
| Conductor cross-section | 4x 0.34 mm ² |
| Wire diameter incl. insulation | 1.5 mm ±0.05 mm |
| External cable diameter | 6.50 mm ±0.2 mm |
| Outer sheath, material | PUR |
| External sheath, color | green RAL 6018 |
| Conductor material | Tin-plated Cu litz wires |

NBC-R4ACS/0,3-93C/R4ACS - Patch cable



1112940

<https://www.phoenixcontact.com/us/products/1112940>

| | |
|---|---|
| Material wire insulation | PE |
| Single wire, color | white, yellow, blue, orange |
| Overall twist | Star quad |
| Optical shield covering | 85 % |
| Insulation resistance | ≥ 500 MΩ*km |
| Loop resistance | ≤ 120.00 Ω/km |
| Wave impedance | 100 Ω ±15 Ω (at 1 ... 100 MHz) |
| Nominal voltage, cable | ≤ 300 V |
| Test voltage Core/Core | 2000 V (50 Hz, 1 min.) |
| Test voltage Core/Shield | 2000.00 V (50 Hz, 1 min.) |
| Minimum bending radius, fixed installation | 5 x D |
| Minimum bending radius, flexible installation | 7.5 x D |
| Dynamic load capacity (bending) | Max. bending cycles: 3000000, Bending radius: 200 mm, Traversing path: 10 m, Traversing rate: 4 m/s, Acceleration: 4 m/s ² |
| Dynamic load capacity (torsion) | Torsion: ±30 °/m |
| Halogen-free | according to IEC 60754-1 |
| Flame resistance | according to IEC 60332-1-2 in accordance with UN ECE-R 118.03 according to CSA C 22.2 No. 210-FT1 |
| Resistance to oil | in accordance with DIN EN 60811-404 |
| Other resistance | UV resistant |
| Special properties | Flexible cable conduit capable |
| Ambient temperature (operation) | -40 °C ... 70 °C (cable, fixed installation) -40 °C ... 70 °C (Cable, flexible installation) |

Environmental and real-life conditions

Ambient conditions

| | |
|---|-----------------------------------|
| Ambient temperature (operation) | -40 °C ... 85 °C (RJ45 connector) |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C (RJ45 connector) |

Standards and regulations

| | |
|--------------------------|-------------|
| Standards/specifications | IEC 60603-7 |
|--------------------------|-------------|

NBC-R4ACS/0,3-93C/R4ACS - Patch cable



1112940

<https://www.phoenixcontact.com/us/products/1112940>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1112940>

|  UL Listed Approval ID: E335024-V1S7 | | | | |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 57 V | 1.75 A | - | - |

|  cUL Listed Approval ID: E335024-V1S7 | | | | |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
| | Nominal voltage U_N | Nominal current I_N | Cross section AWG | Cross section mm^2 |
| keine | | | | |
| | 57 V | 1.75 A | - | - |

NBC-R4ACS/0,3-93C/R4ACS - Patch cable



1112940

<https://www.phoenixcontact.com/us/products/1112940>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

NBC-R4ACS/0,3-93C/R4ACS - Patch cable



1112940

<https://www.phoenixcontact.com/us/products/1112940>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com