FOC-ST:PA-ST:PA-OM1:D01/3 - FO patch cable

1111536

https://www.phoenixcontact.com/us/products/1111536

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Multi-mode OM1 duplex jumper, ST-ST, UPC polishing, length 3.0 m



Your advantages

- Comprehensively tested according to IEC 61753-122-2 and IEC 61753-1 Cat. C
- Temperature change test in accordance with IEC 61300-2-1
- Vibration test according to IEC 61300-2-1
- Tensile strength of the cable connection according to IEC 61300-2-5
- Multimode patch cable with outstanding optical and mechanical properties for indoor installation
- Ideal for use in distributor systems and for connecting termination devices
- Fire protection with LSZH sheath and UL 94 V0 components
- Interferometer tests at every stage of the certification process
- Satisfies optical and mechanical industry standards
- Connector with UPC polishing for optimum attenuation values

Commercial data

Item number	1111536
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIBC
GTIN	4063151028077
Weight per piece (including packing)	44.4 g
Weight per piece (excluding packing)	44.4 g
Customs tariff number	85447000
Country of origin	CN

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	2

Electrical properties

Transmission medium	FO
Transmission speed	1 Gbps

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	≥ 500

Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	LSZH

Connector

Connection 1

Type	Plug straight B-FOC (ST) / IP20
Degree of protection	IP20

Connection 2

Type	Plug straight B-FOC (ST) / IP20
Degree of protection	IP20

Cable/line

Cable length	3 m
Cable weight	5.3 kg/km
Cable type	FO duplex cable
Cable type	Zip cord
Cable abbreviation	I-V(ZN)H
External cable diameter	2x 2.00 mm
Outer sheath, material	LSZH
External sheath, color	orange
Smallest bending radius, fixed installation	30 mm
Smallest bending radius, movable installation	30 mm
Halogen-free	complying with IEC 60754-1/2
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Concentration of fumes	in accordance with IEC 61034
Flame resistance	yes

FO cable

Fiber	Fiberglass
Fiber type	Multimode fiberglass, 62.5/125 µm
Attenuation	≤ 3.5 dB/km (with 850 nm)
Transmission medium	Multi-mode fiberglass

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C
Ambient temperature (assembly)	-20 °C ... 60 °C
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes

Standards and regulations

Flame resistance	yes
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Concentration of fumes	in accordance with IEC 61034
Standards/specifications	IEC 61300-3-4
	RL: IEC 61300-3-6

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 10.0	EC002700

UNSPSC

UNSPSC 21.0	26121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com