

# NBC-R4ACS/0,2-93K/R4ACS - Patch cable



1113146

<https://www.phoenixcontact.com/us/products/1113146>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Patch cable, RJ45/IP20 straight on RJ45/IP20 straight, cable length: 0.2 m, number of positions: 4, 100 Mbps, CAT5, connection cross section: AWG 23- 22, PROFINET, 1x4xAWG22/7, SF/TQ, signal red RAL 3020

## Your advantages

- Perfect for industrial applications
- Worldwide approval with CE, UL, WEEE, and EAC
- Secure connection and disconnection with reliable locking clip protection
- Ideal EMC properties, thanks to 360° shielding
- Simultaneous power transmission with PoE++
- Resistant to shock and vibrations, thanks to robust molding
- High-speed data transmission with up to 100 Mbps (CAT5)

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1113146       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AB11          |
| Product key                          | ABNABA        |
| GTIN                                 | 4063151034061 |
| Weight per piece (including packing) | 40.4 g        |
| Weight per piece (excluding packing) | 33.951 g      |
| Customs tariff number                | 85444210      |
| Country of origin                    | PL            |

1113146

<https://www.phoenixcontact.com/us/products/1113146>

## Technical data

### Product properties

|                     |                          |
|---------------------|--------------------------|
| Product type        | Data cable preassembled  |
| Product family      | RJ45 INDUSTRIAL PN4 CAT5 |
| Sensor type         | PROFINET                 |
| Number of positions | 4                        |
| Shielded            | yes                      |

### Electrical properties

|   |          |
|---|----------|
| Rated voltage (III/2)                   | 72 V     |
| Rated current                           | 1.75 A   |
| Insulation resistance                   | > 1 TΩ   |
| Contact resistance                      | < 20 mΩ  |
| Transmission speed                      | 100 Mbps |
| Transmission characteristics (category) | CAT5     |
| Transmission speed                      | 100 Mbps |

### Dimensions

|        |         |
|--------|---------|
| Width  | 13.8 mm |
| Height | 14.8 mm |
| Length | 44.2 mm |

### Connector

#### Connection 1

|  |  |
|--|--|
| Type                                   | RJ45 Plug, straight, 4-position                            |
| Number of positions                    | 4  |
| Signal type/category                   | PROFINET CAT5 (IEC 11801), 100 Mbps<br>EtherCAT®, 100 Mbps |
| Insertion/withdrawal cycles            | ≥ 750  |
| Insertion force                        | 50 N (per signal contact)                                  |
| Withdrawal force                       | 30 N (per signal contact)                                  |
| Overvoltage category                   | I  |
| Degree of pollution                    | 2  |
| Material Contact                       | CuSn6  |
| Material Contact surface               | Ni/Au  |
| Material Contact carrier               | PC   |
| Material Housing                       | PP   |
| Color (Housing)                        | black  |
| Flammability rating according to UL 94 | V2   |
| Degree of protection                   | IP20   |
| Ambient temperature (operation)        | -40 °C ... 85 °C   |

# NBC-R4ACS/0,2-93K/R4ACS - Patch cable



1113146

<https://www.phoenixcontact.com/us/products/1113146>


## Connection 2

|  |  |
|--|--|
| Type                                   | RJ45 Plug, straight, 4-position                            |
| Number of positions                    | 4  |
| Signal type/category                   | PROFINET CAT5 (IEC 11801), 100 Mbps<br>EtherCAT®, 100 Mbps |
| Insertion/withdrawal cycles            | ≥ 750  |
| Insertion force                        | 50 N (per signal contact)                                  |
| Withdrawal force                       | 30 N (per signal contact)                                  |
| Overvoltage category                   | I  |
| Degree of pollution                    | 2  |
| Material Contact                       | CuSn6  |
| Material Contact surface               | Ni/Au  |
| Material Contact carrier               | PC   |
| Material Housing                       | PP   |
| Color (Housing)                        | black  |
| Flammability rating according to UL 94 | V2   |
| Degree of protection                   | IP20   |
| Ambient temperature (operation)        | -40 °C ... 85 °C   |

## Cable/line

|              |        |
|--------------|--------|
| Cable length | 0.20 m |
|--------------|--------|

## Sercos III [93K]

|                                 |  |
|---------------------------------|--|
| Dimensional drawing             |  |
| Cable weight                    | 68 kg/km   |
| UL AWM Style                    | 21694 (60 °C / 600 V)  |
| Number of positions             | 4  |
| Shielded                        | yes  |
| Cable type                      | Sercos III [93K]   |
| Conductor structure             | 1x4xAWG22/7, SF/TQ   |
| Signal runtime                  | 5.3 ns/m   |
| Conductor structure signal line | 7x 0.25 mm   |
| AWG signal line                 | 22   |
| Conductor cross-section         | 4x 0.34 mm <sup>2</sup>  |
| Wire diameter incl. insulation  | approx. 1.55 mm  |
| External cable diameter         | 6.50 mm ±0.2 mm  |
| Outer sheath, material          | PVC  |

# NBC-R4ACS/0,2-93K/R4ACS - Patch cable



1113146

<https://www.phoenixcontact.com/us/products/1113146>

|   |   |
|---|---|
| External sheath, color                        | signal red RAL 3020   |
| Conductor material                            | Tin-plated Cu litz wires  |
| Material wire insulation                      | PE  |
| Single wire, color                            | white, yellow, blue, orange   |
| Thickness, outer sheath                       | approx. 0.90 mm   |
| Type of pair shielding                        | Aluminum-lined polyester foil   |
| Overall twist                                 | Star quad   |
| Max. conductor resistance                     | ≤ 120 Ω/km  |
| Insulation resistance                         | ≥ 0.5 GΩ*km   |
| Coupling resistance                           | ≤ 20.00 mΩ/m (at 10 Hz)   |
| Wave impedance                                | 100 Ω ±15 Ω (at 100 MHz)  |
| Nominal voltage, cable                        | 600 V   |
| Test voltage Core/Core                        | 2000 V (50 Hz, 1 min.)  |
| Test voltage Core/Shield                      | 2000.00 V (50 Hz, 1 min.)   |
| Minimum bending radius, fixed installation    | 3 x D   |
| Minimum bending radius, flexible installation | 7 x D   |
| Smallest bending radius, fixed installation   | 20 mm   |
| Smallest bending radius, movable installation | 46 mm   |
| Flame resistance                              | according to UL 1685 (CSA FT 4)   |
| Resistance to oil                             | Resistant to oil to a limited extent  |
| Other resistance                              | UV resistant (according to UL 1581, Section 1200)   |
| Ambient temperature (operation)               | -40 °C ... 70 °C (cable, fixed installation)<br>-40 °C ... 70 °C (Cable, flexible installation) |
| Ambient temperature (installation)            | -20 °C ... 60 °C  |

## Standards and regulations

|                          |             |
|--------------------------|-------------|
| Standards/specifications | IEC 60603-7 |
|--------------------------|-------------|

# NBC-R4ACS/0,2-93K/R4ACS - Patch cable



1113146

<https://www.phoenixcontact.com/us/products/1113146>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1113146>

|  <b>UL Listed</b><br>Approval ID: E335024-V1S7 |                       |                       |                   |                             |
|---|-----------------------|-----------------------|-------------------|-----------------------------|
|   | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine   |                       |                       |                   |                             |
|   | 57 V                  | 1.75 A                | -                 | -                           |

|  <b>cUL Listed</b><br>Approval ID: E335024-V1S7 |                       |                       |                   |                             |
|--|-----------------------|-----------------------|-------------------|-----------------------------|
|  | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
| keine  |                       |                       |                   |                             |
|  | 57 V                  | 1.75 A                | -                 | -                           |

1113146

<https://www.phoenixcontact.com/us/products/1113146>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27060307 |
| ECLASS-15.0 | 27060307 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC001855 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# NBC-R4ACS/0,2-93K/R4ACS - Patch cable



1113146

<https://www.phoenixcontact.com/us/products/1113146>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)