

SAC-4P+D-22AWG-OE-OE-680-300,0 - Cable reel



1112982

<https://www.phoenixcontact.com/us/products/1112982>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, shielded, PVC, gray, 4-wire, color single wire: brown, white, blue, black, cable length: 300 m, Foil shielding plus drain wire

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1112982 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BF16 |
| Product key | AF1IIB |
| GTIN | 4063151034030 |
| Weight per piece (including packing) | 22.22 g |
| Weight per piece (excluding packing) | 22.22 g |
| Country of origin | US |

SAC-4P+D-22AWG-OE-OE-680-300,0 - Cable reel



1112982

<https://www.phoenixcontact.com/us/products/1112982>

Technical data

Product properties

| | |
|---------------------|--------------------|
| Product type | Cable by the meter |
| Application | Connector |
| Number of positions | 4 |


Electrical properties

| | |
|-----------------------|-------|
| Nominal voltage U_N | 300 V |
|-----------------------|-------|

Cable/line

| | |
|--------------|-------|
| Cable length | 300 m |
|--------------|-------|

PVC, gray, 105°C [680]

| | |
|---|---|
| Dimensional drawing |  |
| Cable weight | 45.42 kg/km |
| UL AWM Style | 2517 (105 °C / 300 V) |
| Number of positions | 4 |
| Shielded | yes |
| Cable type | PVC, gray, 105°C [680] |
| AWG signal line | 22 |
| Wire diameter incl. insulation | 1.27 mm ±0.03 mm |
| External cable diameter | 5.08 mm ±0.2 mm |
| Outer sheath, material | PVC |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |
| Material wire insulation | PVC (Signal line) |
| Single wire, color | brown, white, blue, black |
| Type of pair shielding | Plastic-coated aluminum foil, aluminum side inside |
| Overall twist | Conductors, fillers, and drain wire are twisted with left-hand lay |
| Max. conductor resistance | max. 51.1 Ω/km (20 °C) |
| Insulation resistance | ≥ (550 M Ohms/m @ 500V) |
| Nominal voltage, cable | 300 V |
| Minimum bending radius, flexible installation | 8 x D |
| Smallest bending radius, movable installation | 41 mm |
| Flame resistance | FT4 |
| Other resistance | UV resistant |

SAC-4P+D-22AWG-OE-OE-680-300,0 - Cable reel



1112982

<https://www.phoenixcontact.com/us/products/1112982>

| | |
|---------------------------------|---|
| Special properties | UL standards PLTC and ITC |
| Ambient temperature (operation) | -30 °C ... 105 °C (cable, fixed installation) |

SAC-4P+D-22AWG-OE-OE-680-300,0 - Cable reel



1112982

<https://www.phoenixcontact.com/us/products/1112982>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27061801 |
| ECLASS-15.0 | 27061801 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC003249 |
|----------|----------|

1112982

<https://www.phoenixcontact.com/us/products/1112982>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com