

FOC-LC:AA-SC:AA-OS2:D01/5 - FO patch cable




1115610

<https://www.phoenixcontact.com/us/products/1115610>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Single-mode OS2 duplex jumper, LC-SC, APC polishing, length 5 m



Your advantages

- Glass fiber optical, 8-shaped FO cable jumper
- Singlemode patch cable for indoor installation
- Excellent mechanical and optical properties
- Indoor use, suitable for FO distribution and termination devices
- Made of halogen-free flame-retardant material, RoHS compliant
- All components satisfy UL 94, V0
- Satisfies industry standards for optical and mechanical properties
- Insertion loss ≤ 0.5 dB (varies depending on the condition)
- Connector with UPC polishing for optimum attenuation values

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1115610 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB16 |
| Product key | ABNIBC |
| GTIN | 4063151040222 |
| Weight per piece (including packing) | 53.8 g |
| Weight per piece (excluding packing) | 44 g |
| Customs tariff number | 85447000 |
| Country of origin | CN |

1115610

<https://www.phoenixcontact.com/us/products/1115610>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Number of positions | 2 |
| Connection profile | LC/APC-SC/APC connector |

Electrical properties

| | |
|---------------------|------------------------|
| Transmission medium | Single-mode fiberglass |
| Transmission speed | 100 Gbps |
| Transmission speed | 100 GBit/s |

Mechanical properties

| | |
|---------------------------------------|------|
| Tensile strength short-term/long-term | 70 N |
|---------------------------------------|------|

Mechanical data

| | |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

Material specifications

| | |
|--|------|
| Flammability rating according to UL 94 | V0 |
| Outer sheath, material | LSZH |

Dimensions

External dimensions

| | |
|------------------------|------|
| External diameter min. | 2 mm |
| External diameter max. | 4 mm |

Connector

Connection 2

| | |
|------|----------------|
| Type | Plug SC duplex |
|------|----------------|

Cable/line

| | |
|-----------------------------------|------------------------|
| Cable length | 5.00 m |
| Cable weight | 5.30 kg/km |
| Cable type | Single-mode fiberglass |
| Cable type | Zip cord |
| Cable abbreviation | I-V(ZN)H |
| Cable structure | Figure 8 cable |
| External cable diameter | 2.00 mm |
| Outer sheath, material | LSZH |
| External sheath, color | yellow |
| Single wire, number of litz wires | 2 |
| Individual wire diameter | 900 µm |

FOC-LC:AA-SC:AA-OS2:D01/5 - FO patch cable



1115610

<https://www.phoenixcontact.com/us/products/1115610>

| | |
|---|---|
| Bending radius, long-term | 50 mm |
| Bending radius short term/long term | 30 mm |
| Smallest bending radius, fixed installation | 30 mm |
| Smallest bending radius, movable installation | 16 mm |
| Tensile strength short-term/long-term | 70 N |
| Lateral pressure, long-term | 100.00 N/cm |
| Halogen-free | complying with IEC 60754-1/2 |
| Resistance to oil | Not resistant to oil, gasoline, acids, and lyes |
| Concentration of fumes | in accordance with IEC 61034 |
| Flame resistance | yes |
| Behavior in fire | No corrosive or toxic fumes |

FO cable

| | |
|---------------------|--|
| Number of fibers | 2 |
| Fiber | Fiberglass |
| Fiber type | Single mode fiberglass, 9/125 µm |
| Cable, attenuation | 0.5 dB/km (1310 nm), 0.4 dB/km (1550 nm) |
| Attenuation | ≤ 0.5 dB/km (1310 nm) |
| Return Loss | ≥ 60 dB |
| Transmission medium | Single-mode fiberglass |

Standards and regulations

| | |
|------------------------|---|
| Behavior in fire | No corrosive or toxic fumes |
| Flame resistance | yes |
| Resistance to oil | Not resistant to oil, gasoline, acids, and lyes |
| Concentration of fumes | in accordance with IEC 61034 |

1115610

<https://www.phoenixcontact.com/us/products/1115610>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27061003 |
| ECLASS-15.0 | 27061003 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002700 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

1115610

<https://www.phoenixcontact.com/us/products/1115610>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com