
FOC-LC:AA-SC:AA-OS2:D01/0.5 - FO patch cable

1115614

https://www.phoenixcontact.com/us/products/1115614

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Single-mode OS2 duplex jumper, LC-SC, APC polishing, length 0.5 m



Your advantages

- Glass fiber optical, 8-shaped FO cable jumper
- Singlemode patch cable for indoor installation
- Excellent mechanical and optical properties
- Indoor use, suitable for FO distribution and termination devices
- Made of halogen-free flame-retardant material, RoHS compliant
- All components satisfy UL 94, V0
- Satisfies industry standards for optical and mechanical properties
- Insertion loss ≤0.5 dB (varies depending on the condition)
- Connector with UPC polishing for optimum attenuation values

Commercial data

Item number	1115614
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AB16
Product key	ABNIBC
GTIN	4063151040154
Weight per piece (including packing)	21.1 g
Weight per piece (excluding packing)	21 g
Customs tariff number	85447000
Country of origin	CN

Technical data

Product properties

Product type	Data cable preassembled
Number of positions	2

Electrical properties

Transmission medium	FO
Transmission speed	100 Gbps

Mechanical properties

Tensile strength short-term/long-term	70 N

Mechanical data

Insertion/withdrawal cycles	≥ 500

Material specifications

Flammability rating according to UL 94	V0
Outer sheath, material	LSZH

Dimensions

External dimensions

External diameter min.	2.00 mm
External diameter max.	4.00 mm

Connector

Connection 2

Type	Plug straight SC / IP20
Degree of protection	IP20

Cable/line

Cable length	0.5 m
Cable weight	5.3 kg/km
Cable type	FO duplex cable
Cable type	Zip cord
Cable abbreviation	I-V(ZN)H
Outer sheath, material	LSZH
External sheath, color	yellow
Wire diameter incl. insulation	2x 2 mm
Individual wire diameter	900 µm
Bending radius, long-term	50.00 mm
Bending radius short term/long term	30.00 mm
Smallest bending radius, fixed installation	30 mm

Smallest bending radius, movable installation	16 mm
Tensile strength short-term/long-term	70 N
Lateral pressure, long-term	100.00 N/cm
Halogen-free	complying with IEC 60754-1/2
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Concentration of fumes	in accordance with IEC 61034
Flame resistance	yes
Behavior in fire	No corrosive or toxic fumes

FO cable

Fiber	Fiberglass
Fiber type	Single mode fiberglass, 9/125 µm
Attenuation	≤ 0.5 dB/km (1310 nm)
Return Loss	≥ 60 dB
Transmission medium	Single-mode fiberglass

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C
Ambient temperature (storage/transport)	-20 °C ... 60 °C
Ambient temperature (assembly)	-20 °C ... 60 °C
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes

Standards and regulations

Behavior in fire	No corrosive or toxic fumes
Flame resistance	yes
Resistance to oil	Not resistant to oil, gasoline, acids, and lyes
Concentration of fumes	in accordance with IEC 61034

Classifications

ECLASS

ECLASS-13.0	27061003
ECLASS-15.0	27061003

ETIM

ETIM 10.0	EC002700

UNSPSC

UNSPSC 21.0	26121600

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%

EF3.1 Climate Change

CO2e kg	0.156 kg CO2e

Phoenix Contact 2026 © - all rights reserved
https://www.phoenixcontact.com

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com