

MM-EML (15X6)R C1 YE/BK - Label



1116160

<https://www.phoenixcontact.com/us/products/1116160>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, Mixed color, unmarked, can be labeled with: THERMOMARK GO, mounting type: adhesive, Number of individual labels: 321, text field height: 6 mm, text field width: 15 mm

Product description

The MM-EML... polyester self-adhesive labels are available as pre-punched material for equipment marking.

Your advantages

- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The material is cUL certified
- The pre-punched self-adhesive labels are particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the innovative material composition, each label can be printed which results in zero wastage
- The pre-punched geometry enables easy and convenient use



Commercial data

| | |
|------------------------|---------------|
| Item number | 1116160 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG23 |
| Product key | BG241E |
| GTIN | 4063151040291 |

MM-EML (15X6)R C1 YE/BK - Label



1116160

<https://www.phoenixcontact.com/us/products/1116160>

| | |
|--------------------------------------|----------|
| Weight per piece (including packing) | 66 g |
| Weight per piece (excluding packing) | 54 g |
| Customs tariff number | 96121010 |
| Country of origin | CN |

Technical data

Product properties

| | |
|--------------|------------------|
| Product type | Conductor marker |
|--------------|------------------|

Marking

| | |
|-----------------------------|------------------|
| Number of individual labels | 321 |
| Identification technology | Thermal transfer |

Dimensions

| | |
|--------|----------|
| Width | 15.00 mm |
| Height | 6.00 mm |
| Depth | 0.06 mm |

Text field

| | |
|-------------------|-------|
| Text field width | 15 mm |
| Text field height | 6 mm |

Material specifications

| | |
|-----------------------|--|
| Foil strength | 50 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) |
| | yellow (RAL 1018) |
| | black (RAL 9005) |
| Material | Polyester |
| Base element material | Polyester |
| Components | free from silicone, halogen, and cadmium |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|---|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |
| Procedure | Artificial irradiation. |

MM-EML (15X6)R C1 YE/BK - Label



1116160

<https://www.phoenixcontact.com/us/products/1116160>

Wipe resistance of inscriptions

| | |
|---|--|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|---|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

MM-EML (15X6)R C1 YE/BK - Label



1116160

<https://www.phoenixcontact.com/us/products/1116160>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1116160>



cULus Recognized
Approval ID: MH48542

MM-EML (15X6)R C1 YE/BK - Label



1116160

<https://www.phoenixcontact.com/us/products/1116160>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

MM-EML (15X6)R C1 YE/BK - Label



1116160

<https://www.phoenixcontact.com/us/products/1116160>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 2.91 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com