

MM-WMTB HF (40X12)R C1 WH/BK - Cable marker



1116166

<https://www.phoenixcontact.com/us/products/1116166>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable marker, Roll, Mixed color, unmarked, can be labeled with: THERMOMARK GO, cable diameter range: 6 ... 115 mm, mounting type: Assembly with cable ties, Number of individual labels: 50, text field height: 8.5 mm, text field width: 40 mm

Product description

Prepunched, halogen-free MM-WMTB HF conductor markers made of polyurethane are attached to the conductor with a cable tie.

Your advantages

- The pre-punched geometry enables easy and convenient use
- Thanks to the innovative material composition, each label can be printed which results in zero wastage
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- No visible difference between retrospective marking and existing markings created with a desktop roll printer
- The cable markers are mounted very easily using a cable tie. Alternatively, a large number of conductors can also be bundled together in this way
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing



Commercial data

Item number	1116166
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG221E
GTIN	4063151042011
Weight per piece (including packing)	78.5 g
Weight per piece (excluding packing)	78 g

MM-WMTB HF (40X12)R C1 WH/BK - Cable marker



1116166

<https://www.phoenixcontact.com/us/products/1116166>

Customs tariff number	96121010
Country of origin	CN

MM-WMTB HF (40X12)R C1 WH/BK - Cable marker



1116166

<https://www.phoenixcontact.com/us/products/1116166>

Technical data

Product properties

Product type	Conductor marker
--------------	------------------

Marking

Number of individual labels	50
Number of individual labels per row	1
Identification technology	Thermal transfer

Dimensions

Width	60 mm
Height	11.55 mm
Depth	0.45 mm

Text field

Text field width	40 mm
Text field height	8.5 mm

Material specifications

Foil strength	450 µm
Color	multicolored (RAL -)
	white (RAL 9010)
	black (RAL 9005)
Material	PUR
Flammability rating according to UL 94	HB
Base element material	PUR
Components	free from silicone, halogen, and cadmium

Cable/line

External cable diameter	6 mm ... 115 mm
-------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-	VDMA 24364-A1-L:2018-05
--	-------------------------

MM-WMTB HF (40X12)R C1 WH/BK - Cable marker



1116166

<https://www.phoenixcontact.com/us/products/1116166>

conformity)	
Result	Test passed

Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. -]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed
Gasoline [CAS No. 64742-49-0]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed

MM-WMTB HF (40X12)R C1 WH/BK - Cable marker



1116166

<https://www.phoenixcontact.com/us/products/1116166>

IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed
Test duration	96 h

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	Assembly with cable ties
---------------	--------------------------

MM-WMTB HF (40X12)R C1 WH/BK - Cable marker



1116166

<https://www.phoenixcontact.com/us/products/1116166>

Classifications

ECLASS

ECLASS-13.0	27281102
ECLASS-15.0	27281102

ETIM

ETIM 10.0	EC001530
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

1116166

<https://www.phoenixcontact.com/us/products/1116166>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.282 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com