

# RFC 4072R - Controller



1136419

<https://www.phoenixcontact.com/us/products/1136419>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Controller (SPS), PLCnext Control; Programming: High-level language and IEC 61131-3; Operating system: Yocto/Linux® (real-time); Programming tool: PLCnext Engineer, Eclipse®, Visual Studio®, MATLAB®/ Simulink®; System redundancy; Processor: Intel® Core™ i5-6300U, 2x 2.4 GHz.

## Your advantages

- Real-time-capable Linux operating system for deterministic and reliable execution of time-critical processes
- Supports numerous protocols such as: HTTP, HTTPS, FTP, OPC UA, SNTP, SNMP, SMTP, SQL, MySQL, DCP, etc. – for smooth communication with IT systems
- Direct connection to the Proficloud, the PLCnext Store and any cloud platforms – for seamless IoT integration of your applications
- Support for numerous fieldbus protocols (PROFINET, Modbus TCP/RTU, Ethernet/IP, etc.) for easy integration into existing automation technology systems and installations
- Maximum design freedom thanks to the combination of classic PLC programming with modern high-level languages such as C++, C#, or Python
- Meets the highest security requirements of industrial automation – for the protection of your applications and data

## Commercial data

Item number	1136419
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR09
Product key	DRADBA
GTIN	4063151072230
Weight per piece (including packing)	3,062 g
Weight per piece (excluding packing)	2,000 g
Customs tariff number	85371091
Country of origin	DE

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Controller
Product family	PLCnext Control
Type	Stand-alone
Special properties	System redundancy

#### Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
Pollution degree	2 (when installed in a control cabinet or housing with IP54 degree of protection or higher)

#### Display

Diagnostics display	yes
---------------------	-----

### System properties

Flash memory	100 Mbyte (internal flash memory)
	SD card from Phoenix Contact (for external flash memory, see accessories)
Retentive data storage	2 Mbyte

#### IEC 61131 runtime system

Program memory	16 Mbyte
Data storage system	32 Mbyte

#### INTERBUS-Master

Amount of process data (Input/output data)	max. 128 kByte (Input and output data)
--------------------------------------------	----------------------------------------

#### PROFINET

Device function	PROFINET-Controller
Number of supported devices	max. 256
Vendor ID	00B0 <sub>hex</sub> / 176 <sub>dez</sub>

#### Function

Diagnostics display	yes
Redundancy function	yes
Note on redundancy function	Controller redundancy
Safety function	no

#### Functionality

Programming languages supported	Instruction list (IL)
	Symbolic flowchart (SFC)

	Ladder diagram (LD)
	Function block diagram (FBD)
	Structured text (ST)
	C++
	C#
	Java
	Python®
	Simulink®

## System requirements

Application interface	OPC UA®
	OPC UA Pub/Sub

## Electrical properties

Power consumption	typ. 25 W (Without fan module)
	max. 35 W (With fan module)
Maximum power dissipation for nominal condition	25 W (Without fan module)
Transmission medium	Copper
	FO

## Supply

Supply voltage	24 V DC
Supply voltage range	18 V DC ... 32.1 V DC (including ripple (3.6 V <sub>PP</sub> ))
Power supply connection	Via COMBICON, max. conductor cross-section 2.5 mm <sup>2</sup>

## Real-time clock

Realtime clock	integrated (capacitive buffering)
Description realtime clock	1.73 s/day = 20 ppm at 25 °C

## Potentials

Protective circuit	Surge protection of the supply voltage; electronic
	Polarity reversal protection of the supply voltage; electronic

## Connection data

Tightening torque	0.5 ... 0.6 Nm
-------------------	----------------

## COMBICON connector

Conductor cross-section, rigid	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section, flexible	0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>
Conductor cross-section AWG	24 ... 12

## Interfaces

Web server	yes
------------	-----

## USB

Number of interfaces	1
Connection method	USB type A, socket

## Ethernet

Bus system	RJ45
Number of interfaces	4
Connection method	RJ45 jack
Note on the connection method	Auto negotiation and auto crossing, auto polarity exchange
Transmission speed	10/100/1000 Mbps (LAN 1/LAN 2, half duplex or full duplex) 10/100 Mbps (LAN3.1/LAN3.2 (internally switched), half duplex or full duplex)

## Dimensions

### External dimensions

Width / Height / Depth	122 mm / 182 mm / 173 mm (without fan module)
	122 mm / 220 mm / 173 mm (With fan module)

## Material specifications

Color	gray (RAL 7042)
-------	-----------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 60 °C up to 2000 m above mean sea level (recommended: above 50°C with fan module)
	0 °C ... 55 °C 2000 m ... 3000 m above mean sea level (With fan module only)
	0 °C ... 50 °C 3000 m ... 4000 m above mean sea level (With fan module only)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Shock (operation)	20g (in accordance with EN 60068-2-27/IEC 60068-2-27)
Vibration (operation)	1g (in accordance with EN 60068-2-6/IEC 60068-2-6)
Air pressure (operation)	60 kPa ... 108 kPa (up to 4000 m above mean sea level)
Air pressure (storage/transport)	58 kPa ... 108 kPa (up to 4500 m above mean sea level)
Resistance to gases that may endanger the functions, in acc. with DIN 40046-36, DIN 40046-37	Use of the device in these ambient conditions is prohibited.

## EMC data

Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU
Conformance with EMC directives	Immunity test in accordance with EN IEC 61000-6-2 Electrostatic discharge (ESD) IEC 61000-4-2 Criterion B, ±6 kV contact discharge, ±8 kV air discharge
	Immunity test in accordance with EN IEC 61000-6-2 Electromagnetic fields IEC 61000-4-3 Criterion A, Field intensity: 10 V/m

# RFC 4072R - Controller



1136419

<https://www.phoenixcontact.com/us/products/1136419>

	Immunity test in accordance with EN IEC 61000-6-2 Fast transients (burst)IEC 61000-4-4 Criterion B, Supply lines: $\pm 2$ kV, Signal/data lines: $\pm 2$ kV
	Immunity test in accordance with EN IEC 61000-6-2 Transient overvoltage (surge)IEC 61000-4-5 Criterion B, supply lines: $\pm 0.5$ kV, signal/data cables: $\pm 1$ kV
	Immunity test in accordance with EN IEC 61000-6-2 Conducted interferenceIEC 61000-4-6 Criterion A, Test voltage 10 V
	Noise emission test in accordance with EN IEC 61000-6-4 Class A

## Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# RFC 4072R - Controller



1136419

<https://www.phoenixcontact.com/us/products/1136419>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1136419>

**DNV**

Approval ID: TAA00003CX

# RFC 4072R - Controller



1136419

<https://www.phoenixcontact.com/us/products/1136419>

## Classifications

### ECLASS

ECLASS-13.0	27242207
ECLASS-15.0	27242207

### UNSPSC

UNSPSC 21.0	32151700
-------------	----------

1136419

<https://www.phoenixcontact.com/us/products/1136419>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	fb620ac8-c3b8-42b6-9454-fafe7da884fb

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)