

CHARX SEC-3050 - AC charging controller



1139018

<https://www.phoenixcontact.com/us/products/1139018>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX control modular, AC charging controller, with Embedded Linux system, IEC 61851-1, ISO/IEC 15118, operating mode: Stand-Alone, Client, Server, interface: Ethernet (2x), CHARX control modular system bus, MICRO-USB type C, communication protocol: OCPP 1.6J, Modbus/TCP, MQTT, Connectable peripheral devices: Energy meter, RFID, DC residual current detection, DIN rail mounting

Commercial data

Item number	1139018
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWBRDA
GTIN	4063151082833
Weight per piece (including packing)	248 g
Weight per piece (excluding packing)	186 g
Customs tariff number	85371091
Country of origin	PL

CHARX SEC-3050 - AC charging controller



1139018

<https://www.phoenixcontact.com/us/products/1139018>

Technical data

Product properties

Product type	AC charging controller
Product family	CHARX control modular
Design	with Embedded Linux system
Charging mode	Mode 3, Case B + C
Operating mode	Stand-Alone
	Client
	Server
Modem for communication present	no
Connectable peripheral devices	Energy meter
	RFID
	DC residual current detection

System properties

Processor	Arm® Cortex®-A7, 528 MHz i.MX6 UL
RAM	512 Mbyte (RAM)
Data storage system	8 GByte (eMMC)
Operating system	Linux
Management	Web-based management

Electrical properties

Supply

Supply voltage	12 V DC \pm 5 %
Supply voltage range	11.4 V DC ... 12.6 V DC
Current consumption	max. 2 A (Stand-alone operation)
	< 200 mA (No load, without external loads)

Insulation characteristics

Pollution degree	2 (in acc. with IEC 60664-1)
Overvoltage category	III

Input data

Digital

Number of digital inputs	4
Description of the input	Digital input
Nominal input voltage U_N	12 V
Input voltage range U1	0 V ... 3 V (Off)
Input voltage range U2	9 V ... 15 V (On)

Output data

Digital

CHARX SEC-3050 - AC charging controller



1139018

<https://www.phoenixcontact.com/us/products/1139018>

Output name	Digital output
Number outputs	4
Maximum output voltage	≤ 12 V (Low-side operation)
Maximum output current	max. 600 mA

Connection data

Push-in Technology

Conductor cross-section rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 16
Cable cross-section range	0.25 mm ² ... 1.5 mm ² (with ferrules)
Stripping length of the individual wire	8 mm
	10 mm (for contactor control)

Interfaces

Interface	Ethernet (2x)
	CHARX control modular system bus
	USB-C

Interface for Ethernet

Interface	Ethernet
Connection method	RJ45 jack
Number of interfaces	2
Number of supported devices	2
Serial transmission speed	10/100 Mbps
Transmission length	100 m
Operating mode	WAN/LAN
	LAN/LAN
Protocols supported	OCPP 1.6J
	Modbus/TCP
	MQTT
	HTTP
	HTTPS

Interface for configuration and diagnostics

Interface	Configuration and diagnostics
Connection method	USB type C
Number of interfaces	1
Protocols supported	RNDIS

Interface for energy meter

Interface	Energy meter
Bus system	RS-485
Transmission speed range	9.6 kbps ... 115.2 kbps (Automatic setting in accordance with the selected energy meter)

CHARX SEC-3050 - AC charging controller



1139018

<https://www.phoenixcontact.com/us/products/1139018>

Interface for RFID reader

Interface	RFID readers
Bus system	RS-485
Transmission speed range	9.6 kbps ... 115.2 kbps (Automatic setting in accordance with the selected RFID reader)

Interface for CHARX control modular system bus

Interface	CHARX control modular system bus
Connection method	DIN rail bus connector
Number of interfaces	1

Interface for vehicle

Interface	Vehicle interface
Communication protocol	IEC 61851-1
	ISO 15118
	GB/T 18487
Proximity	IEC 61851-1
	GB/T 18487
Control voltage	± 12 V (Locking actuator)
Locking release in the event of mains failure	Integrated release function of the locking actuator for disconnection of Infrastructure Plug and Infrastructure Socket Outlet
Rated current	2 A

Interface for residual current detection

Interface	Residual current detection
Sensor supply voltage	12 V DC
Signal level	12 V (Different terminal points)
	0 V (Different terminal points)
	12 V

Interface for temperature monitoring

Interface	Temperature monitoring
Sensor type	Pt 1000
	PTC chain
Tripping characteristic	configurable

Interface for contactor control

Interface	Contactor control
Interface description	Floating switch contact
Switching voltage	max. 250 V AC (Necessary for ISO 15118 communication)
	max. 30 V DC
Rated current	2 A
Interrupting rating	max. 1500 VA

Dimensions

CHARX SEC-3050 - AC charging controller



1139018

<https://www.phoenixcontact.com/us/products/1139018>

Charging controller

Width	37.6 mm
Height	121 mm
Depth	85 mm

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 65 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above mean sea level)
Air pressure (storage/transport)	58 kPa ... 106 kPa (up to 4500 m above mean sea level)

Standards and regulations

Standards

Standards/regulations	IEC 61851-1
	ISO/IEC 15118

Mounting

Mounting type	DIN rail mounting
Assembly note	DIN rail mounting
Mounting position	any

CHARX SEC-3050 - AC charging controller



1139018

<https://www.phoenixcontact.com/us/products/1139018>

Drawings

Schematic diagram



Connections and status indicators

CHARX SEC-3050 - AC charging controller



1139018

<https://www.phoenixcontact.com/us/products/1139018>

Classifications

ECLASS

ECLASS-13.0	27144703
ECLASS-15.0	27144703

ETIM

ETIM 10.0	EC002889
-----------	----------

UNSPSC

UNSPSC 21.0	39121800
-------------	----------

CHARX SEC-3050 - AC charging controller



1139018

<https://www.phoenixcontact.com/us/products/1139018>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	3d48fd58-8de9-4b55-af4e-aae4ec700ec7

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com