

MM-EML (EX8)R C1 YE/BK - Label



1116050

<https://www.phoenixcontact.com/us/products/1116050>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, Mixed color, unmarked, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, roll length: 8 m, text field height: 6 mm, text field width: 8000 mm

Product description

The MM-EML... polyester self-adhesive labels are available as continuous media for equipment marking.

Your advantages

- The material is cUL certified
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 1116050 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | BG23 |
| Product key | BG241E |
| GTIN | 4063151041700 |
| Weight per piece (including packing) | 57.3 g |
| Weight per piece (excluding packing) | 47 g |

MM-EML (EX8)R C1 YE/BK - Label



1116050

<https://www.phoenixcontact.com/us/products/1116050>

| | |
|-----------------------|----------|
| Customs tariff number | 96121010 |
| Country of origin | CN |

1116050

<https://www.phoenixcontact.com/us/products/1116050>

Technical data

Product properties

| | |
|--------------|---------------|
| Product type | Device marker |
|--------------|---------------|

Marking

| | |
|---------------------------|------------------|
| Identification technology | Thermal transfer |
|---------------------------|------------------|

Dimensions

| | |
|----------------|---------|
| Length of roll | 8.00 m |
| Height | 8 mm |
| Depth | 0.06 mm |

Text field

| | |
|-------------------|---------|
| Text field width | 8000 mm |
| Text field height | 6 mm |

Material specifications

| | |
|-----------------------|------------------------------------------|
| Foil strength | 50 µm |
| Adhesive | Acrylic |
| Color | multicolored (RAL -) |
| | yellow (RAL 1018) |
| | black (RAL 9005) |
| Material | Polyester |
| Base element material | Polyester |
| Components | free from silicone, halogen, and cadmium |

Environmental and real-life conditions

Ambient conditions

| | |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C |
| Recommended ambient temperature (storage/transport) | 23 °C |
| Recommended humidity (storage/transport) | 50 % (Storage in a dry and dark place in the original packaging is recommended) |

Test for substances that would hinder coating with paint or varnish

| | |
|-------------------------------------------------------------------|----------------------|
| Testing for paint wetting impairment substances (LABS-conformity) | VW PV 3.10.7:2005-02 |
| Result | Test passed |

UV resistance

| | |
|---------------|---------------------------------------|
| Specification | DIN EN ISO 4892-2:2021-11 (following) |
| Result | Test passed |
| Test duration | 96 h |

Wipe resistance of inscriptions

| | |
|---------------|-------------------------------------|
| Specification | DIN EN 61010-1 (VDE 0411-1):2011-07 |
|---------------|-------------------------------------|

MM-EML (EX8)R C1 YE/BK - Label



1116050

<https://www.phoenixcontact.com/us/products/1116050>

| | |
|-------------------------------------------------|------------------------------------------------|
| | DIN EN 62208 (VDE 0660-511):2012-06 (in parts) |
| Isopropanol (99%) [67-63-0] | Test passed |
| n-Hexane [CAS No. 110-54-3] | Test passed |
| Water + Petroleum ether [CAS No. 64742-82-1] | Test passed |

Testing in a condensation changing climate in the presence of sulfur dioxide

| | |
|---------------|--------------------------|
| Specification | DIN EN ISO 22479:2022-08 |
| Result | Test passed |
| Procedure | Method B |
| Cycles | 2 |

Salt spray test

| | |
|---------------|-----------------------------------------------|
| Specification | DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10 |
| Result | Test passed |

Standards and regulations

| | |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

Mounting

| | |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

MM-EML (EX8)R C1 YE/BK - Label



1116050

<https://www.phoenixcontact.com/us/products/1116050>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1116050>



cULus Recognized
Approval ID: MH48542

MM-EML (EX8)R C1 YE/BK - Label



1116050

<https://www.phoenixcontact.com/us/products/1116050>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27281103 |
| ECLASS-15.0 | 27281103 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001288 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

MM-EML (EX8)R C1 YE/BK - Label



1116050

<https://www.phoenixcontact.com/us/products/1116050>

Environmental product compliance

EU RoHS

| | |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

China RoHS

| | |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 2.955 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com